

# MAD400 series

**AIR UNITS (Drain Trap)**




**mindman**

## Specification



### Symbol



| Model                    | MAD400                 |     |     |
|--------------------------|------------------------|-----|-----|
| Bore No.                 | 8A                     | 10A | 15A |
| Port size                | 1/4                    | 3/8 | 1/2 |
| Medium                   | Air                    |     |     |
| Operating pressure range | 0.15~1 MPa             |     |     |
| Proof pressure           | 1.5 MPa                |     |     |
| Ambient temperature      | -5~+60°C (No freezing) |     |     |
| Weight                   | 480 g                  |     |     |

※ Standard unit contains semi-auto-drain function when operating pressure below 0.05 MPa.

## Order example

**MAD400** – **8A** – **D3** – □

MODEL

BORE SIZE

8A: 1/4  
10A: 3/8  
15A: 1/2

AUTO DRAIN VALVE

PORT THREAD

Blank: Rc thread  
G: G thread  
NPT: NPT thread

Blank: Male thread (MADV400-WB)  
D3: Female thread (MADV400-WA)

