


MCGA Dimensions / Push type $\phi 20 \sim \phi 80$

TWIN-GUIDE CYLINDER




MCGA-23/MCGA-63



MCGA-23/MCGA-63

For tube I.D. $\phi 80$, stroke 101~700mm



MCGA-23/MCGA-63

Code Tube I.D.	A	B	B1	C	C1	D	E	E1	F	G	G1	H	K	K1	L	L1	L2	M	N1	N2	P	P1	Q	Q1	R	U	Z	Z1
20	75	34	32	63	20	M5×0.8×15dp	45	-	M4	32	16	M5×0.8×10dp	75	15	54	36	18	M4×0.7×8dp	22.5	20	4	6	$\phi 8$	$\phi 10$	Rc1/8	25	11	10
32	106	51.5	45	90	30	M8×1.25×20dp	63	-	M6	40	18	M6×1.0×12dp	100	20	66.5	41.5	29.5	M5×0.8×10dp	32	25	5	9	$\phi 13(\phi 12)$	$\phi 16$	Rc1/4	30	12	12
40	128	59	52	112	36	M8×1.25×20dp	80	-	M6	50	20	M6×1.0×12dp	125	25	81	51	30	M5×0.8×10dp	40	30	5	14	$\phi 16$	$\phi 16$	Rc1/4	35	16	16.5
50	150	69	62	132	45	M10×1.5×25dp	100	20	M8	63	25	M8×1.25×16dp	140	30	87	52	39	M6×1.0×12dp	37.5	50	6	16	$\phi 20$	$\phi 20$	Rc3/8	40	16	17.5
63	180	87	78	156	53	M12×1.75×30dp	118	25	M10	80	40	M10×1.5×20dp	175	35	100	60	68	M8×1.25×16dp	47.5	60	9	16	$\phi 25$	$\phi 20$	Rc3/8	60	17.5	21
80	243	110	100	212	71	M16×2.0×40dp	160	30	M12	106	56	M10×1.5×20dp	224	40	110.5	62.5	※	M10×1.5×20dp	60	80	10	18	$\phi 35$	$\phi 25$	Rc3/8	75	22	19.5

※ With stroke 30~75mm L2=17.5, stroke 100mm L2=87.5

□ :For MCGA-23 type, stroke 30~100mm, () : For MCGA-63 type

MCGA-23/MCGA-63 Tube I.D. $\phi 80$, stroke 101~700mm

Code Tube I.D.	A	B	B1	C	C1	D	E	E1	F	G	G1	H	K	K1	L	L1	L3	M	N1	N2	P	P1	Q	Q1	R	U	Z	Z1
80	243	110	100	212	71	M16×2.0×40dp	160	30	M12	106	56	M10×1.5×20dp	224	40	213	150	256	M10×1.5×20dp	60	80	10	18	$\phi 35$	$\phi 25$	3/8	75	40	



M-10

Mindman