

MAFR500 series

AIR UNIT (F.R.UNIT)




Mindman



Specification

Model	MAFR500	
Bore No.	20A	25A
Port size	3/4	1
Medium	Air	
Operating pressure range	0.05~1 MPa	
Proof pressure	1.5 MPa	
Regulated pressure range	0.05~0.85 MPa	
Ambient temperature	-5~+60°C (No freezing)	
Filter element	40 μm	
Attachment	Pressure gauge, bracket	
Weight	2037 g	

Symbol



※ Standard unit contains semi-auto-drain function when operating pressure below 0.05 MPa.

Order example

MAFR500 - 20A - D - □

MODEL

BORE SIZE
20A: 3/4
25A: 1

D: Auto drain valve
(YD401)

PORT THREAD
Blank: Rc thread
G: G thread
NPT: NPT thread

