


MAL310 series Stainless steel #316 type

AIR UNITS (L.UNIT)



Symbol



Specification

Model	MAL310	
Bore No.	8A	10A
Port size	Rc1/4	Rc3/8
Medium	Air	
Max. operating pressure	1 MPa	
Proof pressure	1.5 MPa	
Ambient temperature	-5~+60°C (No freezing)	
Lubricating oil capacity	140 c.c	
Min. flow for oil drip	30 ℓ/min	40 ℓ/min
Recommended lubricating oil	Turbine oil ISO-VG32	
Weight	1070 g	

Order example

MAL310 – 10A – □

MODEL

BORE SIZE

8A : 1/4
10A : 3/8

PORT THREAD

Blank: Rc thread
G: G thread
NPT: NPT thread

