
MUAW series


## 2/2 WAY N.C. PISTON TYPE SOLENOID VALVE

Mindman

2-WAY normally closed solenoid valve. Available fluid: Water, air.



### **Order example**



## **Specification**

- MUAW series is multiplex acting, piston guide, conductive and normal close.
- AC voltage tolerance: ±10%, DC voltage tolerance: ±1%

# Material

Parts name	Material					
Body	Cast bronze					
Coil	Special copper wire (H class)					
Core	Stainless steel					
Tube	Stainless steel					
Spring	Stainless steel					
Plug	PTFE+15%GF					
Piston	Brass					
Piston plug	NBR					

#### Caution

- Min pressure to open: over 0.05~0.1 MPa.
- Before pipelining, the pipe line must be very clean without any contaminants or impurity.
- To extend the lifetime, Y-line filter should be installed in the front end of solenoid valve.
- It should be installed horizontally; vertical installation is not advisable.

### Not for fluid of

- Liquid when heat, solid when cool.
- Corrosive fluid.
- Viscosity over 50 cst.
- Temperature over 80°C.

Model	DIN	Port size	CV	Orifice	Fluid	Operating pressuer range (MPa)		Dimensions (mm)			Weight
		FUILSIZE		(mm)	temp.°C	Water	Air	L	Н	D	(kg)
MUAW-15		Rc1/2"	4.0	17	-5~+80	0.05~1	0.05~1.5	82	125	58	1.60
MUAW-20		Rc3/4"	6.0	17	-5~+80	0.05~1	0.05~1.5	82	125	58	1.67
MUAW-25		Rc1"	12.0	22	-5~+80	0.05~1	0.05~1.5	91	133	58	2.02
MUAW-35		Rc1 1/4"	18.0	30	-5~+80	0.1~1	0.1~1.5	111	141	58	3.08
MUAW-40		Rc1 1/2"	22.0	32	-5~+80	0.1~1	0.1~1.5	111	144	58	3.10
MUAW-50		Rc2"	48.0	50	-5~+80	0.1~1	0.1~1.5	163	175	58	6.82

