








Specification

Model	MVHT-302, MVHT-400		
Bore No.	8A	10A	15A
Port size	1/4	3/8	1/2
No. of port	3(2)		
No. of position	2		
Medium	Air		
Operating pressure range	0~1.5 MPa		
Proof pressure	2 MPa		
Ambient temperature	-5~+60°C (No freezing)		
Weight	249 g, 220 g		

Order example





MVHT Dimensions







MVHT-302









MVHT-400

