



Selection table



Specification

Model	PGV-40S
Bore No.	6A
Port size	1/8
Medium	Air
Operating pressure range	-100~0 kPa (*)
Precision	ASME B class
Ambient temperature	-5~+60°C (No freezing)
Weight	50 g

* Do not use for positive pressure, otherwise it will cause damage to pressure gauge.

Order example

PGV — 40 S — NPT

MODEL

GAUGE
SIZE
40

CASE
MATERIAL
S: Stainless steel

PORT THREAD
Blank: R thread
NPT: NPT thread

Dimensions

