



### Specification

Model	TPU*
Medium	Air
Max. pressure range	0~100 psi (0~0.7 MPa)
Working vacuum	-29.5 in.Hg (-100 kPa)
Ambient temperature	-5~+140°F(-15~+60°C) (No freezing)

### Taiwan made PU tube

Model	ID×OD (mm)	Each roll (m)	Available color
<b>TPU0420</b>	2×4	200	B, BU, O, T
<b>TPU0425</b>	2.5×4	200	B, BU, O, G, Y, T
<b>TPU0503</b>	3×5	200	B, BU, O, G, Y, T
<b>TPU0604</b>	4×6	200	B, BU, O, G, Y, T
<b>TPU0850</b>	5×8	100	B, BU, O, G, Y, T
<b>TPU0806</b>	6×8	100	B, BU, O, G, Y, T
<b>TPU0906</b>	6.5×9.5	200	B, BU, O, G, Y, T
<b>TPU1065</b>	6.5×10.0	100	B, BU, O, G, Y, T
<b>TPU1108</b>	8.0×11	100	B, BU, O, G, Y, T
<b>TPU1208</b>	8.0×12	100	B, BU, O, G, Y, T
<b>TPU1296</b>	9.6×12.7	100	B, BU, O, G, Y, T
<b>TPU1613</b>	13×16	100	B, BU, O, G, Y, T

Available color

● Black(B), ● Blue(BU), ● Orange(O), ● Green(G), ● Yellow(Y), ○ Transparent(T)

### Order example

**TPU0503 – 200 – B**

