


MAR710 series Stainless steel # 316

PRESSURE REGULATOR



mindman



Feature

- The material of body, adjust mechanism, screw & bolt, bottom cover and inside part is AISI 316L.
- Applications include marine environments, oil and gas production, chemicals and food processing, medical analysis etc.

Specification

Model	MAR710	
Bore No.	25A	40A
Port size	1	1 1/2
Medium	Air	
Max. operating pressure	3 MPa	
Regulated pressure range (*)	Standard : 0.1~1 MPa	
	Optional : 0.17~1.75 MPa	
Ambient temperature	-20~+80°C (No freezing)	
Flow rate (*)	13560 L/min	14160 L/min
Attachment	Pressure gauge (PG-50S2), Bracket (B1-MAR710)	
Weight	4600 g	

Order example

MAR710 — 40A — ☐ C B — ☐

MODEL PORT SIZE
25A: 1
40A: 1 1/2

Blank: Without
C: External pressure gauge (PG-50S2)





PORT THREAD
Blank: Rc thread
G: G thread
NPT: NPT thread

ADJUSTABLE PRESS. RANGE
Blank: 0.1~1 MPa
17K: 0.17~1.75 MPa (*)

BRACKET
Blank: Without bracket
B: L type bracket

* 17K only for hex head screw

17K hex head



Flow feature

