


MAF402 series

AIR UNIT (FILTER)



Symbol



Specification

Model	MAF402		
Bore No.	10A	15A	20A
Port size	3/8	1/2	3/4
Medium	Air		
Operating pressure range (*)	0.05~1 MPa		
Proof pressure	1.5 MPa		
Ambient temperature	- 5~+60°C (No freezing)		
Filter element	Standard: 40μm, Option: 5, 20μm		
Weight	454 g		

* Standard unit contains semi-auto-drain function when operating pressure below 0.05 MPa.

Order example

