

MGT* 外觀尺寸 $\phi 50, \phi 63$


雙導桿氣壓缸



MGTB (滑動軸承—高級銅合金)

MGTU (線性滾珠軸承)

$\phi 50, \phi 63$



代號 內徑	A	A1	B	B1	C	E	F	G	H	J	K	L	L1	N	R	S	T	U	V	W
50	141	135	70	65	150	100	46.5	23	85	7.5	19	216	110	M8x1.25 貫通	104	20	20	81	ø9, ø14(深)8.5	94
63	156	150	80	75	165	105	56.5	28	100	5	19	230	125	M8x1.25 貫通	119	20	20	96	ø9, ø14(深)8.5	94

荷重圖表

最大容許負荷

MGTB, MGTU $\phi 50, \phi 63$

