MAF411 series Stainless steel # 316

AIR UNIT (FILTER)

mindman



Feature

- The model designed as a high-performance product for instrument air used in corrosive atmospheres. Outside metal part is AISI 316L.
- Applications include marine environments, oil and gas production, chemicals and food processing, medical analysis etc.

Specification


Model	MAF411	
Bore No.	15A	20A
Port size	1/2	3/4
Medium	Air	
Max. operating perssure	3 MPa	
Ambient temperature	–20~+80°C (No freezing)	
Filter element (*)	25μm	
Flow rate (*)	5350 L/min	6850 L/min
Attachment	Bracket (B1-MAF311)	
Drain capacity	100 cm^3	
Weight	1600 g	


* Flow is at inlet pressure 1 MPa, outlet pressure 0.6 MPa with pressure drop △ 0.1 MPa.
* If your inquiry is not included in above table, please kindly contact us.

Order example

MAF411 – 20A – □ – □

MODEL
PORT SIZE
15A: 1/2
20A: 3/4
BRACKET
Blank: Without bracket
B: L type bracket
PORT THREAD
Blank: Rc thread
G: G thread
NPT: NPT thread





Flow feature

