




Code Tubr I.D.	A	B	C	D	E	F	G	H	H1	I	J	K	L	M	N	O	P
16	108	58	47	62	38	15	38	50	48	M5×7dp,P.C.D38	33	8	M5×8dp	14	26	15.5	Rc1/8
20	128	68	55	78	47	15	46	62.5	60	M6×7dp,P.C.D46	38	10	M6×8dp	17	27	18.5	Rc1/8
25	135.5	77	58.5	84	55	15.5	48	67	65	M6×9dp,P.C.D48	41.5	10	M6×8dp	17	37	20	Rc1/8
32	170	94	69.5	106	68	20	55	85	83	M8×10dp,P.C.D55	49.5	12.5	M8×8.5dp	20	47	24	Rc1/8



Code Tubr I.D.	Q	S1	S2	T	U	V	W1
16	8 $^{+0.03}_{-0}$ (wide)×3.3dp	6	17 (H7)×2.5dp	24 (H7)×3dp	2- ϕ 6.8 thru, ϕ 11×6.5dp, M8×12dp(sink)	M3×4dp	M10×1.0
20	10 $^{+0.03}_{-0}$ (wide)×3.5dp	10	22 (H7)×2.5dp	32 (H7)×3dp	2- ϕ 8.6 thru, ϕ 14×8.5dp, M10×15dp(sink)	M4×6dp	M12×1.0
25	12 $^{+0.03}_{-0}$ (wide)×4dp	13	22 (H7)×3dp	32 (H7)×3.7dp	2- ϕ 8.6 thru, ϕ 14×8.5dp, M10×15dp(sink)	M4×5dp	M14×1.5
32	12 $^{+0.03}_{-0}$ (wide)×5dp	13	26 (H7)×3dp	35 (H7)×4.7dp	2- ϕ 10.5 thru, ϕ 18×10.5dp, M12×18dp(sink)	M5×5dp	M20×1.5

Code Tubr I.D.	W2	W3	X1	X2	Y1	Y2	Y3	Y4
16	27	26	7	17	MDSC-1008-3-N	29.5	—	—
20	23	32	8	19	MDSC-1210-3-N	36	—	—
25	36	37	8	22	MDSC-1412BS-3-N	33	MDFC-1410-N	61.5
32	43	47	12	30	MDSC-2020-3-N	72	MDFC-2016-N	78

Flange rod type

$\phi 16$

$\phi 20 \sim \phi 32$



Code Tube I.D.	A	E	J	K	L	N
16	64.5	31.5	17.5	-	-	-
20	78	40	23	16	9.2	8
25	81.5	40	23	20	11.2	10
32	109.5	60	40	20	13.2	12

※ Other dimensions are the same as standard type.