

Features

- Opening / closing stroke move than twice the standard (MCHG2).
- Interchangeable with MCHG2 in mounting.
- Magnetic as standard.

Order example

MCHG2L – 16 M

MODEL

TUBE I.D.

16
25
32
40
50
63
80

M: Magnet

* Magnetic as standard.

Sensor switch

RT × 1

NUMBER of
AUTO SWITCH

AUTO SWITCH TYPE

perpendicular	in-line		style
RTV	RT	RK	Reed switch
RTNV	RTN	RKN	NPN
RTPV	RTP	RKP	PNP

for ø32~ø80


for ø16, ø25

* RT specification, please refer to page 5-15,16.




Specification

Model	MCHG2L								
Acting type	Double acting								
Tube I.D. (mm)	16	25	32	40	50	63	80		
Stroke (mm)	10	12	16	20	28	32	40		
Medium	Air								
Operating pressure	0.2~0.6 MPa								
Ambient temperature	-10~+60°C (No freezing)								
Repeatability	±0.01 mm								
Max. operating frequency (c.p.m)	120			60			30		
Lubrication	Cylinder	Not required							
	Lever	Grease (Actuation at)							
Effective gripping force N (lbf) at (0.5 MPa) (*)	External	14(3.1)	42(9.4)	74(16.6)	118(26.5)	187(42)	335(75)	500(112)	
	Internal	16(3.6)	47(10.6)	82(18.4)	130(29)	204(46)	359(81)	525(118)	
Weight (g)	100	190	373	600	930	1850	2880		

* Open and closed diameter values apply for external gripping of work pieces.




Auto switch mounting groove position (2 places) Mounting hole counter bore dimensions




Note. The counter bore configuration differs only for the mounting hole section between the auto switch mounting grooves.

Code Tube I.D.	A	AB	AC	B	C	D	E	G	H	I	J	K	M	MA	MB	MM	MR	N1	P	PP	Q	QA	QQ
16	30	30.6	40	43.5	28	30.5	7	8	5h9 ⁺⁰ _{-0.030}	6	2	12.5	4	6.5	5	3.4	25	14	18.5	23.5	4	5	M3×0.5
25	42	42.6	52	49	31.5	34.2	7.8	13	6h9 ⁺⁰ _{-0.030}	8	3	16	4.5	8	8	4.5	34	16.5	24	30	6	6	M3×0.5

Code Tube I.D.	R	TT	UA	UU	X	XA	XX	Y	YA	YY	Z	ZA	ZZ
16	12	M3×0.5	6	M3×0.5	12.5	2	2H9 ^{+0.025} ₋₀	11	2	2H9 ^{+0.025} ₋₀	3	1.5	17H9 ^{+0.043} ₋₀
25	19	M5×0.8	6	M4×0.7	17	3	3H9 ^{+0.025} ₋₀	14.5	3	3H9 ^{+0.025} ₋₀	5	1.5	26H9 ^{+0.052} ₋₀



Auto switch mounting groove position (2 places)



Code Tube I.D.	A	AB	AC	B	C	D	E	F	G	H	I	J	K	L	M	MA	MB	MM	MR	N1	N2	O	P	PP	Q
32	52	52.6	72	58	35.5	39.6	6	2	16	8h9 ⁺⁰ _{-0.036}	11	4.5	23	2H9 ^{+0.025} ₋₀	5	8	8	4.5	44	20	8	10.4	34	42	9
40	62	62.6	82	64	38.5	42.5	8	2	18	8h9 ⁺⁰ _{-0.036}	12	4.5	25.5	3H9 ^{+0.025} ₋₀	7	9.5	11	5.5	53	22	9	13.5	37.5	47.5	9
50	70	70.6	104	77.5	46.5	51.3	7	2	20	10h9 ⁺⁰ _{-0.036}	14	5	32	4H9 ^{+0.030} ₋₀	8	9.5	14.5	5.5	62	29	9	17.7	46	60	10
63	86	86.6	120	89	51	58.5	7.5	3	26	12h9 ⁺⁰ _{-0.043}	17	5.5	37	6H9 ^{+0.030} ₋₀	10	11	17	6.6	76	30.5	12	19.5	54	70	11
80	106	106.6	140	116	70	78.5	9	4	30	14h9 ⁺⁰ _{-0.043}	20	6	40.5	8H9 ^{+0.036} ₋₀	11	11	23	6.6	95	37.5	14	23.5	60.5	80.5	12

Code Tube I.D.	QA	QQ	R	T	TT	UA	UU	X	XA	XX	Y	YA	YY	Z	ZA	ZZ
32	8	M4×0.7	24	3	M5×0.8	6	M4×0.7	22	3	3H9 ^{+0.025} ₋₀	19.5	3	3H9 ^{+0.025} ₋₀	5	2	34H9 ^{+0.062} ₋₀
40	8	M4×0.7	30	3	M5×0.8	10	M5×0.8	26.5	4	4H9 ^{+0.030} ₋₀	23.5	4	4H9 ^{+0.030} ₋₀	6	2	42H9 ^{+0.062} ₋₀
50	10	M5×0.8	32	3	M5×0.8	10	M5×0.8	31	4	4H9 ^{+0.030} ₋₀	28	4	4H9 ^{+0.030} ₋₀	6	2	52H9 ^{+0.074} ₋₀
63	10	M5×0.8	40	4	M5×0.8	12	M6×1	38	5	5H9 ^{+0.030} ₋₀	34.5	5	5H9 ^{+0.030} ₋₀	7	2.5	65H9 ^{+0.074} ₋₀
80	12	M6×1	50	5	Rc1/8	12	M6×1	47.5	6	6H9 ^{+0.030} ₋₀	43.5	6	6H9 ^{+0.030} ₋₀	8	3	82H9 ^{+0.087} ₋₀