


MAF200D / M 系列


空氣調理組合 (精密過濾器)



符號



D: 0.3µm




M: 0.01µm

規格

型號	MAF200D/M	
配管口徑代號	6A	8A
配管口徑尺寸	1/8	1/4
使用流體	空氣	
使用壓力範圍 (*)	0.05~1 MPa	
耐壓力	1.5 MPa	
周圍溫度	-5~+60°C (不凍結)	
過濾精度	0.3µm, 0.01µm	
冷凝水儲留量	6.5 cm ³ , 20 cm ³ (MAF200L)	
重量	187 g, 155 g (MAF200L)	

* 壓力低於 0.05 MPa, 可自動排水。

訂購代號



流量特性圖

