

MACT500 series

AIR UNIT (F.R.L.UNIT)




Mindman



Specification

Model	MACT500	
Components	MAF500, MAR500, MAL500	
Bore No.	20A	25A
Port size	3/4	1
Medium	Air	
Operating pressure range	0.05~1 MPa	
Proof pressure	1.5 MPa	
Regulated pressure range	0.05~0.85 MPa	
Ambient temperature	- 5~ + 60°C (No freezing)	
Filter element	40 μm	
Lubricating oil capacity	175 c.c	
Min. flow for oil drip	190 ℓ/min	
Recommended lubricating oil	Turbine oil ISO-VG32	
Attachment	Pressure gauge, bracket	
Weight	3800 g	

Symbol



※ Standard unit contains semi-auto-drain function when operating pressure below 0.05 MPa.

Order example

MACT500 – 20A – D – □

MODEL

BORE SIZE
20A: 3/4
25A: 1

D: Auto drain valve
(YD401)

PORT THREAD
Blank: Rc thread
G: G thread
NPT: NPT thread

Flow feature

