MHPSC series

NO CONTACT TRANSFER






Bernouilli effect Air Exhaust Object Exhaust

The principle of these prehension is based on the exploitation of the Bernouilli effect. A positive pressure is applied through form adequate (Insert + curve). The exhaust of this air goes through of low pressure and gets a vacuum aspiring any kind of object.

Order example




Specification


Model	MHPSC						
Size	20	30	40	60			
Port size	М3	M5	M5	M5			
Medium	Dry air filter 40µ						
Consumption in air (*) I/min	100	100	110	210			
Lifting force (*) in N	0.9	1.3	2	6			
Operating pressure range	0.2~0.7 MPa						
Ambient temperature	+5~+60°C						
Level of noise	25dB						
Material	Aluminum A5056 and stainless steel						
Weight	10 g	30 g	54 g	124 g			

^{*} Indicative value for sizes 20 and 30: Pressure of 0.5 MPa with an air supply by tube ø2,5x4 length: 1m. for sizes 40 and 60: Pressure of 0.5 MPa with an air supply by tubeø4x6 length: 1m.

Lifting force



Consumption in air






MHPSC Application examples


NO CONTACT TRANSFER




■ Transfer disc, CD, DVD




■ Pick up circuit board




■ Eggs or fruits packaging



■ Glass sheet leave (no mark on the face)




■ Paper sheet with small thickness. (Transfer sheet by sheet)



■ Handling of object on concave or convex surface. Handling of biscuit, wafer, paste, pastry making, membrane, sponge, textile, mirror, etc...









MHPSC Dimensions






MHPSC-40CD Using for CD ro DVD (with centering part)






MHPSC-40U


Smooth surface with treatment







MHPSC-**CI

Prehensor with three points of contact







Code Model	Α	В	C	D	Е	G	Н	J
20	2.2	16.6	14	12	20	M4x5	МЗ	Plug M3
30	3.4	24.4	22	17	30	M4x10	M5	Plug M5
40	5.3	32.5	32	17	40	M4x10	M5	Plug M5
60	5.3	48.8	44	17	60	M4x10	M5	Plug M5

