MXCD series

∕∕∕indman

2/2 WAY N.C. DIAPHRAGM TYPE SOLENOID VALVE



Caution

- In order to prolong operating life, it is better to allocate pipe horizontally and coil to face upward.
- Voltage drop range is within ± 10%.
- Pressure of voltage DC is 70% of voltage AC only.
- Combined diaphragm design assures no breaking.
- Fluid temp.: -10~+80°C (Naphtha 120°C)


Not for fluid of

- Liquid when heat, solid when cool.
- · Corrosive fluid.
- Viscosity over 50 cst.

Weight

Model	MXCD					
Code	8	10	12			
N.W (kg)	0.61	0.6	0.59			

Order example



G: Square DIN *2. Note, if diesel fuel or gasoline.

Specification

Model MXCD: Forged brass body, for water, air, naphtha.									
Code Seal (Port size) Mat'l	Orifice mm	Max. operating pressure diff. (0~bar)							
		Water	Air	Naphtha	acid & alkali (S.Steel)	CV			
8(1/4")	\ \ \	11	0.3~20	0.3~20	0.3~20	0.2~20	2.4		
10(3/8")		12	0.3~20	0.3~20	0.3~20	0.2~20	2.7		
12(1/2")		12	0.3~20	0.3~20	0.3~20	0.2~20	2.7		

