## **RLZ** series LINEAR POSITION SENSOR





#### **Order example**



#### Applicable



#### Features

- Repeatability ± 0.01 mm
- Analog output invertible (0~10V↔10~0V)(4~20mA↔20~4mA)
- Sampling time ≤ 0.3 ms
- Voltage / current output switchable
- Freely set measuring range

#### **Specification**

	Model	RLZ								
Me	asuring range	40±1 mm								
Po	wer supply voltage	15 ~ 30 V DC, Ripple ( P-P ) ≤ 10 %								
Cu	rrent consumption	≤ 15 mA ( with no load )								
Dis	placement resolution *1	0.001 mm								
Lin	earity error *1	± 0.2 mm @ 25 °C								
Re	peatability *1	± 0.01 mm @ 25 °C								
Sa	mpling time	≤ 0.3 ms								
An ou	alog voltage tput *2	Voltage Output : 0 ~ 10 V Min. Load Impedance : 2 KΩ Linearity : ± 0.05 % F.S. @ 25 °C Sensitivity : 0.25 mV/μm								
An ou	alog current tput *2	Current Output : 4 ~ 20 mA Max. Load Impedance : 500 Ω Linearity : ± 0.05 % F.S. @ 25 °C Sensitivity : 0.4 μA/μm								
Ma	gnetic field strength*1,3	20 ~ 200 Gauss								
	Enclosure	IP69 IEC 60529								
п	Ambient temp. Range	Operation : 0 ~ 50 °C, Storage : -10 ~ 60 °C (No condensation or freezing)								
nviro	Ambient humidity range	Operation / Storage : 35 ~ 85 % RH ( No condensation)								
nme	Withstand voltage	1000 V AC in 1-min ( between case and lead wire )								
Int	Insulation resistance	$\geq 50~\text{M}\Omega$ ( at 500 V DC, between case and lead wire )								
	Shock *4	30 G								
	Vibration *5	10 G								
Le	ad wire	ø2.9 PUR - 26 AWG ( 0.15mm <sup>2</sup> ) - 3 cores								
Pro	otection circuit	Power source reverse polarity, Surge suppression								
We	ight (with 2M lead wire)	Approx. 33 g (C type), Approx. 37 g (T type)								
Co	nnect diagram	(Brown) (Brown) (White) (White) (Blue)								

\*1. Measuring standard target : ø15.5 × ø8 × 5t ( The movement of anisotropy rubber magnet and piston are from same direction. )

- \*2. Only one of analog output can be selected while setting.
- \*3. The difference of magnetism, environment, and interference of magnetic field can cause the deviation of measurement.
- \*4. Sin wave / X , Y , Z 3 directions / 3 times each direction / 11 ms each time. \*5. Double amplitude 1.5 mm or 10 G / 10 Hz  $\sim$  55 Hz  $\sim$  10 Hz ( Sweep 1 min ) /
- X, Y, Z 3 directions / 2 hours each time.
- \*6. Caution for safety please refer to page10-3.



**RLZ** Applicable cylinder

#### LINEAR POSITION SENSOR

#### **∆** Caution

\* The repeatibility of sensor will be affected by the operational condition and environment.

\* Avoid piston and magnet of cylinder spin to cause inaccuracy.

\* To ensure good repeatability, models marked with 
require special specification orders.

	Model	Stroke Tube I.D.	5	10	15	20	25	30	40	50	60	80	100	150	200	250	300	400	500
Mini	MCMJP (C type)	10					•	•											
		16					۲	۲	۲										
Guide cylinder	MCGI (T type)	20,25				۲	۲	۲	۲	۲	۲	۲	۲						
		32,40			۲	۲	۲	۲	۲	۲	۲	۲	۲	۲	۲				
		50			۲	۲	۲	۲	۲	۲	۲	۲	۲	۲	۲	۲	۲		
		63,80,100		۲	۲	۲	۲	۲	۲	۲	۲	۲	۲	۲	۲	۲	۲		
	MCDJ (C type)	6				۲		۲	۲	۲									
		10		۲		۲		۲		۲									
	Model	Tube I.D.	6	8	10	12	16	20	25	32	40	50	63	80	100	125	160	200	300
Cylinder	MCKQI2 (T type)									۲	۲								
	MGTB/U/X *1 (T type)									۲	۲								
ਸ	MCRJ-S	90°																	
otar	(C type)	180°	•	•															
ry actuat	MCRQ (C type)					۲	•	•	•	•		İ							
	MCRQ-S	90°					•	•	•										
9	(C type)	180°					•	•	•										
Gripper	MCHD (C type) *2	Short				۲	۲	۲											
		Medium		•*3		۲	۲	۲											
		Long		۲		۲	۲	۲											
	MCHU (C type)					•	•	•											
	MCHS (C															•	•	•	
	MCHX (C type)				۲		۲	۲	۲	۲	۲								
	MCHY (C					۲	۲	۲											

\*1. The cylinders for MGTB/U/X are MCKQI2.

\*2. MCHD must use single magnet specification.

\*3. Please install the sensor in the middle of MCHD-8 medium stroke (as shown in Figure 2).

\*4. The built-in magnets must be glued except \*2.

\*5. RLZ is also applicable to the models marked with () in standard specification if good repeatability is not required. (except MCHD and MCRQ-12 series)

\*6. Please contact us if required models not found in the table

### Order example of special cylinder



Suitable for RLZ series \* Special cylinder, please contact us

#### **Precautions** (Read before installing)

- Be sure to tighten within the recommended tightening torque when mounting the actuator position sensor.
- According to the installation condition, the cylinder may not operate even when mounted appropriately. If the sensor doesn't work, try following solutions:1. Restart the power. 2. Operate the cylinder for several times.
- Turn off power before connecting wiring. Wrong wiring or short circuit will damage and / or cause malfunction.











Special cylinder
 250 300 400 500

Standard cylinder

then tighten the screw by hexagon wrench 2.0 mm with tightening

torque 0.2 ~ 0.4 Nm

(as shown in Figure 1)

# **RLZ** Dimensions LINEAR POSITION SENSOR



### Wiring of the QD

• 3 wire QD wiring



1 Brown(+) 3 Blue(-) 4 White (analog output)

#### **Analog output function**

- Analog voltage / current output can be switched.
- Analog output can be inverted.



# Information indicator LED color description

Please ensure that the required measurement range of the cylinder is within the measurement range of RLZ.



G (Green)	Within the setting range					
N (Non)	Within the measuring range, but outside the setting range.					
R (Red)	Outside the measuring range					

Dimensions RLZ-C

C type











9.5

4.8









19.5

ø