



Features




User manual




Features

- 65K Full color TFT-LCD display
- 4 Directions display for easy setup and viewing
- Response time < 0.3 S
- Switchable analog input/output and switch output
- RS485 Modbus RTU
- Applicable industries: Semiconductor, Laser Welding, IoT

Panel description





Order example



Dimensions / Pin No.

Pin	Description
1	+ 24V DC
2	Analog input 0 ~ 10V or 4 ~ 20mA
3	RS485 A+
4	Analog output 1 ~ 5V or 0 ~ 10V or 4 ~ 20mA
5	Not Used
6	Switch output NPN or PNP
7	RS485 B-
8	0V



Port size: Rc1/8"

* Cable: 20 ~ 24AWG
 * Connector model : 0156-1C08-BK (Brand : Dinkle)
 * Please use a 2.5 mm flat screwdriver.

Specifications

Model		MFCB		
Valve type		Proportional solenoid valve normally closed when power off (N.C.)		
Fluid		Non-corrosive / Non-flammable gas: Dry air, N ₂ , CO ₂ , Ar		
Flow rate	Air, N ₂ , Ar	200 L/min		
	CO ₂	100 L/min		
Display		1.3" 65K Full color TFT-LCD display		
Flow control	Display range		0 ~ 100 % F.S.	
	Minimum Setting scale	LPM	1 L/min	
CFM *1		1 ft ³ /min		
Pressure	Display range		-101 ~ 1000 kPa	
	Minimum Setting scale	kPa	1	
		MPa	0.001	
		kgf/cm ²	0.01	
		bar	0.01	
psi	0.1			
Temperature	Display range		0~50°C / 32~122 °F (Non-freezing)	
	Minimum Setting scale	°C	0.1	
°F		0.1		
Humidity	Display range		10 ~ 90% RH	
	Minimum setting scale		0.1 % RH	
Accuracy	Flow control *2	Control accuracy		± 3% F.S.
		Repeatability		± 1% F.S.
		Temp. characteristic *3		± 5% F.S.
		Pressure characteristic *4		± 2% F.S.
	Pressure	Indicator accuracy		± 2% F.S.
		Repeatability		± 0.1% F.S.
	Temperature	Indicator accuracy		± 0.2 °C
Humidity	Repeatability		± 0.25% RH	
Analog input and output		± 1 % F.S.		
Switch output *5	Switch output		NPN open collector output Max. load current : 200 mA Max. supply voltage : 24 V DC Voltage drop : ≤ 1.5 V	PNP open collector output Max. load current : 200 mA Max. supply voltage : 24 V DC Voltage drop : ≤ 1.5 V
	Output mode	Flow control	Tolerance mode, error mode	
	Response time	Flow control	0.3 s (typ.) to the setting ± 2 % F.S.	
Analog input and output *5		DC 1 ~ 5 V, 0 ~ 10 V, 4 ~ 20 mA		
Communication interface		RS485 Modbus RTU		
Power	Power supply voltage		DC 24 V	
	Current consumption		≤ 300 mA	
Environment	Working pressure range		350 ~ 500 kPa	
	Standard differential pressure		350 kPa (Inlet pressure : 350 kPa, Outlet pressure: 0 kPa)	
	Withstand pressure		1000 kPa	
	Enclosure		IP40	
	Working fluid temp.		0 ~ 50 °C (No condensation or freezing)	
	Ambient temp. range		Operation : 0 ~ 50 °C ; Storage : -10 ~ 60 °C (No condensation or freezing)	
Ambient humidity range		Operation / Storage: 35 ~ 85 % R.H. (No condensation)		
Accessories		2M cable		
Weight		685 g		

*1. When the display unit is CFM or ft³, the actual flow is the display value×10⁻².

*2. Based on dry compressed air and measured by our standard flow meter as a reference for other gas.

*3. Benchmark : 25 °C (Temperature range: 0 ~ 50 °C)

*4. Benchmark : Inlet pressure : 350 kPa,
Outlet pressure : 1 atmospheric pressure, 25 °C

*5. Switchable, please follow the manual for setup.