

Vacuum Pad

Static dissipative R69 type


To protect electronic devices from ESD (Electro-Static Discharge)

NEW



Surface resistance 10^6 to $10^9 \Omega$

Surface resistance suitable for ESD (Electro-Static Discharge) control.



For suction conveyance of IC chips, PCB and electronic components.




Model Designation (Example)



(1) Vacuum Pad

(1) Pad size

Code		4	6	8	10	15	20	25	30	40	50	4 × 20	4 × 30	8 × 30
Pad size (mm) * Oval pad:A×B		φ4	φ6	φ8	φ10	φ15	φ20	φ25	φ30	φ40	φ50			
Pad type	Standard	Small	✓	—	—	—	—	—	—	—	—	—	—	—
		General	✓	✓	✓	✓	✓	✓	✓	✓	✓	—	—	—
	Bellows		—	✓	✓	✓	✓	—	✓	—	—	—	—	—
	Soft		✓	—	—	—	—	—	—	—	—	—	—	—
	Soft bellows		—	✓	✓	—	—	—	—	—	—	—	—	—
	Skidproof		—	—	—	✓	✓	—	✓	✓	—	—	—	—
	Ultrathin		—	—	✓	✓	—	—	—	—	—	—	—	—
	Oval		—	—	—	—	—	—	—	—	—	✓	✓	✓

(3) Pad type

Code	RM	R	B	L	LB	K	P	E
Pad type	Standard (Small)	Standard (General)	Bellows	Soft	Sof bellows	Skidproof	Ultrathin	Oval
								

(4) Pad material

Code	SE-R69
Rubber material	Static dissipative silicone
Surface resistance (Ω)	10 ⁶ to 10 ⁹
Surface hardness	HS50

*Vacuum Pad with Holder type is also available.

Model code

Standard



Small

Model code

VP4RMSE-R69

Skidproof



Model code

VP10KSE-R69

VP20KSE-R69

VP30KSE-R69

VP40KSE-R69

Standard



General

Model code

VP4RSE-R69

VP6RSE-R69

VP8RSE-R69

VP10RSE-R69

VP15RSE-R69

VP20RSE-R69

VP25RSE-R69

VP30RSE-R69

VP40RSE-R69

VP50RSE-R69

Ultrathin



Model code

VP8PSE-R69

VP10PSE-R69

VP15PSE-R69

Bellows



Model code

VP6BSE-R69

VP8BSE-R69

VP10BSE-R69

VP15BSE-R69

VP20BSE-R69

VP30BSE-R69

Oval



Model code

VP4x20ESE-R69

VP4x30ESE-R69

VP8x30ESE-R69

Soft



Model code

VP4LSE-R69

Soft bellows



Model code

VP6LBSE-R69

VP8LBSE-R69

VP10LBSE-R69

Related product

Vacuum Pad Holder

Spring type, Direct mount Low dust emission holder **VPLFG**

Vacuum Pad Holder with low dust emission.

Built-in special bush provides low sliding and low dust emission.

No need for individual piping, reducing the setup time.

Space-saving Holder that allows piping with a manifold block.


3 mm and 6 mm are available for the stroke option.

Optional cap nut is also available.

The holder body can be fixed with a manifold block by tightening with the cap nut.

Non-rotating shaft prevents workpiece misalignment during conveyance

Non-rotating shaft can be selected depending on the application.



OVERSEAS SALES DEPARTMENT (HQ)
PISCO TAIWAN CO., LTD.
NIHON PISCO TAIWAN CO., LTD.
PISCO USA, INC.
PISCO KOREA CO., LTD.
PISCO VIETNAM CO., LTD.
PISCO CHINA CO., LTD.
NIHON PISCO CO., LTD. BANGKOK REPRESENTATIVE OFFICE

TEL. +81-(0)265-76-7751
TEL. +886-(0)6-726-5762
TEL. +886-(0)6-726-4520
TEL. +1-630-993-3500
TEL. +82-32-327-9795
TEL. +84-24-3200-0310
TEL. +86-21-3123-2755
TEL. +66-(0)2-612-7366

+81-(0)265-76-3305
+886-(0)6-726-5752
+886-(0)6-726-1526

+82-32-327-0385
+84-24-3200-5331

+66-(0)2-612-7399

e-mail. intl@pisco.co.jp
e-mail. P8638@ms16.hinet.net

e-mail. info@pisco.com
e-mail. webmaster@pisco.co.kr
e-mail. piscovn@pisco-vn.com
e-mail. info@pisco-china.com
e-mail. piscobkk@pisco.co.jp

 <https://www.pisco.co.jp/en>