


SLOT-TYPE PHOTOMICROSENSOR






Order example



Dimension



1	+	Brown	8~24V DC
2	1	Black	Output 1 (NC)
3	2	White	Output 2 (NO)
4	-	Blue	GND (0V)

Specification

Model	RLT-N	RLT-P
Sensing distance	6 mm (slot width)	
Sensing object	Opaque: 2×0.8mm min.	
Differential distance	0.025 mm max.	
Light source (Peak wavelength)	Infrared LED with a peak wavelength of 940 mm	
Indicator	Ligh indicator (Red LED)	
Supply voltage	8~24 VDC ± 10%, ripple (p-p): 10% max.	
Current consumption	20 mA max.	
Control output	Load power supply voltage: 8~24 VDC Load current: 50 mA max Off-stagte current: 0.5 mA max. 50 mA load current with a residual voltage of 1.0 Vmax. 19 mA load current with a residual voltage of 0.4V max.	
Protection circuit	Power supply reverse polarty protection; output reverse polarity protection: overcurrent protection	
Response frequency	1 kHz min. (2 kHz average)	
Ambient illumination	1000 lx max. with fluorescent light on the surface of the receiver	
Ambient temperature	Operating: -25~55°C, Storage: -30~80°C (with no icing or condensation)	
Ambient humidity range	Operating: 5~85% RH (with no icing o	, ,
Vibration resistance (Destruction)		e amplitude (15-min periods, K, Y and Z directions
Shock resistance (Destruction)	Destruction: 500 m/s2 for direc	
Degree of protection	IEC 60529 IP50	
Connecting method	Connector	
Case material	Acrylonitrile butadiene styrene (ABS)	
Wight (Packed state)	Appro	ox. 3g

^{* 1.} Caution for safety please refer to page 7-8~9.

Connect diagram

NPN NO/NC	PNP NO/NC	
Power supply (+) (Brown) Output 1 (Black) (NC) Load Output 2 (White) (NO) Load VDC GND (-) (Blue)	Power supply (+) (Blown) Output 1 (Black) (NC) Output 2 (White) (NO) Coad VDC (ND (-) (Blue) Coad	

Assembling style

Cylinder type	Mounting
METFB, METS2 MESH2, MESS2	

