


TPG60 series

PNEUMATIC GRINDER – LINKAGE COMPLIANT TOOL



mindman

Specification

Model	TPG60
Compliant stroke (mm)	8 (One-sided)
Compliant force (N)	20~50
Rated operate pressure (MPa)	Compliant: 0.2~0.5 Spindle: 0.6
Air consumption (LPM)	Compliant: Neglectable Spindle: 150
Recomm. lubricating oil (*1)	Turbine oil ISO-VG32
Oscillating speed (RPM)	18000
Collet size (inch)	3 (Grinding wheel, sanding disc)
Weight (kg)	2.4

*1. Only for the pneumatic spindle. Adjust oil quantity as needed.

*2. Do not disassemble this product yourself. For repairs or replacement of consumables, please contact our sales.




Manual



Model selection



Caution for safety
(Read before installing)



(Grinding wheel not included,
must be purchased separately)

Feature







Good for large burrs on curved edges

- Minimal compliance force and lightweight grinding. Capable of performing multiple functions based on different sanding disc installations.
- Applicable material: Cast iron, stainless steel, wood, aluminum, copper, steel, plastic, composite materials

Order example

TPG60

MODEL



No.	Part	Qty	Note
1	Pneumatic grinder	1	
2	Compliant linkage	1	
3	Tool body	1	
4	Pneumatic grinder air supply connector	1	6 mm fitting
5	Air pressure connector	1	6 mm fitting
6	Grinding wheel air pressure connector	1	6 mm fitting
7	Grinding wheel, sandpaper disc	0	Purchased separately