


# COMPACT CYLINDER



	<b>COMPACT CYLINDER</b>	
<b>MCJA</b>	ø12~ø100.....	2-2
	Multiple Position .....	2-14
	Back to Back Type .....	2-17
<b>MCJQ2</b>	ø12~ø25.....	2-20
<b>F MCJQ</b>	ø12~ø100 .....	2-23
	Multiple Position .....	2-48
<b>MCKJQ</b>	ø12~ø40 No Rotation .....	2-53
<b>MCJI</b>	ø20~ø100.....	2-59
	Multiple Position .....	2-67
	<b>PLATE OVAL CYLINDER</b>	
<b>MCJU</b>	ø25~ø63.....	2-70
	<b>MULTI-MOUNT CYLINDER</b>	
<b>F MCFA</b>	ø6~ø32 .....	2-76
<b>F MCFB</b>	ø6~ø20.....	2-82

**F Fast delivery (11 & 12 style)**

Our goal is to achieve 3-day lead time, if there is stock of component set. For more information, please go to our [MINDMAN website \(www.mindman.com.tw\)](http://www.mindman.com.tw) and click on the "Component Set Inventory" button.



Special spec




Rod end shape



Technical data






Caution for safety  
(Read before installing)



### Features

- Ultra Compact, light weight and space saving cylinder.
- Wide range of bore sizes and strokes (12mm~100mm).
- Single and double acting available.
- Ideal for use in machinery where space is limited and incorporating sensor groove which enables flush fitting of sensors.

### Specification

Model	MCJA									
Acting type	Double acting / Single acting			Double acting						
Tube I.D. (mm)	12	16	20	25	32	40	50	63	80	100
Port size	M5×0.8			Rc1/8	Rc1/4	Rc3/8				
Medium	Air									
Operating pressure range (MPa)	Double acting		0.05~1	0.03~1	0.02~1					
	Single acting		0.2~1	0.15~1	0.1~1	—				
Proof pressure	1.5 MPa									
Ambient temperature	-5°C~+60°C (No freezing)									
Available speed range	50~500 mm/sec									
Sensor switch (*)	RCE  , RCE1  , RDEP 									

\* RDEP only for tube I.D. ø12~ø50.

### Order example

MCJA — 12 — 40 — 25 M — □

MODEL

TUBE I.D.

STROKE

M: Magnet

PORT THREAD

- 1: Single rod  
2: Double rod













Blank: M5×0.8  
(for ø12~ø25)

Blank: Rc thread

G: G thread

NPT: NPT thread  
(for ø32~ø100)

STYLE

Code	Symbol	Description
1 1		Double acting / Male thread
1 2		Double acting / Female thread
1 3		Single acting / Normally extended male thread
1 4		Single acting / Normally extended female thread
1 5		Single acting / Normally returned male thread
1 6		Single acting / Normally returned female thread
2 1		Double rod / Male thread
2 2		Double rod / Female thread
2 3		Single acting / Double rod / Male thread
2 4		Single acting / Double rod / Female thread
2 7		Double rod / Adjustable male thread Please mark "adjustable stroke" at order list
2 8		Double rod / Adjustable female thread Please mark "adjustable stroke" at order list

### Double acting – Table for standard stroke

Tube I.D.	Stroke (mm)	Max. stroke
ø12,16	5,10,15,20,25,30	300
ø20,25,32,40,50,63,80	5,10,15,20,25,30,35,40,45,50	300
ø100	5,10,15,20,25,30,35,40,45,50	125

\* Please contact us if the stroke is out of specification.


### Single acting – Table for standard stroke

Tube I.D.	Stroke (mm)
ø12,16,20,25,32,40	5,10,15,20,25,30
ø50	5,10,15,20


\* Please contact us if the stroke is out of specification.

## COMPACT CYLINDER

### ■ Rod nut

Code	NUT
Mounting Tube I.D.	
$\varnothing 12$	<b>NUT-M5x0.8x4Hx8B</b>
$\varnothing 16$	
$\varnothing 20$	<b>NUT-M6x1.0x5Hx10B</b>
$\varnothing 25$	<b>NUT-M8x1.25x5Hx13B</b>
$\varnothing 32$	<b>NUT-M10x1.25x6Hx17B</b>
$\varnothing 40$	<b>NUT-M14x1.5x8Hx22B</b>
$\varnothing 50$	<b>NUT-M18x1.5x11Hx26B</b>
$\varnothing 63$	
$\varnothing 80$	<b>NUT-M22x1.5x13Hx32B</b>
$\varnothing 100$	<b>NUT-M26x1.5x14Hx35B</b>







### ■ Flat washer kits

Code	WS
Fig Tube I.D.	
$\varnothing 12$	<b>WS-MCJA-12</b>
$\varnothing 16$	<b>WS-MCJA-16</b>
$\varnothing 20$	<b>WS-MCJA-20</b>
$\varnothing 25$	<b>WS-MCJA-25</b>
$\varnothing 32$	<b>WS-MCJA-32</b>
$\varnothing 40$	<b>WS-MCJA-40</b>
$\varnothing 50$	<b>WS-MCJA-50</b>
$\varnothing 63$	<b>WS-MCJA-63</b>
$\varnothing 80$	<b>WS-MCJA-80</b>
$\varnothing 100$	<b>WS-MCJA-100</b>

### ■ Weight


#### Cylinder weight

Unit: g


Model	Basic weight MCJA-11	Basic weight (magnet) MCJA-11	Stroke 5 mm MCJA-11	Basic weight MCJA-12	Basic weight (magnet) MCJA-12	Stroke 5 mm MCJA-12
Tube I.D.						
$\varnothing 12$	43	45	6	41	43	6
$\varnothing 16$	60	65	8	57	63	8
$\varnothing 20$	84	92	11	79	87	11
$\varnothing 25$	101	114	14	106	120	14
$\varnothing 32$	170	187	16	155	173	16
$\varnothing 40$	274	300	23	235	261	23
$\varnothing 50$	448	479	32	384	415	32
$\varnothing 63$	635	699	40	571	634	40
$\varnothing 80$	1178	1275	61	1057	1153	61
$\varnothing 100$	2058	2231	83	1806	1980	83

\* The weight is based on 5 mm stroke.

#### Accessories weight


Model	Rod nut
Tube I.D.	
$\varnothing 12$	1
$\varnothing 16$	1
$\varnothing 20$	2
$\varnothing 25$	4
$\varnothing 32$	8
$\varnothing 40$	18
$\varnothing 50$	32
$\varnothing 63$	32
$\varnothing 80$	56
$\varnothing 100$	56

### Double acting




### Single acting

#### Normally returned



### Single acting

#### Normally extended




### Seal kit

Acting type	Rod packing		Piston packing		Cover ring	Piston gasket
	Double action normally extended	Normally returned	Double acting	Single acting	Double acting single acting	Double acting single acting
Q'y	1	0	1	1	2	1
ø12	KSYR-6	—	OPA-12	OPA-12	S-12	d4×w1
ø16	KSYR-6	—	OPA-16	OPA-16	S-14	d4×w1
ø20	KSYR-8	—	OPA-20	OPA-20	S-18	d6×w1
ø25	KSYR-10	—	OPA-25	OPA-25	S-22	d8×w1
ø32	KSYR-12	—	OPA-32	OPA-32	d28×w2	S-9
ø40	KSYR-16	—	OPA-40	OPA-40	S-36	S-9
ø50	KSYR-20	—	OPA-50	OPA-50	AS-31	S-16
ø63	KSYR-20	—	OPA-63	—	AS-35	S-16
ø80	ORA-25	—	OPA-80	—	AS-41	d20×w1
ø100	SDR-30	—	OPA-100	—	S-95	S-26

### Double acting

#### (with magnet)



### Order example Component parts

Tube I.D.	Component parts
ø12	CP-MCJA-12(M)
ø16	CP-MCJA-16(M)
ø20	CP-MCJA-20(M)
ø25	CP-MCJA-25(M)
ø32	CP-MCJA-32(M)
ø40	CP-MCJA-40(M)
ø50	CP-MCJA-50(M)
ø63	CP-MCJA-63(M)
ø80	CP-MCJA-80(M)
ø100	CP-MCJA-100(M)

M: With magnet

### Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	100	Q'y	Component parts (inclusion)	Repair kits (inclusion)	
1	Head cover	Aluminum alloy										1	●		
2	Snap ring (Front end)	*2	spring steel	*2	Spring steel								1	●	
3	Cover ring	NBR										2	●	●	
4	Cushion packing	—	NBR									2	●	●	
5	Piston gasket	NBR										1	●	●	
6	Piston packing	NBR										1	●	●	
7	Piston	Aluminum alloy										1	●		
8	Screw	With magnet	Stainless steel				SCM				1	●			
		Without magnet	SCM	Stainless steel				SCM				1	●		
9	Piston rod *1	With magnet	*2	Carbon steel								1			
		Without magnet		Carbon steel								1			
10	Body	Aluminum alloy										1			
11	Rod packing	NBR										1*3	●	●	
12	Rod cover	Aluminum alloy										1	●		
13	Bush	—	Bearing alloy								1	●			
14	Magnet ring	Magnet material										1	●		
15	Spring	SWP				—				1	●				
16	Silencer	Brass				—				1	●				
17	Snap ring (Rear end)	Stainless steel				Spring steel				1	●				

\*1. When customized material is bearing steel, only two-side across flat (wrench flat) is available.

\*2. Stainless steel


\*3. Single acting / Normally returned, Q'y=0.

### Repair kits



Tube I.D.	Repair kits
ø12	PS-MCJA-12
ø16	PS-MCJA-16
ø20	PS-MCJA-20
ø25	PS-MCJA-25
ø32	PS-MCJA-32
ø40	PS-MCJA-40
ø50	PS-MCJA-50
ø63	PS-MCJA-63
ø80	PS-MCJA-80
ø100	PS-MCJA-100

### 12


$\phi 12, \phi 16$



$\phi 20, \phi 25$



$\phi 32\sim\phi 100$



### Long stroke



#### Without counter bore

With magnet type:  
The stroke length must be over 100mm.  
Without magnet type:  
The stroke length must be over 110mm.

$\phi 12, \phi 16$



$\phi 20\sim\phi 100$



Code Tube I.D.	C	D	EE	E1	E2	F	G	H	K	KK	LH	M	N	PA	PB
12	1	6	M5×0.8	16.3	23	5	11	5	3	M3×0.5×6depth	—	4.3	$\phi 6.5\times 4.5$ depth, M5×0.8×7.5depth	6.5	6
16	1.5	6	M5×0.8	19.8	28	5	11	5.5	3	M3×0.5×6depth	—	4.3	$\phi 6.5\times 4.5$ depth, M5×0.8×7.5depth	7	6.5
20	1.5	8	M5×0.8	24	—	6	15	5.5	3	M4×0.7×8depth	—	4.3	$\phi 6.5\times 4.5$ depth, M5×0.8×7.5depth	7.5	—
25	2	10	M5×0.8	28	—	8	17	6	3	M5×0.8×10depth	—	5.1	$\phi 9\times 7$ depth, M6×1.0×10depth	8	—
32	3	12	Rc1/8 (*1)	34	—	10	22	7	3	M6×1.0×12depth	48.5	5.1	$\phi 9\times 7$ depth, M6×1.0×10depth	9	—
40	3	16	Rc1/8 (*1)	40	—	14	28	7	3	M8×1.25×12depth	56.5	6.9	$\phi 10.5\times 8$ depth, M8×1.25×12depth	10	—
50	4	20	Rc1/4 (*2)	48	—	17	38	9	3	M10×1.5×15depth	70	6.9	$\phi 11\times 8.5$ depth, M8×1.25×16.5depth	10	—
63	4	20	Rc1/4 (*2)	60	—	17	40	9	3	M10×1.5×15depth	83	6.9	$\phi 11\times 8.5$ depth, M8×1.25×16.5depth	12	—
80	5	25	Rc3/8 (*3)	74	—	22	45	11	4	M14×1.5×20depth	102	10.5	$\phi 14\times 10.5$ depth, M12×1.75×12depth	13	—
100	5	30	Rc3/8 (*3)	90	—	27	55	12	4	M18×1.5×20depth	122	12.3	$\phi 18.5\times 13$ depth, M14×2×17depth	17	—

\*1. Without magnet with stroke=5mm, EE=M5×0.8

\*2. Without magnet with stroke=5mm, EE=Rc1/8

\*3. Without magnet with stroke=5mm, EE=Rc1/4


Code Tube I.D.	T	V	V1	X	Y	Z	Without magnet		Magnet	
							S	ZZ	S	ZZ
12	—	25	32	3.2	6.3	1	17	22	27	32
16	—	29	38	3.2	6.3	1	18.5	24	28.5	34
20	—	34	—	3.2	6.3	1	19.5	25	29.5	35
25	—	40	—	4.2	7.8	1	21	27	31	37
32	14	44	—	4.2	7.8	1	24.5	31.5	34.5	41.5
40	14	52	—	6.2	10.3	1.6	26	33	36	43
50	19	62	—	6.2	10.8	1.6	28	37	38	47
63	20	75	—	6.2	10.8	1.6	32	41	42	51
80	27	94	—	8.2	13.8	1.6	41	52	51	62
100	26	114	—	10.2	17.3	2	51	63	61	73

## COMPACT CYLINDER



mindman

**11**



$\phi 12, \phi 16$



$\phi 20, \phi 25$



$\phi 32\sim\phi 100$



Long stroke


Without counter bore

With magnet type:  
The stroke length must be over 100mm.  
Without magnet type:  
The stroke length must be over 110mm.

$\phi 12, \phi 16$



$\phi 20\sim\phi 100$



Code Tube I.D.	AM	AQ	B	C	D	EE	E1	E2	F	G	H1	K	L	LH	M	N	PA	PB
12	10	12	8	1	6	M5×0.8	16.3	23	5	11	17	3	4	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	6.5	6
16	10	12	8	1.5	6	M5×0.8	19.8	28	5	11	17.5	3	4	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	7	6.5
20	13	15	10	1.5	8	M5×0.8	24	—	6	15	20.5	3	5	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	7.5	—
25	15	17	13	2	10	M5×0.8	28	—	8	17	23	3	5	—	5.1	$\phi 9 \times 7$ depth, M6×1.0×10depth	8	—
32	15	18	17	3	12	Rc1/8 (*1)	34	—	10	22	25	3	6	48.5	5.1	$\phi 9 \times 7$ depth, M6×1.0×10depth	9	—
40	25	28	22	3	16	Rc1/8 (*1)	40	—	14	28	35	3	8	56.5	6.9	$\phi 10.5 \times 8$ depth, M8×1.25×12depth	10	—
50	25	28	26	4	20	Rc1/4 (*2)	48	—	17	38	37	3	11	70	6.9	$\phi 11 \times 8.5$ depth, M8×1.25×16.5depth	10	—
63	25	28	26	4	20	Rc1/4 (*2)	60	—	17	40	37	3	11	83	6.9	$\phi 11 \times 8.5$ depth, M8×1.25×16.5depth	12	—
80	30	33	32	5	25	Rc3/8 (*3)	74	—	22	45	44	4	13	102	10.5	$\phi 14 \times 10.5$ depth, M12×1.75×12depth	13	—
100	35	38	35	5	30	Rc3/8 (*3)	90	—	27	55	50	4	14	122	12.3	$\phi 18.5 \times 13$ depth, M14×2×17depth	17	—

\*1. Without magnet with stroke=5mm, EE=M5×0.8

\*2. Without magnet with stroke=5mm, EE=Rc1/8


\*3. Without magnet with stroke=5mm, EE=Rc1/4

Code Tube I.D.	Q	T	V	V1	X	Y	Z	Without magnet		Magnet	
								S	ZZ	S	ZZ
12	M5×0.8	—	25	32	3.2	6.3	1	17	34	27	44
16	M5×0.8	—	29	38	3.2	6.3	1	18.5	36	28.5	46
20	M6×1.0	—	34	—	3.2	6.3	1	19.5	40	29.5	50
25	M8×1.25	—	40	—	4.2	7.8	1	21	44	31	54
32	M10×1.25	14	44	—	4.2	7.8	1	24.5	49.5	34.5	59.5
40	M14×1.5	14	52	—	6.2	10.3	1.6	26	61	36	71
50	M18×1.5	19	62	—	6.2	10.8	1.6	28	65	38	75
63	M18×1.5	20	75	—	6.2	10.8	1.6	32	69	42	79
80	M22×1.5	27	94	—	8.2	13.8	1.6	41	85	51	95
100	M26×1.5	26	114	—	10.2	17.3	2	51	101	61	111



## COMPACT CYLINDER

### 14



$\phi 12, \phi 16$



$\phi 20, \phi 25$



$\phi 32\sim\phi 50$



**Long stroke**  
**Without counter bore**  
 With magnet type:  
 The stroke length must be over 100mm.  
 Without magnet type:  
 The stroke length must be over 110mm.

$\phi 12, \phi 16$

$\phi 20\sim\phi 50$

### Single acting – Table for standard stroke

Tube I.D.	Stroke (mm)
$\phi 12, 16, 20, 25, 32, 40$	5, 10, 15, 20, 25, 30
$\phi 50$	5, 10, 15, 20

\* Please contact us if the stroke is out of specification.

### 13

**Male thread**

Code Tube I.D.	AM	AQ	H1	Q
12	10	12	17	M5×0.8
16	10	12	17.5	M5×0.8
20	13	15	20.5	M6×1.0
25	15	17	23	M8×1.25
32	15	18	25	M10×1.25
40	25	28	35	M14×1.5
50	25	28	37	M18×1.5

Code Tube I.D.	C	D	EE	E1	E2	F	G	H	K	KK	LH	M	N	PA	PB
12	1	6	M5×0.8	16.3	23	5	11	5	3	M3×0.5×6depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	6.5	6
16	1.5	6	M5×0.8	19.8	28	5	11	5.5	3	M3×0.5×6depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	7	6.5
20	1.5	8	M5×0.8	24	—	6	15	5.5	3	M4×0.7×8depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	7.5	—
25	2	10	M5×0.8	28	—	8	17	6	3	M5×0.8×10depth	—	5.1	$\phi 9 \times 7$ depth, M6×1.0×10depth	8	—
32	3	12	Rc1/8	34	—	10	22	7	3	M6×1.0×12depth	48.5	5.1	$\phi 9 \times 7$ depth, M6×1.0×10depth	9	—
40	3	16	Rc1/8	40	—	14	28	7	3	M8×1.25×12depth	56.5	6.9	$\phi 10.5 \times 8$ depth, M8×1.25×12depth	10	—
50	4	20	Rc1/4 (*)	48	—	17	38	9	3	M10×1.5×15depth	70	6.9	$\phi 11 \times 8.5$ depth, M8×1.25×16.5depth	10	—

\* Without magnet with stroke=5mm, EE=Rc1/8

Code Tube I.D.	T	V	V1	X	Y	Z
12	—	25	32	3.2	6.3	1
16	—	29	38	3.2	6.3	1
20	—	34	—	3.2	6.3	1
25	—	40	—	4.2	7.8	1
32	14	44	—	4.2	7.8	1
40	14	52	—	6.2	10.3	1.6
50	19	62	—	6.2	10.8	1.6

Code Tube I.D.	Without magnet				Magnet			
	Stroke 5, 10		Stroke 15~30		Stroke 5, 10		Stroke 15~30	
	S	ZZ	S	ZZ	S	ZZ	S	ZZ
12	27	32	37	42	37	42	47	52
16	28.5	34	38.5	44	38.5	44	48.5	54
20	29.5	35	39.5	45	39.5	45	49.5	55
25	31	37	41	47	41	47	51	57
32	34.5	41.5	44.5	51.5	44.5	51.5	54.5	61.5
40	36	43	46	53	46	53	56	63


Code Tube I.D.	Without magnet				Magnet			
	Stroke 5~20				Stroke 5~20			
	S	ZZ	S	ZZ	S	ZZ	S	ZZ
50	28	37	38	47				

## COMPACT CYLINDER



Mindman

### 16



$\phi 12, \phi 16$



$\phi 20, \phi 25$



$\phi 32\sim\phi 50$



Long stroke


Without counter bore

With magnet type:  
The stroke length must be over 100mm.  
Without magnet type:  
The stroke length must be over 110mm.

$\phi 12, \phi 16$



$\phi 20\sim\phi 50$




### Single acting – Table for standard stroke

Tube I.D.	Stroke (mm)
$\phi 12, 16, 20, 25, 32, 40$	5, 10, 15, 20, 25, 30
$\phi 50$	5, 10, 15, 20

\* Please contact us if the stroke is out of specification.

### 15

Male thread



Code Tube I.D.	AM	AQ	H1	Q
12	10	12	17	M5×0.8
16	10	12	17.5	M5×0.8
20	13	15	20.5	M6×1.0
25	15	17	23	M8×1.25
32	15	18	25	M10×1.25
40	25	28	35	M14×1.5
50	25	28	37	M18×1.5

Code Tube I.D.	C	D	EE	E1	E2	F	G	H	K	KK	LH	M	N	PA	PB
12	1	6	M5×0.8	16.3	23	5	11	5	3	M3×0.5×6depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	6.5	6
16	1.5	6	M5×0.8	19.8	28	5	11	5.5	3	M3×0.5×6depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	7	6.5
20	1.5	8	M5×0.8	24	—	6	15	5.5	3	M4×0.7×8depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	7.5	—
25	2	10	M5×0.8	28	—	8	17	6	3	M5×0.8×10depth	—	5.1	$\phi 9 \times 7$ depth, M6×1.0×10depth	8	—
32	3	12	Rc1/8	34	—	10	22	7	3	M6×1.0×12depth	48.5	5.1	$\phi 9 \times 7$ depth, M6×1.0×10depth	9	—
40	3	16	Rc1/8	40	—	14	28	7	3	M8×1.25×12depth	56.5	6.9	$\phi 10.5 \times 8$ depth, M8×1.25×12depth	10	—
50	4	20	Rc1/4 (*)	48	—	17	38	9	3	M10×1.5×15depth	70	6.9	$\phi 11 \times 8.5$ depth, M8×1.25×16.5depth	10	—


\* Without magnet with stroke=5mm, EE=Rc1/8

Code Tube I.D.	T	V	V1	X	Y	Z
12	—	25	32	3.2	6.3	1
16	—	29	38	3.2	6.3	1
20	—	34	—	3.2	6.3	1
25	—	40	—	4.2	7.8	1
32	14	44	—	4.2	7.8	1
40	14	52	—	6.2	10.3	1.6
50	19	62	—	6.2	10.8	1.6


Code Tube I.D.	Without magnet				Magnet			
	Stroke 5,10	Stroke 15~30	Stroke 5,10	Stroke 15~30	Stroke 5,10	Stroke 15~30	Stroke 5,10	Stroke 15~30
	S	ZZ	S	ZZ	S	ZZ	S	ZZ
12	27	32	37	42	37	42	47	52
16	28.5	34	38.5	44	38.5	44	48.5	54
20	29.5	35	39.5	45	39.5	45	49.5	55
25	31	37	41	47	41	47	51	57
32	34.5	41.5	44.5	51.5	44.5	51.5	54.5	61.5
40	36	43	46	53	46	53	56	63

Code Tube I.D.	Without magnet				Magnet			
	Stroke 5~20				Stroke 5~20			
	S	ZZ	S	ZZ	S	ZZ	S	ZZ
50	28	37	38	47				

### Double acting




### Single acting




### Double acting

(with magnet)



### Double acting

Adjustable stroke



### Seal kit

Acting type	Rod packing		Piston packing		Cover ring	Piston gasket
	Double acting	Single acting	Double acting	Single acting	Double acting single acting	Double acting single acting
Q'y	2	1	1	1	2	1
ø12	KSYR-6	KSYR-6	OPA-12	OPA-12	d11×w1	d4×w1
ø16	KSYR-6	KSYR-6	OPA-16	OPA-16	S-14	d4×w1
ø20	KSYR-8	KSYR-8	OPA-20	OPA-20	S-18	d6×w1
ø25	KSYR-10	KSYR-10	OPA-25	OPA-25	S-22	d6×w1
ø32	KSYR-12	KSYR-12	OPA-32	OPA-32	d28×w2	d8×w1
ø40	KSYR-16	KSYR-16	OPA-40	OPA-40	S-36	d11×w1
ø50	KSYR-20	KSYR-20	OPA-50	OPA-50	AS-31	S-14
ø63	KSYR-20	—	OPA-63	—	AS-35	S-14
ø80	ORA-25	—	OPA-80	—	AS-41	S-18
ø100	SDR-30	—	OPA-100	—	S-95	S-26

### Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	100	Q'y	Component parts (inclusion)	Repair kits (inclusion)	
1	Snap ring (Front end)	*2	Spring steel	*2	Spring steel							2	●		
2	Cover ring	NBR										2	●	●	
3	Cushion packing	—	NBR										2	●	●
4	Piston gasket	NBR										1	●	●	
5	Piston packing	NBR										1	●	●	
6	Piston	Aluminum alloy										1	●		
7	Piston With magnet rod *1	Stainless steel	Carbon steel										2		
	Without magnet	*2	Carbon steel										2		
8	Body	Aluminum alloy										1			
9	Rod packing	NBR										2 <sup>*3</sup>	●	●	
10	Rod cover	Aluminum alloy										2	●		
11	Bush	—	Bearing alloy										2	●	
12	Magnet ring	Magnet material										1	●		
13	Spring	SWP										1	●		
14	Silencer	Brass										1	●		
15	Cushion packing	PU										1	●		
16	Adjustable nut	Carbon steel										1	●		

\*1. When customized material is bearing steel, only two-side across flat (wrench flat) is available.

\*2. Stainless steel

\*3. Single acting type, Q'y=1

### Order example Component parts

Tube I.D.	Component parts
ø12	CP-MCJA-2-12(M)
ø16	CP-MCJA-2-16(M)
ø20	CP-MCJA-2-20(M)
ø25	CP-MCJA-2-25(M)
ø32	CP-MCJA-2-32(M)
ø40	CP-MCJA-2-40(M)
ø50	CP-MCJA-2-50(M)
ø63	CP-MCJA-2-63(M)
ø80	CP-MCJA-2-80(M)
ø100	CP-MCJA-2-100(M)

M: With magnet


### Repair kits

Tube I.D.	Repair kits
ø12	PS-MCJA-2-12
ø16	PS-MCJA-2-16
ø20	PS-MCJA-2-20
ø25	PS-MCJA-2-25
ø32	PS-MCJA-2-32
ø40	PS-MCJA-2-40
ø50	PS-MCJA-2-50
ø63	PS-MCJA-2-63
ø80	PS-MCJA-2-80
ø100	PS-MCJA-2-100


COMPACT CYLINDER

22

$\varnothing 12, \varnothing 16$



$\varnothing 20, \varnothing 25$



$\varnothing 32\sim\varnothing 100$

Long stroke

Without counter bore




With magnet type:  
The stroke length must be over 100mm.

Without magnet type:  
The stroke length must be over 110mm.

$\varnothing 12, \varnothing 16$



$\varnothing 20\sim\varnothing 100$



Code Tube I.D.	AM	AQ	C	D	EE	E1	E2	F	G	H	H1	K
12	10	12	1	6	M5×0.8	16.3	23	5	11	5	17	3
16	10	12	1.5	6	M5×0.8	19.8	28	5	11	5.5	17.5	3
20	13	15	1.5	8	M5×0.8	24	—	6	15	5.5	20.5	3
25	15	17	2	10	M5×0.8	28	—	8	17	6	23	3
32	15	18	3	12	Rc1/8 (*1)	34	—	10	22	7	25	3
40	25	28	3	16	Rc1/8 (*1)	40	—	14	28	7	35	3
50	25	28	4	20	Rc1/4 (*2)	48	—	17	38	9	37	3
63	25	28	4	20	Rc1/4 (*2)	60	—	17	40	9	37	3
80	30	33	5	25	Rc3/8 (*3)	74	—	22	45	11	44	4
100	35	38	5	30	Rc3/8 (*3)	90	—	27	55	12	50	4


\*1. Without magnet with stroke=5mm, EE=M5×0.8

\*2. Without magnet with stroke=5mm, EE=Rc1/8

\*3. Without magnet with stroke=5mm, EE=Rc1/4

21

Male thread





Code Tube I.D.	KK	LH	M	N	PA	PB	Q	T	V	V1	X	Y	Z	Without magnet		Magnet	
														S	ZZ	S	ZZ
12	M3×0.5×6 dp	—	4.3	ø6.5×4.5 dp, M5×0.8×7.5 dp	6.5	6	M5×0.8	—	25	32	3.2	6.3	1	17	27	27	37
16	M3×0.5×6 dp	—	4.3	ø6.5×4.5 dp, M5×0.8×7.5 dp	7	6.5	M5×0.8	—	29	38	3.2	6.3	1	18.5	29.5	28.5	39.5
20	M4×0.7×8 dp	—	4.3	ø6.5×4.5 dp, M5×0.8×7.5 dp	7.5	—	M6×1.0	—	34	—	3.2	6.3	1	19.5	30.5	29.5	40.5
25	M5×0.8×10 dp	—	5.1	ø9×7 dp, M6×1.0×10 dp	8	—	M8×1.25	—	40	—	4.2	7.8	1	21	33	31	43
32	M6×1.0×12 dp	48.5	5.1	ø9×7 dp, M6×1.0×10 dp	9	—	M10×1.25	14	44	—	4.2	7.8	1	24.5	38.5	34.5	48.5
40	M8×1.25×12 dp	56.5	6.9	ø10.5×8 dp, M8×1.25×12 dp	10	—	M14×1.5	14	52	—	6.2	10.3	1.6	26	40	36	50
50	M10×1.5×15 dp	70	6.9	ø11×8.5 dp, M8×1.25×16.5 dp	10	—	M18×1.5	19	62	—	6.2	10.8	1.6	28	46	38	56
63	M10×1.5×15 dp	83	6.9	ø11×8.5 dp, M8×1.25×16.5 dp	12	—	M18×1.5	20	75	—	6.2	10.8	1.6	32	50	42	60
80	M14×1.5×20 dp	102	10.5	ø14×10.5 dp, M12×1.75×12 dp	13	—	M22×1.5	27	94	—	8.2	13.8	1.6	41	63	51	73
100	M18×1.5×20 dp	122	12.3	ø18.5×13 dp, M14×2×17 dp	17	—	M26×1.5	26	114	—	10.2	17.3	2	51	75	61	85

## COMPACT CYLINDER

### 24

$\phi 12, \phi 16$




Long stroke  
Without counter bore

With magnet type:  
The stroke length must be over 100mm.  
Without magnet type:  
The stroke length must be over 110mm.


$\phi 12, \phi 16$





$\phi 20\sim\phi 50$



$\phi 20, \phi 25$



$\phi 32\sim\phi 50$




### Single acting – Table for standard stroke

Tube I.D.	Stroke (mm)
$\phi 12, 16, 20, 25, 32, 40$	5, 10, 15, 20, 25, 30
$\phi 50$	5, 10, 15, 20

\* Please contact us if the stroke is out of specification.

### 23

Male thread



Code Tube I.D.	AM	AQ	H1	Q
12	10	12	17	M5×0.8
16	10	12	17.5	M5×0.8
20	13	15	20.5	M6×1.0
25	15	17	23	M8×1.25
32	15	18	25	M10×1.25
40	25	28	35	M14×1.5
50	25	28	37	M18×1.5

Code Tube I.D.	C	D	EE	E1	E2	F	G	H	K	KK	LH	M	N	PA	PB
12	1	6	M5×0.8	16.3	23	5	11	5	3	M3×0.5×6depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	6.5	6
16	1.5	6	M5×0.8	19.8	28	5	11	5.5	3	M3×0.5×6depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	7	6.5
20	1.5	8	M5×0.8	24	—	6	15	5.5	3	M4×0.7×8depth	—	4.3	$\phi 6.5 \times 4.5$ depth, M5×0.8×7.5depth	7.5	—
25	2	10	M5×0.8	28	—	8	17	6	3	M5×0.8×10depth	—	5.1	$\phi 9 \times 7$ depth, M6×1.0×10depth	8	—
32	3	12	Rc1/8	34	—	10	22	7	3	M6×1.0×12depth	48.5	5.1	$\phi 9 \times 7$ depth, M6×1.0×10depth	9	—
40	3	16	Rc1/8	40	—	14	28	7	3	M8×1.25×12depth	56.5	6.9	$\phi 10.5 \times 8$ depth, M8×1.25×12depth	10	—
50	4	20	Rc1/4 (*)	48	—	17	38	9	3	M10×1.5×15depth	70	6.9	$\phi 11 \times 8.5$ depth, M8×1.25×16.5depth	10	—

\* Without magnet with stroke=5mm, EE=Rc1/8


Code Tube I.D.	T	V	V1	X	Y	Z
12	—	25	32	3.2	6.3	1
16	—	29	38	3.2	6.3	1
20	—	34	—	3.2	6.3	1
25	—	40	—	4.2	7.8	1
32	14	44	—	4.2	7.8	1
40	14	52	—	6.2	10.3	1.6
50	19	62	—	6.2	10.8	1.6

Code Tube I.D.	Without magnet				Magnet			
	Stroke 5,10	Stroke 15-30	Stroke 5,10	Stroke 15-30	Stroke 5,10	Stroke 15-30	Stroke 5,10	Stroke 15-30
	S	ZZ	S	ZZ	S	ZZ	S	ZZ
12	27	37	37	47	37	47	47	57
16	28.5	39.5	38.5	49.5	38.5	49.5	48.5	59.5
20	29.5	40.5	39.5	50.5	39.5	50.5	49.5	60.5
25	31	43	41	53	41	53	51	63
32	34.5	48.5	44.5	58.5	44.5	58.5	54.5	68.5
40	36	50	46	60	46	60	56	70


Code Tube I.D.	Without magnet				Magnet			
	Stroke 5-20				Stroke 5-20			
	S	ZZ	S	ZZ	S	ZZ	S	ZZ
50	28	46	38	56				

### 28


$\phi 12, \phi 16$




$\phi 20, \phi 25$



$\phi 32\sim\phi 100$



\*ADJ: Adjustable stroke



### Long stroke



#### Without counter bore

With magnet type:  
The stroke length must be over 100mm.  
Without magnet type:  
The stroke length must be over 110mm.

$\phi 12, \phi 16$



$\phi 20, \phi 100$




Code Tube I.D.	A	AM	AQ	A1	AR	B	C	D	EE	E1	E2	F	G	H	H1	J	K	KK
12	13	10	12	2	16	8	1	6	M5×0.8	16.3	23	5	11	5	17	12	3	M3×0.5×6 dp
16	13	10	12	2	16.5	8	1.5	6	M5×0.8	19.8	28	5	11	5.5	17.5	12	3	M3×0.5×6 dp
20	15	13	15	2	19	13	1.5	8	M5×0.8	24	—	6	15	5.5	20.5	16	3	M4×0.7×8 dp
25	15	15	17	2	19.5	13	2	10	M5×0.8	28	—	8	17	6	23	16	3	M5×0.8×10 dp
32	12	15	18	2	18	17	3	12	Rc1/8 (*1)	34	—	10	22	7	25	20	3	M6×1.0×12 dp
40	12	25	28	2	20	19	3	16	Rc1/8 (*1)	40	—	14	28	7	35	30	3	M8×1.25×12 dp
50	15	25	28	2	22	24	4	20	Rc1/4 (*2)	48	—	17	38	9	37	40	3	M10×1.5×15 dp
63	15	25	28	2	22	24	4	20	Rc1/4 (*2)	60	—	17	40	9	37	40	3	M10×1.5×15 dp
80	20	30	33	3	33	32	5	25	Rc3/8 (*3)	74	—	22	45	11	44	50	4	M14×1.5×20 dp
100	20	35	38	3	33	32	5	30	Rc3/8 (*3)	90	—	27	55	12	50	50	4	M18×1.5×20 dp

\*1. Without magnet with stroke=5mm, EE=M5×0.8

\*2. Without magnet with stroke=5mm, EE=Rc1/8

\*3. Without magnet with stroke=5mm, EE=Rc1/4



### 27 Male thread



Code Tube I.D.	L	LH	M	N	PA	PB	Q	T	U	V	V1	W	X	Y	Z	Without magnet		Magnet	
																S	ZZ	S	ZZ
12	4	—	4.3	$\phi 6.5 \times 4.5$ dp, M5×0.8×7.5 dp	6.5	6	M5×0.8	—	M5×0.8	25	32	22.5	3.2	6.3	1	17	44.5	27	54.5
16	4	—	4.3	$\phi 6.5 \times 4.5$ dp, M5×0.8×7.5 dp	7	6.5	M5×0.8	—	M5×0.8	29	38	23.5	3.2	6.3	1	18.5	47.5	28.5	57.5
20	5	—	4.3	$\phi 6.5 \times 4.5$ dp, M5×0.8×7.5 dp	7.5	—	M6×1.0	—	M8×1.25	34	—	26	3.2	6.3	1	19.5	51	29.5	61
25	5	—	5.1	$\phi 9 \times 7$ dp, M6×1.0×10 dp	8	—	M8×1.25	—	M8×1.25	40	—	27.2	4.2	7.8	1	21	54.2	31	64.2
32	6	48.5	5.1	$\phi 9 \times 7$ dp, M6×1.0×10 dp	9	—	M10×1.25	14	M10×1.25	44	—	26	4.2	7.8	1	24.5	57.5	34.5	67.5
40	7	56.5	6.9	$\phi 10.5 \times 8$ dp, M8×1.25×12 dp	10	—	M14×1.5	14	M12×1.25	52	—	28	6.2	10.3	1.6	26	61	36	71
50	8	70	6.9	$\phi 11 \times 8.5$ dp, M8×1.25×16.5 dp	10	—	M18×1.5	19	M16×1.5	62	—	31	6.2	10.8	1.6	28	68	38	78
63	8	83	6.9	$\phi 11 \times 8.5$ dp, M8×1.25×16.5 dp	12	—	M18×1.5	20	M16×1.5	75	—	31	6.2	10.8	1.6	32	72	42	82
80	13	102	10.5	$\phi 14 \times 10.5$ dp, M12×1.75×12 dp	13	—	M22×1.5	27	M22×1.5	94	—	44	8.2	13.8	1.6	41	96	51	106
100	13	122	12.3	$\phi 18.5 \times 13$ dp, M14×2×17 dp	17	—	M26×1.5	26	M22×1.5	114	—	44	10.2	17.3	2	51	107	61	117


## COMPACT CYLINDER

### Dimensions




### Installation of sensor switch

$\phi 12\sim\phi 40$



$\phi 50\sim\phi 100$



### Order example

RCE1 — □

MODEL





RCE / RCE1 (C: Reed switch)  
RNE (N: Solid state switch)  
RDEP (Solid state switch)

WIRE LENGTH

1M: L=1000m  
2M: L=2000m  
QD: M8 3Pin connector  
EQD: M8 3Pin connector

### Description

▽ RCE, RCE1, RDEP switch ↓ Port



# MCJA Multiple position series

## COMPACT CYLINDER



Special spec



Rod end shape



Technical data



Caution for safety  
(Read before installing)



### Features

Two-stage stroke: Two compact cylinders with same I.D. but different strokes length are connected to achieve two-stage stroke.

### Specification

Model	MCJA-3*									
Acting type	Double acting / Single acting			Double acting						
Tube I.D. (mm)	12	16	20	25	32	40	50	63	80	100
Port size	M5×0.8		Rc1/8	Rc1/4	Rc3/8					
Medium	Air									
Operating pressure range (MPa)	Double acting		0.05~1	0.03~1	0.02~1					
	Single acting		0.2~1	0.15~1	0.1~1	—				
Proof pressure	1.5 MPa									
Ambient temperature	-5~+60°C (No freezing)									
Available speed range	50~500 mm/sec									
Sensor switch (*)	RCE , RCE1 , RDEP									

\* RDEP only for tube I.D.  $\phi 12\sim\phi 50$ .

### Order example

MCJA — 32 — 40 — 10×25 M — □

MODEL

3: Multiple position

TUBE I.D.

M: Magnet

STROKE1×STROKE2

Stroke 1: First stroke  
Stroke 2: Total stroke

PORT THREAD

Blank: M5×0.8  
(for  $\phi 12\sim\phi 25$ )  
Blank: Rc thread  
G: G thread  
NPT: NPT thread  
(for  $\phi 32\sim\phi 100$ )

\* The total stroke must be greater than the first stroke.

STYLE

Code	Symbol	Description
3 1		Double acting / Male thread
3 2		Double acting / Female thread
3 5		Single acting / Normally returned male thread
3 6		Single acting / Normally returned female thread

### Double acting – Table for standard stroke

Tube I.D.	Stroke (mm)	Max. stroke (mm)	
		First	Total
$\phi 12, 16$	5, 10, 15, 20, 25, 30	130	300
$\phi 20, 25, 32$ $\phi 40, 50, 63, 80$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50	130	300
$\phi 100$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50	120	125

\* Please contact us if the stroke is out of specification.

### Flat washer kits

WS — MCJA — 3 — 40

FLAT WASHER

MODEL

MULTIPLE POSITION

TUBE I.D.

\* Only for tube I.D.  $\phi 20\sim\phi 100$ .


### Single acting – Table for standard stroke

Tube I.D.	Stroke (mm)
$\phi 12, 16, 20, 25, 32, 40$	5, 10, 15, 20, 25, 30
$\phi 50$	5, 10, 15, 20

\* Please contact us if the stroke is out of specification.


## COMPACT CYLINDER

### Double acting



### Single acting

Normally returned




### Seal kit

Acting type	Rod packing		Piston packing		Cover ring	Piston gasket
	Double acting	Normally returned	Double acting	Single acting	Double acting single acting	Double acting single acting
Q'y	2	1	2	2	4	2
ø12	KSYR-6	KSYR-6	OPA-12	OPA-12	S-12	d4×w1
ø16	KSYR-6	KSYR-6	OPA-16	OPA-16	S-14	d4×w1
ø20	KSYR-8	KSYR-8	OPA-20	OPA-20	S-18	d6×w1
ø25	KSYR-10	KSYR-10	OPA-25	OPA-25	S-22	d8×w1
ø32	KSYR-12	KSYR-12	OPA-32	OPA-32	d28×w2	S-9
ø40	KSYR-16	KSYR-16	OPA-40	OPA-40	S-36	S-9
ø50	KSYR-20	KSYR-20	OPA-50	OPA-50	AS-31	S-16
ø63	KSYR-20	—	OPA-63	—	AS-35	S-16
ø80	ORA-25	—	OPA-80	—	AS-41	d20×w1
ø100	SDR-30	—	OPA-100	—	S-95	S-26

### Double acting

(with magnet)



### Order example Component parts

Tube I.D.	Component parts
ø12	CP-MCJA-3-12(M)
ø16	CP-MCJA-3-16(M)
ø20	CP-MCJA-3-20(M)
ø25	CP-MCJA-3-25(M)
ø32	CP-MCJA-3-32(M)
ø40	CP-MCJA-3-40(M)
ø50	CP-MCJA-3-50(M)
ø63	CP-MCJA-3-63(M)
ø80	CP-MCJA-3-80(M)
ø100	CP-MCJA-3-100(M)

M: With magnet

### Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	100	Q'y	Component parts (inclusion)	Repair kits (inclusion)
1	Head cover	Aluminum alloy										1	●	
2	Snap ring (Front end)	*2	Spring steel		*2		Spring steel					1	●	
3	Cover ring	NBR										4	●	●
4	Cushion packing	—	NBR									4	●	●
5	Piston gasket	NBR										2	●	●
6	Piston packing	NBR										2	●	●
7	Piston	Aluminum alloy										2	●	
8	Screw	With magnet	Stainless steel				SCM				2	●		
		Without magnet	SCM	Stainless steel				SCM				2	●	
9	Piston rod *1	With magnet	*2	Carbon steel								2		
		Without magnet		Carbon steel								2		
10	Body	Aluminum alloy										2		
11	Rod packing	NBR										2 <sup>*3</sup>	●	●
12	Rod cover	Aluminum alloy										1	●	
13	Bush										Bearing alloy	2	●	
14	Magnet ring	Magnet material										2	●	
15	Spring	SWP				—				2	●			
16	Silencer	Brass										1	●	
17	Center cover	Aluminum alloy										1	●	
18	Bolt	SCM										2		
19	Snap ring (Rear end)	Stainless steel				Spring steel				1	●			

\*1. When customized material is bearing steel, only two-side across flat (wrench flat) is available.

\*2. Stainless steel

\*3. Single acting / Normally returned, Q'y=1


### Repair kits

Tube I.D.	Repair kits
ø12	PS-MCJA-3-12
ø16	PS-MCJA-3-16
ø20	PS-MCJA-3-20
ø25	PS-MCJA-3-25
ø32	PS-MCJA-3-32
ø40	PS-MCJA-3-40
ø50	PS-MCJA-3-50
ø63	PS-MCJA-3-63
ø80	PS-MCJA-3-80
ø100	PS-MCJA-3-100


COMPACT CYLINDER

32


$\phi 12, \phi 16$



$\phi 20, \phi 25$



$\phi 32\sim\phi 100$



\*Stroke 1: First stroke Stroke 2: Total stroke


Code Tube I.D.	AM	AQ	C	D	EE	E1	E2	F	G	H	H1	K
12	10	12	1	6	M5×0.8	16.3	23	5	11	5	17	3
16	10	12	1.5	6	M5×0.8	19.8	28	5	11	5.5	17.5	3
20	13	15	1.5	8	M5×0.8	24	—	6	15	5.5	20.5	3
25	15	17	2	10	M5×0.8	28	—	8	17	6	23	3
32	15	18	3	12	Rc1/8 (*1)	34	—	10	22	7	25	3
40	25	28	3	16	Rc1/8 (*1)	40	—	14	28	7	35	3
50	25	28	4	20	Rc1/4 (*2)	48	—	17	38	9	37	3
63	25	28	4	20	Rc1/4 (*2)	60	—	17	40	9	37	3
80	30	33	5	25	Rc3/8 (*3)	74	—	22	45	11	44	4
100	35	38	5	30	Rc3/8 (*3)	90	—	27	55	12	50	4

\*1. Without magnet with stroke=5mm, EE=M5×0.8

\*2. Without magnet with stroke=5mm, EE=Rc1/8

\*3. Without magnet with stroke=5mm, EE=Rc1/4

31 Male thread




Long stroke

Without counter bore

With magnet type:  
The stroke length must be over 100mm.  
Without magnet type:  
The stroke length must be over 110mm.

$\phi 12\sim\phi 100$



Code Tube I.D.	KK	LH	M	N	PA	PB	Q	T	V	V1	X	Y	Z	Without magnet		Magnet	
														S	ZA	S	ZA
12	M3×0.5×6depth	—	4.3	$\phi 6.5\times 4.5\text{depth}$ , M5×0.8×7.5depth	6.5	6	M5×0.8	—	25	32	3.2	6.3	1	17	39	27	59
16	M3×0.5×6depth	—	4.3	$\phi 6.5\times 4.5\text{depth}$ , M5×0.8×7.5depth	7	6.5	M5×0.8	—	29	38	3.2	6.3	1	18.5	42.5	28.5	62.5
20	M4×0.7×8depth	—	4.3	$\phi 6.5\times 4.5\text{depth}$ , M5×0.8×7.5depth	7.5	—	M6×1.0	—	34	—	3.2	6.3	1	19.5	44.5	29.5	64.5
25	M5×0.8×10depth	—	5.1	$\phi 9\times 7\text{depth}$ , M6×1.0×10depth	8	—	M8×1.25	—	40	—	4.2	7.8	1	21	48	31	68
32	M6×1.0×12depth	48.5	5.1	$\phi 9\times 7\text{depth}$ , M6×1.0×10depth	9	—	M10×1.25	14	44	—	4.2	7.8	1	24.5	56	34.5	76
40	M8×1.25×12depth	56.5	6.9	$\phi 10.5\times 8\text{depth}$ , M8×1.25×12depth	10	—	M14×1.5	14	52	—	6.2	10.3	1.6	26	59	36	79
50	M10×1.5×15depth	70	6.9	$\phi 11\times 8.5\text{depth}$ , M8×1.25×16.5depth	10	—	M18×1.5	19	62	—	6.2	10.8	1.6	28	65	38	85
63	M10×1.5×15depth	83	6.9	$\phi 11\times 8.5\text{depth}$ , M8×1.25×16.5depth	12	—	M18×1.5	20	75	—	6.2	10.8	1.6	32	73	42	93
80	M14×1.5×20depth	102	10.5	$\phi 14\times 10.5\text{depth}$ , M12×1.75×12depth	13	—	M22×1.5	27	94	—	8.2	13.8	1.6	41	93	51	113
100	M18×1.5×20depth	122	12.3	$\phi 18.5\times 13\text{depth}$ , M14×2×17depth	17	—	M26×1.5	26	114	—	10.2	17.3	2	51	114	61	134

# MCJA Back to back type series

## COMPACT CYLINDER



Special spec



Rod end shape



Technical data



Caution for safety  
(Read before installing)



### Specification

Model	MCJA-4*									
Acting type	Double acting / Single acting						Double acting			
Tube I.D. (mm)	12	16	20	25	32	40	50	63	80	100
Port size	M5×0.8			Rc1/8		Rc1/4		Rc3/8		
Medium	Air									
Operating pressure range (MPa)	Double acting		0.05~1	0.03~1	0.02~1					
	Single acting		0.2~1	0.15~1	0.1~1		—			
Proof pressure	1.5 MPa									
Ambient temperature	-5~+60°C (No freezing)									
Available speed range	50~500 mm/sec									
Sensor switch (*)	RCE , RCE1 , RDEP									

\* RDEP only for tube I.D.  $\phi$ 12~ $\phi$ 50.

### Order example

MCJA — 42 — 40 — 25×25 M — □

MODEL

4: Back to back type

TUBE I.D.

STROKE1×STROKE2  
Stroke 1: First stroke  
Stroke 2: Second stroke

M: Magnet

PORT THREAD

Blank: M5×0.8  
(for  $\phi$ 12~ $\phi$ 25)  
Blank: Rc thread  
G: G thread  
NPT: NPT thread  
(for  $\phi$ 32~ $\phi$ 100)

STYLE

Code	Symbol	Description
4 1		Double acting / Male thread
4 2		Double acting / Female thread
4 3		Single acting / Normally extended male thread
4 4		Single acting / Normally extended female thread
4 5		Single acting / Normally returned male thread
4 6		Single acting / Normally returned female thread

### Double acting – Table for standard stroke

Tube I.D.	Stroke (mm)	Max. stroke (mm)	
		First	Second
$\phi$ 12,16	5,10,15,20,25,30	130	300
$\phi$ 20,25,32 $\phi$ 40,50,63,80	5,10,15,20,25,30,35,40,45,50	130	300
$\phi$ 100	5,10,15,20,25,30,35,40,45,50	125	125

\* Please contact us if the stroke is out of specification.

### Single acting – Table for standard stroke

Tube I.D.	Stroke (mm)
$\phi$ 12,16,20,25,32,40	5,10,15,20,25,30
$\phi$ 50	5,10,15,20

\* Please contact us if the stroke is out of specification.

### Flat washer kits

WS — MCJA — 3 — 40

FLAT WASHER

MODEL

MULTIPLE POSITION


TUBE I.D.

\* Use the same kits with MCJA multiple position.

\* Only for tube I.D.  $\phi$ 20~ $\phi$ 100.


## COMPACT CYLINDER

### Double acting




### Single acting

Normally returned



### Single acting

Normally extended




### Seal kit

Acting type	Rod packing			Piston packcion		Cover ring	Piston gasket
	Double acting	Normally returned	Normally extended	Double acting	Single acting	Double acting single acting	Double acting single acting
Qty.	2	0	2	2	2	4	2
ø12	KSYR-6	—	KSYR-6	OPA-12	OPA-12	S-12	d4×w1
ø16	KSYR-6	—	KSYR-6	OPA-16	OPA-16	S-14	d4×w1
ø20	KSYR-8	—	KSYR-8	OPA-20	OPA-20	S-18	d6×w1
ø25	KSYR-10	—	KSYR-10	OPA-25	OPA-25	S-22	d8×w1
ø32	KSYR-12	—	KSYR-12	OPA-32	OPA-32	d28×w2	S-9
ø40	KSYR-16	—	KSYR-16	OPA-40	OPA-40	S-36	S-9
ø50	KSYR-20	—	KSYR-20	OPA-50	OPA-50	AS-31	S-16
ø63	KSYR-20	—	—	OPA-63	—	AS-35	S-16
ø80	ORA-25	—	—	OPA-80	—	AS-41	d20×w1
ø100	SDR-30	—	—	OPA-100	—	S-95	S-26

### Double acting

(with magnet)



### Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	100	Q'y	Component parts (inclusion)	Repair kits (inclusion)	
1	Head cover	Aluminum alloy										2	●		
2	Snap ring (Front end)	*2	Spring steel	*2	Spring steel								2	●	
3	Cover ring	NBR										4	●	●	
4	Cushion packing	—	NBR									4	●	●	
5	Piston gasket	NBR										2	●	●	
6	Piston packing	NBR										2	●	●	
7	Piston	Aluminum alloy										2	●		
8	Screw	With magnet	Stainless steel			SCM					2	●			
		Without magnet	SCM	Stainless steel			SCM					2	●		
9	Piston rod *1	With magnet	*2	Carbon steel							2				
		Without magnet		Carbon steel							2				
10	Body	Aluminum alloy										2			
11	Rod packing	NBR										2*3	●	●	
12	Rod cover	Aluminum alloy										2	●		
13	Bush	—	Bearing alloy									2	●		
14	Magnet ring	Magnet material										2	●		
15	Spring	SWP			—							2	●		
16	Silencer	Brass			—							2	●		
17	Bolt	SCM										2			
18	Snap ring (Rear end)	Stainless steel			Spring steel							2	●		

\*1. When customized material is bearing steel, only two-side across flat (wrench flat) is available.

\*2. Stainless steel

\*3. Single acting / Normally returned, Q'y=0

### Order example

#### Component parts

Tube I.D.	Component parts
ø12	CP-MCJA-4-12(M)
ø16	CP-MCJA-4-16(M)
ø20	CP-MCJA-4-20(M)
ø25	CP-MCJA-4-25(M)
ø32	CP-MCJA-4-32(M)
ø40	CP-MCJA-4-40(M)
ø50	CP-MCJA-4-50(M)
ø63	CP-MCJA-4-63(M)
ø80	CP-MCJA-4-80(M)
ø100	CP-MCJA-4-100(M)



M: With magnet

#### Repair kits


Tube I.D.	Repair kits
ø12	PS-MCJA-4-12
ø16	PS-MCJA-4-16
ø20	PS-MCJA-4-20
ø25	PS-MCJA-4-25
ø32	PS-MCJA-4-32
ø40	PS-MCJA-4-40
ø50	PS-MCJA-4-50
ø63	PS-MCJA-4-63
ø80	PS-MCJA-4-80
ø100	PS-MCJA-4-100

### 42




$\phi 12, \phi 16$



$\phi 20, \phi 25$



$\phi 32\sim\phi 100$



\*Stroke 1: First stroke    Stroke 2: Second stroke


Code Tube I.D.	AM	AQ	C	D	EE	E1	E2	F	G	H	H1	K
12	10	12	1	6	M5×0.8	16.3	23	5	11	5	17	3
16	10	12	1.5	6	M5×0.8	19.8	28	5	11	5.5	17.5	3
20	13	15	1.5	8	M5×0.8	24	—	6	15	5.5	20.5	3
25	15	17	2	10	M5×0.8	28	—	8	17	6	23	3
32	15	18	3	12	Rc1/8 (*1)	34	—	10	22	7	25	3
40	25	28	3	16	Rc1/8 (*1)	40	—	14	28	7	35	3
50	25	28	4	20	Rc1/4 (*2)	48	—	17	38	9	37	3
63	25	28	4	20	Rc1/4 (*2)	60	—	17	40	9	37	3
80	30	33	5	25	Rc3/8 (*3)	74	—	22	45	11	44	4
100	35	38	5	30	Rc3/8 (*3)	90	—	27	55	12	50	4

\*1. Without magnet with stroke=5mm, EE=M5×0.8

\*2. Without magnet with stroke=5mm, EE=Rc1/8

\*3. Without magnet with stroke=5mm, EE=Rc1/4

### 41 Male thread




### Long stroke

#### Without counter bore

With magnet type:  
The stroke length must be over 100mm.  
Without magnet type:  
The stroke length must be over 110mm.

$\phi 12\sim\phi 100$



Code Tube I.D.	KK	LH	M	N	PA	PB	Q	T	V	V1	X	Y	Z	Without magnet		Magnet	
														S	ZB	S	ZB
12	M3×0.5×6depth	—	4.3	ø6.5×4.5depth, M5×0.8×7.5depth	6.5	6	M5×0.8	—	25	32	3.2	6.3	1	17	44	27	64
16	M3×0.5×6depth	—	4.3	ø6.5×4.5depth, M5×0.8×7.5depth	7	6.5	M5×0.8	—	29	38	3.2	6.3	1	18.5	48	28.5	68
20	M4×0.7×8depth	—	4.3	ø6.5×4.5depth, M5×0.8×7.5depth	7.5	—	M6×1.0	—	34	—	3.2	6.3	1	19.5	50	29.5	70
25	M5×0.8×10depth	—	5.1	ø9×7depth, M6×1.0×10depth	8	—	M8×1.25	—	40	—	4.2	7.8	1	21	54	31	74
32	M6×1.0×12depth	48.5	5.1	ø9×7depth, M6×1.0×10depth	9	—	M10×1.25	14	44	—	4.2	7.8	1	24.5	63	34.5	83
40	M8×1.25×12depth	56.5	6.9	ø10.5×8depth, M8×1.25×12depth	10	—	M14×1.5	14	52	—	6.2	10.3	1.6	26	66	36	86
50	M10×1.5×15depth	70	6.9	ø11×8.5depth, M8×1.25×16.5depth	10	—	M18×1.5	19	62	—	6.2	10.8	1.6	28	74	38	94
63	M10×1.5×15depth	83	6.9	ø11×8.5depth, M8×1.25×16.5depth	12	—	M18×1.5	20	75	—	6.2	10.8	1.6	32	82	42	102
80	M14×1.5×20depth	102	10.5	ø14×10.5depth, M12×1.75×12depth	13	—	M22×1.5	27	94	—	8.2	13.8	1.6	41	104	51	124
100	M18×1.5×20depth	122	12.3	ø18.5×13depth, M14×2×17depth	17	—	M26×1.5	26	114	—	10.2	17.3	2	51	126	61	146

# MCJQ2 series

## COMPACT CYLINDER



Rod end shape



Technical data



Caution for safety  
(Read before installing)



### Features


- Ultra Compact, light weight and space saving cylinder.
- Single and double acting available.
- Ideal for use in machinery where space is limited and incorporating sensor groove which enables flush fitting of sensors.
- Magnetic as standard.

### Specification

Model	MCJQ2	
Acting type	Double acting	
Tube I.D. (mm)	12,16	20,25
Port size	M5×0.8	
Medium	Air	
Operating pressure range	0.07~1 MPa	0.05~1 MPa
Proof pressure	1.5 MPa	
Ambient temperature	-5°C~+60°C (No freezing)	
Available speed range	50~500 mm/sec	
Sensor switch	RCB	

### Order example

MCJQ2 – 12 – 20 – 25 M




STYLE

Code	Symbol	Description
1 1		Double acting / Male thread
1 2		Double acting / Female thread

### Flat washer kits

WS – MCJQ2 – 20



### Double acting – Table for standard stroke

Tube I.D.	Standard stroke
ø12, 16	5,10,15,20,25,30
ø20, 25	5,10,15,20,25,30,35,40,45,50

\* Please contact us if the stroke is out of specification.


### Cylinder weight

Unit: g

Model	Basic weight MCJQ2-11	Stroke 5mm MCJQ2-11	Basic weight MCJQ2-12	Stroke 5mm MCJQ2-12
Tube I.D.				
ø12	40	7	39	7
ø16	63	9	60	9
ø20	86	11	80	11
ø25	126	14	113	14

### Double acting

(with magnet)



### Material

No.	Part name	Material	Note	Q'y	Repair kits (inclusion)
1	Body	Aluminum alloy	Hard anodized	1	
2	Rod cover	Aluminum bearing alloy	Anodized	1	
3	End cover	Aluminum alloy	Anodized	1	
4	Piston rod	Stainless steel		1	
5	Piston	Aluminum alloy	Anodized	1	
6	Rod packing	NBR		1	●
7	Snap ring	Stainless steel		1	
8	Cover ring	NBR		1	●
9	Piston bolt	Stainless steel		1	
10	Piston packing	NBR		1	●
11	Piston gasket	NBR		1	●
12	Cushion packing	NBR		2	●
13	Magnet	Magnet		1	


### Order example Repair kits

Tube I.D.	Repair kits
ø12	<b>PS-MCJQ2-12</b>
ø16	<b>PS-MCJQ2-16</b>
ø20	<b>PS-MCJQ2-20</b>
ø25	<b>PS-MCJQ2-25</b>


### Seal kit

	Rod packing	Piston packing	Cover ring	Piston gasket
Acting type	Double acting			
Tube I.D. / Q'y	1	1	2	1
ø12	KSYR-6	OPA-12	S-11	d4×w1
ø16	KSYR-8	OPA-16	S-14	d4×w1
ø20	KSYR-10A	OPA-20	S-18	d6×w1
ø25	KSYR-12	OPA-25	S-22.4	d8×w1

**12**




**11 Male thread**



Code Tube I.D.	C1	H1	L1	X
12	9	M5×0.8	14	10.5
16	10	M6×1.0	15.5	12
20	12	M8×1.25	18.5	14
25	15	M10×1.25	22.5	17.5

Code Tube I.D.	Stroke range	A	B	C	D	E	F	H	K	L	M	N	OA	RA	OB	RB	T	P	Q	V	W
12	5~30	31.5	28	6	6	32	6.5	M3×0.5	5	3.5	22	3.5	M4×0.7	7	6.5	3.5	0.5	M5×0.8	11	25	28
16	5~30	34	30.5	8	8	38	5.5	M4×0.7	6	3.5	28	3.5	M4×0.7	7	6.5	3.5	0.5	M5×0.8	10	29	31
20	5~50	36	31.5	10	10	47	5.5	M5×0.8	8	4.5	36	5.5	M6×1.0	10	9	7	1	M5×0.8	10.5	36	30
25	5~50	37.5	32.5	12	12	52	5.5	M6×1.0	10	5	40	5.5	M6×1.0	10	9	7	1	M5×0.8	11	40	35

### Installation of sensor switch



### Order example

RCB — □

MODEL

RCB (C: Reed switch)  
RNB (N: Solid state switch)

WIRE LENGTH

1M: L=1000m  
2M: L=2000m  
QD: M8 3Pin connector  
EQD: M8 3Pin connector

Code Tube I.D.	A	B	C	D	E
12	33	20.5	8	16	22
16	37	22.5	8	16	22
20	42.5	24	5.5	16	22
25	46	26	6	16	22



Special spec




Rod end shape



Technical data



Caution for safety  
(Read before installing)



### Features

- All products use counterbore and thread installation design without any fixed frame to meet the space saving requirements.
- Anodised aluminum tubes provide better corrosion and abrasion resistance.
- The assembly grooves are designed around the body to make the sensor easier to install and fix.
- Compact assembly groove design makes the sensors enable to flush mount and can save space.
- Sensors can be mounted on any one of three faces for 12 and 16 bore and on four faces for 20~100 bore.

### Specification

Model		MCJQ									
Acting type		Double acting / Single acting					Double				
Tube I.D. (mm)		12	16	20	25	32	40	50	63	80	100
Port size		M5×0.8			Rc1/8		Rc1/4		Rc3/8		
Medium		Air									
Operating pressure range (MPa)	Double acting	0.07~1		0.05~1							
	Single acting	0.2~1		0.15~1		0.1~1		—			
Proof pressure		1.5 MPa									
Ambient temperature		-5°C~+60°C (No freezing)									
Available speed range		50~500 mm/sec									
Sensor switch	RCE,RCE1	(*)	●	●	●	●	●	●	●	●	●
	RDEP	●	●	—	●	—	●	●	●	●	●

\*1.  $\varnothing 12$ ,  $\varnothing 16$ : only applicable to RDE and RDE1E.

\*2. RCE , RCE1 , RDEP specification.

### Single acting – Table for standard stroke

Tube I.D.	Standard stroke (mm)
$\varnothing 12, 16, 20, 25, 32, 40$	5, 10
$\varnothing 50$	5, 10, 15, 20


### Double acting – Table for standard stroke

Tube I.D.	Standard stroke	Long stroke (mm)
$\varnothing 12, 16$	5, 10, 15, 20, 25, 30	35, 40, 45, 50, 75, 100
$\varnothing 20$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50	75, 100, 125, 150, 175, 200
$\varnothing 25$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100	75, 100, 125, 150, 175, 200, 250, 300
$\varnothing 32\sim 80$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100	125, 150, 175, 200, 250, 300
Tube I.D.	Standard stroke (mm)	
$\varnothing 100$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100	

\* Please contact us if the stroke is out of specification.

### Order example

**MCJQ – 12 – 20 – 25 M – F – G**



STYLE







Code	Symbol	Description	Code	Symbol	Description
1 1		Double acting / Male thread	2 1		Double rod / Male thread
1 2		Double acting / Female thread	2 2		Double rod / Female thread
1 3		Single acting / Normally extended male thread	2 3		Single acting / Double rod / Male thread
1 4		Single acting / Normally extended female thread	2 4		Single acting / Double rod / Female thread
1 5		Single acting / Normally returned male thread	2 7		Double rod / Adjustable male thread Please mark "adjustable stroke" at order list
1 6		Single acting / Normally returned female thread	2 8		Double rod / Adjustable female thread Please mark "adjustable stroke" at order list

TYPE

Code	Description
Blank	Standard
<b>F</b>	Rear flange  (for standard stroke)
<b>L*</b>	Piston rod extended to 10 mm For adding LB accessories or single rod cylinder with FAC accessories
<b>LA</b>	(for standard stroke) For double rod cylinders with FAC accessories


\* L type not applicable to MCJQ-27/28 adjustable stroke type, if required, please contact us.

### Accessories


Code	Accessories					Rod nut
	LB* (Purchase 2 pcs)	CB	FAC*	FBC	RF	NUT
Mounting Tube I.D.						
ø12	LB-J1-12	CB-J1-12	FAC-J1-12		RF-J1-12	NUT-M5x0.8x4Hx8B
ø16	LB-J1-16	CB-J1-16	FAC-J1-16		RF-J1-16	NUT-M6x1.0x5Hx10B
ø20	LB-J1-20	CB-J1-20	FAC-J1-20		RF-J1-20	NUT-M8x1.25x5Hx13B
ø25	LB-J1-25	CB-J1-25	FAC-J1-25		RF-J1-25	NUT-M10x1.25x6Hx17B
ø32	LB-J1-32	CB-J1-32	FAC-J1-32		RF-J1-32	NUT-M14x1.5x8Hx22B
ø40	LB-J1-40	CB-J1-40	FAC-J1-40		RF-J1-40	
ø50	LB-J1-50	CB-J1-50	FAC-J1-50		RF-J1-50	NUT-M18x1.5x11Hx26B
ø63	LB-J1-63	CB-J1-63	FAC-J1-63		RF-J1-63	
ø80	LB-J1-80	CB-J1-80	FAC-J1-80		RF-J1-80	NUT-M22x1.5x13Hx32B
ø100	LB-J1-100	CB-J1-100	FAC-J1-100		RF-J1-100	NUT-M26x1.5x14Hx35B

\* Standard stroke LB and FAC must be used with the L type (as the piston rod needs to be extended by 10 mm).

### Pin

Applicable	CB accessories
Code	<b>PIN-CB-P</b> (With snap ring)
Fig Tube I.D.	
ø12	PIN-J1-12-1-P
ø16	PIN-J1-16-1-P
ø20	PIN-J1-20-1-P
ø25	PIN-J1-25-1-P
ø32	PIN-J1-32-1-P
ø40	
ø50	PIN-J1-50-1-P
ø63	
ø80	PIN-J1-80-1-P
ø100	PIN-J1-100-1-P

### Flat washer kits

Code	WS
Fig Tube I.D.	
ø12	WS-MCJQ-12
ø16	WS-MCJQ-16
ø20	WS-MCJQ-20
ø25	WS-MCJQ-25
ø32	WS-MCJQ-32
ø40	WS-MCJQ-40
ø50	WS-MCJQ-50
ø63	WS-MCJQ-63
ø80	WS-MCJQ-80
ø100	WS-MCJQ-100

### Order example of self-assembled

The tube I.D. ø40 of LB accessories with stroke 25mm.

No.	Order number	Qty
1	LB-J1-40	2
2	MCJQ-12-40-25-L	1


\* To order accessories/cylinder, please place orders separately according to the order codes in the above table. Please refer to the previous page for the cylinder ordering method.

# MCJQ Inside structure & Parts list – Single rod


## COMPACT CYLINDER




### Double acting




### Double acting (with magnet)



### Single acting Normally extended



### Single acting Normally returned



## Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	100	Q'y	Repair kits (inclusion)
1	Body	Aluminum alloy										1	
2	Rod cover	Aluminum alloy										1	
3	End cover	Aluminum alloy										1	
4	Piston rod	Carbor steel										1	
5	Piston	Aluminum alloy										1	
6	Rod packing	NBR										1	●
7	Snap ring	Stainless steel					Spring steel					1	
8	Cover ring	NBR										1	●
9	Piston bolt	Stainless steel					SCM					1	
10	Piston packing	NBR										1	●
11	Piston gasket	NBR										1	●
12	Cushion packing	NBR										2	●
13	Magnet	Magnet										1	
14	Wear ring	—					Resin					1	
15	Bush	—					Bearing alloy					1	
16	Spring	SWP										1	
17	Spring holder	Aluminum alloy					—					2	


## Order example Repair kits

Tube I.D.	Repair kits
ø12	PS-MCJQ-12
ø16	PS-MCJQ-16
ø20	PS-MCJQ-20
ø25	PS-MCJQ-25
ø32	PS-MCJQ-32
ø40	PS-MCJQ-40
ø50	PS-MCJQ-50
ø63	PS-MCJQ-63
ø80	PS-MCJQ-80
ø100	PS-MCJQ-100

## Seal kit


Acting type	Rod packing		Piston packing		Cover ring		Piston gasket
	Double acting / Normally extended	Normally retruned	Double acting	Single acting	Double acting / Normally extended	Normally retruned	Double acting / Single acting
Q'y	1	0	1	1	1	0	1
ø12	KSYR-6	—	OPA-12	OPA-12	S-11	—	d4×w1
ø16	KSYR-8	—	OPA-16	OPA-16	S-14	—	d5×w1
ø20	KSYR-10A	—	OPA-20	OPA-20	S-18	—	d6×w1
ø25	KSYR-12	—	OPA-25	OPA-25	S-22,4	—	d8×w1
ø32	KSYR-16	—	OPA-32	OPA-32	S-28	—	S-9
ø40	KSYR-16	—	OPA-40	OPA-40	S-36	—	S-10
ø50	KSYR-20	—	OPA-50	OPA-50	S-46	—	S-16
ø63	KSYR-20	—	OPA-63	—	S-60	—	S-16
ø80	ORA-25	—	OPA-80	—	G-75	—	d20×w1
ø100	ORA-30	—	OPA-100	—	G-95	—	S-26

**Long stroke**



**Long stroke**

(with magnet)



### Long stroke – Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	Q'y	Component parts (inclusion)	Repair kits (inclusion)
1	Body	Aluminum alloy									1		
2	Rod cover	Aluminum alloy									1	●	
3	End cover	Aluminum alloy									1	●	
4	Piston rod	Carbor steel									1		
5	Piston	Aluminum alloy									1	●	
6	Rod packing	NBR									1	●	●
7	Snap ring	Stainless steel				Spring steel					2	●	
8	Cover ring	NBR									2	●	●
9	Piston bolt	Stainless steel				SCM					1	●	
10	Piston packing	NBR									1	●	●
11	Piston gasket	NBR									1	●	●
12	Cushion packing	NBR									2	●	●
13	Magnet	Magnet									1	●	
14	Wear ring	Resin									1	●	
15	Bush	—				Bearing alloy					1	●	

### Long stroke – Seal kit


Acting type	Rod packing	Piston packing	Cover ring	Piston gasket
Q'y	1	1	2	1
Double acting				
ø12	KSYR-6	OPA-12	S-11	d4×w1
ø16	KSYR-8	OPA-16	S-14	d5×w1
ø20	KSYR-10A	OPA-20	S-18	d6×w1
ø25	KSYR-12	OPA-25	S-22	d8×w1
ø32	KSYR-16	OPA-32	d28×w2	S-9
ø40	ORA-16	OPA-40	S-36	S-10
ø50	ORA-20	OPA-50	S-46	S-16
ø63	ORA-20	OPA-63	S-60	S-16
ø80	ORA-25	OPA-80	AS-41   G-75	d20×w1

### Order example

#### Component parts / Repair kits

Tube I.D.	Component parts	Repair kits
ø12	<b>CPL-MCJQ-12(M)</b>	<b>PSL-MCJQ-12</b>
ø16	<b>CPL-MCJQ-16(M)</b>	<b>PSL-MCJQ-16</b>
ø20	<b>CPL-MCJQ-20(M)</b>	<b>PSL-MCJQ-20</b>
ø25	<b>CPL-MCJQ-25(M)</b>	<b>PSL-MCJQ-25</b>
ø32	<b>CPL-MCJQ-32(M)</b>	<b>PSL-MCJQ-32</b>
ø40	<b>CPL-MCJQ-40(M)</b>	<b>PSL-MCJQ-40</b>
ø50	<b>CPL-MCJQ-50(M)</b>	<b>PSL-MCJQ-50</b>
ø63	<b>CPL-MCJQ-63(M)</b>	<b>PSL-MCJQ-63</b>
ø80	<b>CPL-MCJQ-80(M)</b>	<b>PSL-MCJQ-80</b>


M: With magnet




No.	Accessories	Material	Page link
1	Mounting accessories LB	Carbon steel	<a href="#">1</a> , <a href="#">2</a>
2	Mounting accessories FAC/FBC	Carbon steel	<a href="#">3</a> , <a href="#">4</a> , <a href="#">5</a> , <a href="#">6</a>
3	Mounting accessories CB+PIN	Cast iron / *	<a href="#">7</a> , <a href="#">8</a> , <a href="#">9</a>
4	Mounting accessories RF	Aluminum	<a href="#">10</a>
5	Floating joint MFC	Carbon steel	<a href="#">11</a>
6	Floating joint MFCS	Carbon steel	<a href="#">12</a>
7	Female rod ends PHS	Carbon steel	<a href="#">13</a>
8	Fitting PC (PISCO)	-	<a href="#">14</a>
9	Speed controller JSC (PISCO)	-	<a href="#">15</a>
10	Sensor switch RCE/RCE1	-	<a href="#">16</a> , <a href="#">17</a>
11	Sensor switch RDEP	-	<a href="#">18</a>

\* Material of PIN and  $\phi 12$ ,  $\phi 16$  CB accessories are carbon steel.


### 12




### 16




### 20



### 25



### 32



### 32



### 11 Male thread

Code Tube I.D.	C1	H1	L1 <sup>*1,2</sup>	L2 <sup>*1</sup>	X
12	9	M5×0.8	14 (24)	24	10.5
16	10	M6×1.0	15.5 (25.5)	25.5	12
20	12	M8×1.25	18.5 (28.5)	28.5	14
25	15	M10×1.25	22.5 (32.5)	32.5	17.5
32	20.5	M14×1.5	28.5 (38.5)	38.5	23.5

\*1. L1: Standard stroke, L2: Long stroke

\*2. ( ) Dimensions for piston rod extended "L" type.

### $\phi 12\sim 25$

Code Tube I.D.	Standard stroke						Long stroke																						
	Stroke range	Without magnet		Magnet		F	L <sup>*2</sup>	Stroke range	A	B	F	L	C	D	E	H	I	K	M	N	OA	OB	P	Q	RA	RB	Z1	Z2	Z3
		A	B	A	B																								
12	5~30	20.5	17	25.5	22	5	3.5 (13.5)	31~100	45.5	32	7.5	13.5	6	6	25	M3×0.5	32	5	15.5	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	4.2	6.3	0.5
16	5~30	20.5	17	25.5	22	5	3.5 (13.5)	31~100	45.5	32	7.5	13.5	8	8	29	M4×0.7	38	6	20	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	4.2	6.3	0.5
20	5~50	24	19.5	34	29.5	5.5	4.5 (14.5)	51~200	55.5	41	9	14.5	7	10	36	M5×0.8	47	8	25.5	5.5	M6×1.0	9	M5×0.8	9	10	7	6.2	8.8	1
25	5~50	27.5	22.5	37.5	32.5	5.5	5 (15)	51~300	59	44	11	15	12	12	40	M6×1.0	52	10	28	5.5	M6×1.0	9	M5×0.8	11	10	7	6.2	8.8	1

### $\phi 32$

Code Tube I.D.	Standard stroke							Long stroke																								
	Stroke range	Without magnet		Magnet		F	L <sup>*2</sup>	Stroke range	A	B	F	L	Q	P	C	D	E	H	I	J	JJ	K	M	N	OA	OB	RA	RB	Z1	Z2	Z3	
		A	B	A	B																											
32	5~50	30	23	40	33	7.5 <sup>*1</sup>	7 (17)	10.5 <sup>*1</sup>	101~300	62.5	45.5	12.5	17	12.5	*1 Rc1/8	13	16	45	M8×1.25	60	4.5	49.5	14	34	5.5	M6×1.0	9	10	7	6.2	8.8	1
	51~100	40	33	40	33	7.5	7 (17)	10.5																								







\*1. Without magnet with stroke=5mm, P=M5×0.8, Q=11.5, F=5.5

\*2. ( ) Dimensions for piston rod extended "L" type.

**12**
 $\phi 50\sim\phi 100$ 

Stroke 5~100

Stroke over 100


 $\phi 40$ 

 $\phi 40\sim\phi 100$   
(Stroke 5~100)

 $\phi 40\sim\phi 80$   
(Stroke over 100)

**11**
**Male thread**

Code Tube I.D.	C1	H1	L1 <sup>*1,2</sup>	L2 <sup>*1</sup>	X
40	20.5	M14×1.5	28.5 (38.5)	38.5	23.5
50	26	M18×1.5	33.5 (43.5)	43.5	28.5
63	26	M18×1.5	33.5 (43.5)	43.5	28.5
80	32.5	M22×1.5	43.5 (53.5)	53.5	35.5
100	32.5	M26×1.5	43.5 (53.5)	—	35.5

<sup>\*1.</sup> L1: Standard stroke, L2: Long stroke

<sup>\*2.</sup> ( ) Dimensions for piston rod extended "L" type.

Code Tube I.D.	Standard stroke								Long stroke					
	Stroke range	Without magnet		Magnet		F	L <sup>*4</sup>	Q	Stroke range	A	B	F	L	Q
		A	B	A	B									
40	5~50	36.5	29.5	46.5	39.5	8	7 (17)	11	125~300	72	55	14	17	14
	51~100	46.5	39.5	46.5	39.5	8	7 (17)	11	125~300	72	55	14	17	14
50	5~50	38.5	30.5	48.5	40.5	10.5 <sup>*1</sup>	8 (18)	10.5 <sup>*1</sup>	125~300	73.5	55.5	14	18	14
	51~100	48.5	40.5	48.5	40.5	10.5 <sup>*1</sup>	8 (18)	10.5 <sup>*1</sup>	125~300	73.5	55.5	14	18	14
63	5~50	44	36	54	46	10.5	8 (18)	15	125~300	75	57	16.5	18	16.5
	51~100	54	46	54	46	10.5	8 (18)	15	125~300	75	57	16.5	18	16.5
80	5~50	53.5	43.5	63.5	53.5	12.5	10 (20)	16	125~300	86	66	19	20	19
	51~100	63.5	53.5	63.5	53.5	12.5	10 (20)	16	125~300	86	66	19	20	19
100	5~50	65	53	75	63	13	12 (22)	23	—	—	—	—	—	—
	51~100	75	63	75	63	13	12 (22)	23	—	—	—	—	—	—

Code Tube I.D.	C	D	E	G <sup>h9</sup>	H	I	J	JJ	K	M	N	OA	OB	P	RA	RB	T	Z1	Z2	Z3
40	13	16	52	28 <sup>+0</sup> <sub>-0.052</sub>	M8×1.25	70	5	57	14	40	5.5	M6×1.0	9	Rc1/8	10	7	14	6.2	8.8	1
50	15	20	64	35 <sup>+0</sup> <sub>-0.062</sub>	M10×1.5	86	7	71	17	50	6.6	M8×1.25	11	Rc1/4 <sup>*1</sup>	14	8	19	8.2	10.8	1
63	15	20	77	35 <sup>+0</sup> <sub>-0.062</sub>	M10×1.5	103	7	84	17	60	9	M10×1.5	14	Rc1/4 <sup>*2</sup>	18	10.5	19	10.2	13.8	1
80	21	25	98	43 <sup>+0</sup> <sub>-0.062</sub>	M16×2.0	132	6	104	22	77	11	M12×1.75	17.5	Rc3/8 <sup>*3</sup>	22	13.5	26	12.2	17.3	2
100	27	30	117	—	M20×2.5	156	6.5	123.5	27	94	11	M12×1.75	17.5	Rc3/8 <sup>*3</sup>	22	13.5	26	12.2	17.3	2

<sup>\*1.</sup> Without magnet with stroke=5mm, P=Rc1/8, Q=12, F=8

<sup>\*2.</sup> Without magnet with stroke=5mm, P=Rc1/4

<sup>\*3.</sup> Without magnet with stroke=5mm, P=Rc1/4

<sup>\*4.</sup> ( ) Dimensions for piston rod extended "L" type.


## COMPACT CYLINDER

14

$\phi 12$

$\phi 16$


$\phi 20, \phi 25$




$\phi 32$

$\phi 40$

$\phi 50$



### 13 Male thread



Code Tube I.D.	C1	H1	L1*	X
12	9	M5×0.8	14 (24)	10.5
16	10	M6×1.0	15.5 (25.5)	12
20	12	M8×1.25	18.5 (28.5)	14
25	15	M10×1.25	22.5 (32.5)	17.5
32	20.5	M14×1.5	28.5 (38.5)	23.5
40	20.5	M14×1.5	28.5 (38.5)	23.5
50	26	M18×1.5	33.5 (43.5)	28.5

\* L1: Standard stroke

\* ( ) Dimensions for piston rod extended "L" type.

Note: The value B of  $\phi 12\sim\phi 40$  type is greater than double acting type.

Code Tube I.D.	Standard stroke				C	D	E	H	I	J	JJ	K	L <sup>*2</sup>	M	N	OA	OB	P	Q	RA	RB	T	Z1	Z2	Z3	
	Without magnet		Magnet																							
	A	B	A	B																						
12	5,10	30.5	27	35.5	32	6	6	25	M3×0.5	32	-	-	5	3.5 (13.5)	15.5	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	-	4.2	6.3	0.5
16	5,10	35.5	32	40.5	37	8	8	29	M4×0.7	38	-	-	6	3.5 (13.5)	20	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	-	4.2	6.3	0.5
20	5,10	34	29.5	44	39.5	7	10	36	M5×0.8	47	-	-	8	4.5 (14.5)	25.5	5.5	M6×1.0	9	M5×0.8	9	10	7	-	6.2	8.8	1
25	5,10	47.5	42.5	57.5	52.5	12	12	40	M6×1.0	52	-	-	10	5 (15)	28	5.5	M6×1.0	9	M5×0.8	11	10	7	-	6.2	8.8	1
32	5,10	55	48	65	58	13	16	45	M8×1.25	60	4.5	49.5	14	7 (17)	34	5.5	M6×1.0	9	Rc1/8	10.5	10	7	14	6.2	8.8	1
40	5,10	61.5	54.5	71.5	64.5	13	16	52	M8×1.25	70	5	57	14	7 (17)	40	5.5	M6×1.0	9	Rc1/8	11	10	7	14	6.2	8.8	1
50	5~20	38.5	30.5	48.5	40.5	15	20	64	M10×1.5	86	7	71	17	8 (18)	50	6.5	M8×1.25	11	Rc1/4 <sup>*1</sup>	10.5 <sup>*1</sup>	14	8	19	8.2	10.8	1

\*1. Without magnet with stroke=5mm, P=Rc1/8, Q=12


\*2. ( ) Dimensions for piston rod extended "L" type.

### 16

ø12

ø16


ø20, ø25




ø32

ø40

ø50





### 15 Male thread

Code Tube I.D.	C1	H1	L1*	X
12	9	M5×0.8	14 (24)	10.5
16	10	M6×1.0	15.5 (25.5)	12
20	12	M8×1.25	18.5 (28.5)	14
25	15	M10×1.25	22.5 (32.5)	17.5
32	20.5	M14×1.5	28.5 (38.5)	23.5
40	20.5	M14×1.5	28.5 (38.5)	23.5
50	26	M18×1.5	33.5 (43.5)	28.5

\* L1: Standard stroke  
\* ( ) Dimensions for piston rod extended "L" type.

Code Tube I.D.	Standard stroke				C	D	E	F	H	I	J	JJ	K	L <sup>*3</sup>	M	N	OA	OB	P	RA	RB	T	Z1	Z2	Z3	
	Without magnet		Magnet																							
	A	B	A	B																						
12	5,10	20.5	17	25.5	22	6	6	25	5	M3×0.5	32	–	–	5	3.5 (13.5)	15.5	3.5	M4×0.7	6.5	M5×0.8	7	4	–	4.2	6.3	0.5
16	5,10	20.5	17	25.5	22	8	8	29	5	M4×0.7	38	–	–	6	3.5 (13.5)	20	3.5	M4×0.7	6.5	M5×0.8	7	4	–	4.2	6.3	0.5
20	5,10	24	19.5	34	29.5	7	10	36	5.5	M5×0.8	47	–	–	8	4.5 (14.5)	25.5	5.5	M6×1.0	9	M5×0.8	10	7	–	6.2	8.8	1
25	5,10	27.5	22.5	37.5	32.5	12	12	40	5.5	M6×1.0	52	–	–	10	5 (15)	28	5.5	M6×1.0	9	M5×0.8	10	7	–	6.2	8.8	1
32	5,10	30	23	40	33	13	16	45	7.5 <sup>*1</sup>	M8×1.25	60	4.5	49.5	14	7 (17)	34	5.5	M6×1.0	9	Rc1/8 <sup>*1</sup>	10	7	14	6.2	8.8	1
40	5,10	36.5	29.5	46.5	39.5	13	16	52	8	M8×1.25	70	5	57	14	7 (17)	40	5.5	M6×1.0	9	Rc1/8	10	7	14	6.2	8.8	1
50	5~20	38.5	30.5	48.5	40.5	15	20	64	10.5 <sup>*2</sup>	M10×1.5	86	7	71	17	8 (18)	50	6.5	M8×1.25	11	Rc1/4 <sup>*2</sup>	14	8	19	8.2	10.8	1


\*1. Without magnet with stroke=5mm, P=M5×0.8, F=5.5

\*2. Without magnet with stroke=5mm, P=Rc1/8, F=8


\*3. ( ) Dimensions for piston rod extended "L" type.

## COMPACT CYLINDER


### Double acting




### Double acting (with magnet)



### Single acting



### Adjustable stroke



## Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	100	Q'y	Component parts (inclusion)	Repair kits (inclusion)
1	Body	Aluminum alloy										1		
2	Rod cover	Aluminum alloy										2	●	
3	Piston rod	With magnet	Stainless steel		Carbor steel						2			
		Without magnet	*1	Carbor steel									2	
4	Piston	Aluminum alloy										1	●	
5	Rod packing	NBR										2	●	●
6	Snap ring	Stainless steel				Spring steel						2	●	
7	Cover ring	NBR										2 *2	●	●
8	Piston packing	NBR										1	●	●
9	Piston gasket	NBR										1	●	●
10	Cushion packing	NBR										2	●	●
11	Magnet	Magnet										1	●	
12	Wear ring	—				Resin						1	●	
13	Bush	—				Bearing alloy						2	●	
14	Spring	SWP								—		1	●	
15	Adjustable nut	Carbor steel										1	●	
16	Hexagon nut	Carbor steel										1	●	
17	Cushion packing	PU										1	●	

\*1. Stainless steel

\*2. Single acting (Q'y=1 pc)

## Seal kit

Acting type	Rod packing		Piston packing		Cover ring		Piston gasket
	Double acting	Single acting	Double acting	Single acting	Double acting	Single acting	
Q'y	2	1	1	1	2	1	1
ø12	KSYR-6	KSYR-6	OPA-12	OPA-12	S-11	S-11	d4×w1
ø16	KSYR-8	KSYR-8	OPA-16	OPA-16	S-14	S-14	d6×w1
ø20	KSYR-10A	KSYR-10A	OPA-20	OPA-20	S-18	S-18	d6×w1
ø25	KSYR-12	KSYR-12	OPA-25	OPA-25	S-22	S-22	S-9
ø32	KSYR-16	KSYR-16	OPA-32	OPA-32	d28×w2	d28×w2	d11×w1
ø40	KSYR-16	KSYR-16	OPA-40	OPA-40	S-36	S-36	S-10
ø50	KSYR-20	KSYR-20	OPA-50	OPA-50	S-46	S-46	S-16
ø63	KSYR-20	—	OPA-63	—	S-60	—	S-14
ø80	ORA-25	—	OPA-80	—	G-75	—	d20×w1
ø100	ORA-30	—	OPA-100	—	G-95	—	S-24


## Order example

### Component parts / Repair kits


Tube I.D.	Component parts	Repair kits
ø12	CP-MCJQ-2-12(M)	PS-MCJQ-2-12
ø16	CP-MCJQ-2-16(M)	PS-MCJQ-2-16
ø20	CP-MCJQ-2-20(M)	PS-MCJQ-2-20
ø25	CP-MCJQ-2-25(M)	PS-MCJQ-2-25
ø32	CP-MCJQ-2-32(M)	PS-MCJQ-2-32
ø40	CP-MCJQ-2-40(M)	PS-MCJQ-2-40
ø50	CP-MCJQ-2-50(M)	PS-MCJQ-2-50
ø63	CP-MCJQ-2-63(M)	PS-MCJQ-2-63
ø80	CP-MCJQ-2-80(M)	PS-MCJQ-2-80
ø100	CP-MCJQ-2-100(M)	PS-MCJQ-2-100

M: With magnet


### Double acting



### Double acting (with magnet)



### Adjustable stroke



## Long stroke – Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	Q'y	Component parts (inclusion)	Repair kits (inclusion)	
1	Body	Aluminum alloy									1			
2	Rod cover	Aluminum alloy									2	●		
3	Piston With magnet	Stainless steel			Carbor steel					2				
	rod Without magnet	*1	Carbor steel									2		
4	Piston	Aluminum alloy									2	●		
5	Rod packing	NBR									2	●	●	
6	Snap ring	Stainless steel			Spring steel					2	●			
7	Cover ring	NBR									2	●	●	
8	Piston packing	NBR									1	●	●	
9	Piston gasket	NBR									1	●	●	
10	Cushion packing	–	NBR									2	●	●
11	Magnet	Magnet									1	●		
12	Wear ring	–			Resin					1	●			
13	Bush	–			Bearing alloy					2	●			
14	Sub-piston	–	PU		Aluminum alloy					1	●			
15	Sub-piston gasket	–			NBR					1	●	●		
16	Adjust nut	Carbor steel									1	●		
17	Hexagon nut	Carbor steel									1	●		
18	Cushion gasket	PU									1	●		

\*1. Stainless steel

## Long stroke – Seal kit

Acting type	Rod packing	Piston packing	Cover ring	Piston gasket	Sub-piston gasket
Q'y	2	1	2	1	1
Double acting					
ø12	KSYR-6	OPA-12	S-11	d4×w1	–
ø16	KSYR-8	OPA-16	S-14	d5×w1	–
ø20	KSYR-10A	OPA-20	S-18	d6×w1	–
ø25	KSYR-12	OPA-25	S-22	S-9	–
ø32	KSYR-16	OPA-32	d28×w2	d11×w1	P-16
ø40	ORA-16	OPA-40	S-36	S-10	P-16
ø50	ORA-20	OPA-50	S-46	S-16	P-20
ø63	ORA-20	OPA-63	S-60	S-14	P-20
ø80	ORA-25	OPA-80	G-75	S-18	S-25

## Order example



### Component parts / Repair kits

Tube I.D.	Component parts	Repair kits
ø12	CPL-MCJQ-2-12(M)	PSL-MCJQ-2-12
ø16	CPL-MCJQ-2-16(M)	PSL-MCJQ-2-16
ø20	CPL-MCJQ-2-20(M)	PSL-MCJQ-2-20
ø25	CPL-MCJQ-2-25(M)	PSL-MCJQ-2-25
ø32	CPL-MCJQ-2-32(M)	PSL-MCJQ-2-32
ø40	CPL-MCJQ-2-40(M)	PSL-MCJQ-2-40
ø50	CPL-MCJQ-2-50(M)	PSL-MCJQ-2-50
ø63	CPL-MCJQ-2-63(M)	PSL-MCJQ-2-63
ø80	CPL-MCJQ-2-80(M)	PSL-MCJQ-2-80

M: With magnet

## COMPACT CYLINDER


22



$\phi 12\sim 25$

$\phi 32$  for stroke 5~100     $\phi 32$  for stroke over 100

21 Male thread



Code Tube I.D.	C1	H1	L1 <sup>*1,2</sup>	L2 <sup>*1</sup>	X
12	9	M5×0.8	14 (24)	24	10.5
16	10	M6×1.0	15.5 (25.5)	25.5	12
20	12	M8×1.25	18.5 (28.5)	28.5	14
25	15	M10×1.25	22.5 (32.5)	32.5	17.5
32	20.5	M14×1.5	28.5 (38.5)	38.5	23.5


\*1. L1: Standard stroke, L2: Long stroke  
 \*2. ( ) Dimensions for L type that both sides piston rod are extended.  
 For LA type that single side piston rod is extended.

Code Tube I.D.	Standard stroke					Long stroke																							
	Stroke range	Without magnet		Magnet		L <sup>*2</sup>	Stroke range	A	B	L	C	D	E	H	I	J	JJ	K	M	N	OA	OB	P	Q	RA	RB	Z1	Z2	Z3
		A	B	A	B																								
12	5~30	29	22	34	27	3.5 (13.5)	31~100	59	32	13.5	6	6	25	M3×0.5	32	-	-	5	15.5	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	4.2	6.3	0.5
16	5~30	29	22	34	27	3.5 (13.5)	31~100	59	32	13.5	8	8	29	M4×0.7	38	-	-	6	20	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	4.2	6.3	0.5
20	5~50	35	26	45	36	4.5 (14.5)	51~200	70	41	14.5	7	10	36	M5×0.8	47	-	-	8	25.5	5.5	M6×1.0	9	M5×0.8	9	10	7	6.2	8.8	1
25	5~50	39	29	49	39	5 (15)	51~300	74	44	15	12	12	40	M6×1.0	52	-	-	10	28	5.5	M6×1.0	9	M5×0.8	11	10	7	6.2	8.8	1
32	5~50	44.5	30.5	54.5	40.5	7 (17)	101~300	79.5	45.5	17	13	16	45	M8×1.25	60	4.5	49.5	14	34	5.5	M6×1.0	9	Rc1/8 <sup>*1</sup>	12.5	10	7	6.2	8.8	1
	51~100	54.5	40.5	54.5	40.5	7 (17)																							

\*1. Without magnet with stroke=5mm, P=M5×0.8  
 \*2. ( ) dimensions for L type that both sides piston rod are extended.  
 For LA type that single side piston rod is extended.




24




$\phi 32$

$\phi 40$

$\phi 50$



### 23 Male thread



Code Tube I.D.	C1	H1	L1*	X
12	9	M5×0.8	14 (24)	10.5
16	10	M6×1.0	15.5 (25.5)	12
20	12	M8×1.25	18.5 (28.5)	14
25	15	M10×1.25	22.5 (32.5)	17.5
32	20.5	M14×1.5	28.5 (38.5)	23.5
40	20.5	M14×1.5	28.5 (38.5)	23.5
50	26	M18×1.5	33.5 (43.5)	28.5

\* L1: Standard stroke  
 \* ( ) Dimensions for L type that both sides piston rod are extended.  
 For LA type that piston rod retracted side is extended.



Code Tube I.D.	Standard stroke						C	D	E	H	I	J	JJ	K	L*2	M	N	OA	OB	P	Q	RA	RB	T	Z1	Z2	Z3
	Stroke range		Without magnet		Magnet																						
	A	B	A	B	A	B																					
12	5,10	29	22	34	27	6	6	25	M3×0.5	32	-	-	5	3.5 (13.5)	15.5	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	-	4.2	6.3	0.5	
16	5,10	29	22	34	27	8	8	29	M4×0.7	38	-	-	6	3.5 (13.5)	20	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	-	4.2	6.3	0.5	
20	5,10	35	26	45	36	7	10	36	M5×0.8	47	-	-	8	4.5 (14.5)	25.5	5.5	M6×1.0	9	M5×0.8	9	10	7	-	6.2	8.8	1	
25	5,10	39	29	49	39	12	12	40	M6×1.0	52	-	-	10	5 (15)	28	5.5	M6×1.0	9	M5×0.8	11	10	7	-	6.2	8.8	1	
32	5,10	44.5	30.5	54.5	40.5	13	16	45	M8×1.25	60	4.5	49.5	14	7 (17)	34	5.5	M6×1.0	9	Rc1/8*1	12.5	10	7	14	6.2	8.8	1	
40	5,10	54	40	64	50	13	16	52	M8×1.25	70	5	57	14	7 (17)	40	5.5	M6×1.0	9	Rc1/8	14	10	7	14	6.2	8.8	1	
50	5~20	56.5	40.5	66.5	50.5	15	20	64	M10×1.5	86	7	71	17	8 (18)	50	6.5	M8×1.25	11	Rc1/4	14	14	8	19	8.2	10.8	1	

\*1. Without magnet with stroke=5mm, P=M5×0.8

\*2. ( ) Dimensions for L type that both sides piston rod are extended. For LA type that piston rod retracted side is extended.

## COMPACT CYLINDER

28




\* ADJ: Adjustable stroke

$\phi 12 \sim 25$

$\phi 32$  for stroke 5~100

$\phi 32$  for stroke over 100

27 Male thread



Code Tube I.D.	C1	H1	L1 <sup>*1,2</sup>	L2 <sup>*1</sup>	X
12	9	M5×0.8	14 (24)	24	10.5
16	10	M6×1.0	15.5 (25.5)	25.5	12
20	12	M8×1.25	18.5 (28.5)	28.5	14
25	15	M10×1.25	22.5 (32.5)	32.5	17.5
32	20.5	M14×1.5	28.5 (38.5)	38.5	23.5

\*1. L1: Standard stroke, L2: Long stroke  
\*2. ( ) Dimensions for piston rod extended "LA" type.

Code Tube I.D.	Standard stroke						Long stroke					
	Stroke range	Without magnet		Magnet		L <sup>*2</sup>	W	Stroke range	A	B	L	W
		A	B	A	B							
12	5~30	45.5	22	50.5	27	3.5 (13.5)	20	31~100	65.5	32	13.5	20
16	5~30	49	22	54	27	3.5 (13.5)	23.5	31~100	69	32	13.5	23.5
20	5~50	54.3	26	64.3	36	4.5 (14.5)	23.8	51~200	79.3	41	14.5	23.8
25	5~50	56.5	29	66.5	39	5 (15)	22.5	51~300	81.5	44	15	22.5
32	5~50	60.9	30.5	70.9	40.5	7 (17)	23.4	101~300	91.5	45.5	17	29
	51~100	70.9	40.5									

Code Tube I.D.	C	D	E	H	I	J	JJ	K	M	N	OA	OB	P	Q
12	6	6	25	M3×0.5	32	-	-	5	15.5	3.5	M4×0.7	6.5	M5×0.8	7.5
16	8	8	29	M4×0.7	38	-	-	6	20	3.5	M4×0.7	6.5	M5×0.8	7.5
20	7	10	36	M5×0.8	47	-	-	8	25.5	5.5	M6×1.0	9	M5×0.8	9
25	12	12	40	M6×1.0	52	-	-	10	28	5.5	M6×1.0	9	M5×0.8	11
32	13	16	45	M8×1.25	60	4.5	49.5	14	34	5.5	M6×1.0	9	Rc1/8 <sup>*1</sup>	12.5

Code Tube I.D.	RA	RB	U	V	W1	X	XA	Y	Y1	Z1	Z2	Z3
12	7	4	M5×0.8	12	16	4	8	13	2	4.2	6.3	0.5
16	7	4	M8×1.25	16	19	5	13	15	2	4.2	6.3	0.5
20	10	7	M8×1.25	16	19	5	13	15	2	6.2	8.8	1
25	10	7	M10×1.25	20	18	6	17	12	2	6.2	8.8	1
32	10	7	M12×1.25	30	19	7	19	12	2	6.2	8.8	1


\*1. Without magnet with stroke=5mm, P=M5×0.8  
\*2. ( ) Dimensions for piston rod extended "LA" type.

28


$\phi 50\sim\phi 100$

Stroke 5~100

Stroke over 100




$\phi 40$



$\phi 40\sim\phi 100$   
(Stroke 5~100)

$\phi 40\sim\phi 80$   
(Stroke over 100)



27 Male thread

Code Tube I.D.	C1	H1	L1 <sup>*1,2</sup>	L2 <sup>*1</sup>	X
40	20.5	M14×1.5	28.5 (38.5)	38.5	23.5
50	26	M18×1.5	33.5 (43.5)	43.5	28.5
63	26	M18×1.5	33.5 (43.5)	43.5	28.5
80	32.5	M22×1.5	43.5 (53.5)	53.5	35.5
100	32.5	M26×1.5	43.5 (53.5)	—	35.5

\*1. L1: Standard stroke, L2: Long stroke  
\*2. ( ) Dimensions for piston rod extended "LA" type.


Code Tube I.D.	Standard stroke								Long stroke					
	Stroke range	Without magnet		Magnet		L <sup>*3</sup>	Q	W	Stroke range	A	B	L	Q	W
		A	B	A	B									
40	5~50	71	40	81	50	7 (17)	14	24	101~300	102.5	55	17	14	30.5
	51~100	81	50											
50	5~50	75	40.5	85	50.5	8 (18)	14	26.5	101~300	105.5	55.5	18	14	32
	51~100	85	50.5											
63	5~50	80	42	90	52	8 (18)	15.5	30	101~300	110	57	18	16.5	35
	51~100	90	52											
80	5~50	100	51	110	61	10 (20)	18	39	101~300	130	66	20	19	44
	51~100	110	61											
100	5~50	111	60.5	121	70.5	12 (22)	22	38.5	—	—	—	—	—	—
	51~100	121	70.5											

Code Tube I.D.	C	D	E	G <sup>H9</sup>	H	I	J	JJ	K	M	N	OA	OB	P	RA	RB	T	U	V	W1	X	XA	Y	Y1	Z1	Z2	Z3
40	13	16	52	28 <sup>+0 -0.052</sup>	M8×1.25	70	5	57	14	40	5.5	M6×1.0	9	Rc1/8	10	7	14	M12×1.25	30	21	7	19	12	2	6.2	8.8	1
50	15	20	64	35 <sup>+0 -0.062</sup>	M10×1.5	86	7	71	17	50	6.6	M8×1.25	11	Rc1/4	14	8	19	M16×1.5	40	22.5	8	24	15	2	8.2	10.8	1
63	15	20	77	35 <sup>+0 -0.062</sup>	M10×1.5	103	7	84	17	60	9	M10×1.5	14	Rc1/4 <sup>*1</sup>	18	10.5	19	M16×1.5	40	25.5	8	24	15	2	10.2	13.8	1
80	21	25	98	43 <sup>+0 -0.062</sup>	M16×2.0	132	6	104	22	77	11	M12×1.75	17.5	Rc3/8 <sup>*2</sup>	22	13.5	26	M22×1.5	50	33	13	32	20	3	12.2	17.3	2
100	27	30	117	—	M20×2.5	156	6.5	123.5	27	94	11	M12×1.75	17.5	Rc3/8 <sup>*2</sup>	22	13.5	26	M22×1.5	50	33	13	32	20	3	12.2	17.3	2

\*1. Without magnet with stroke=5mm, P=Rc1/8  
\*2. Without magnet with stroke=5mm, P=Rc1/4  
\*3. ( ) Dimensions for piston rod extended "LA" type.

## COMPACT CYLINDER


### Dimensions



### Installation of sensor switch

$\phi 12 \sim \phi 40$

$\phi 50 \sim \phi 100$



### Order example

RCE1 — □

MODEL

RCE / RCE1 (C: Reed switch)

RNE (N: Solid state switch)

RDEP (Solid state switch)

WIRE LENGTH

1M: L=1000m

2M: L=2000m

QD: M8 3Pin connector


EQD: M8 3Pin connector

### Description

▼ RCE, RCE1, RDEP\* switch ↓ Port


\* RDEP not suitable for  $\phi 20$ ,  $\phi 32$ .

\*  $\phi 12$ ,  $\phi 16$  only applicable to RDE, RDE1E, RDEP




COMPACT CYLINDER


LB



Female thread




Male thread




Code	Standard stroke							Long stroke														
	Stroke range	Without magnet			Magnet			Stroke range	A	B	LS	L	L1	LD	LG	LH	LT	LX	LY	LZ	X	Y
		A	B	LS	A	B	LS															
12	5~30	35.3	17	5	40.3	22	10	35~100	50.3	32	20	13.5	24	4.5	2.8	17	2	34	29.5	44	8	4.5
16	5~30	35.3	17	5	40.3	22	10	35~100	50.3	32	20	13.5	25.5	4.5	2.8	19	2	38	33.5	48	8	5
20	5~50	41.2	19.5	7.5	51.2	29.5	17.5	75~200	62.7	41	29	14.5	28.5	6.6	4	24	3.2	48	42	62	9.2	5.8
25	5~50	44.7	22.5	7.5	54.7	32.5	17.5	75~300	66.2	44	29	15	32.5	6.6	4	26	3.2	52	46	66	10.7	5.8


FAC



Female thread



Male thread




Code	Standard stroke					Long stroke										
	Stroke range	Without magnet		Magnet		Stroke range	A	B	FD	FT	FV	FX	FZ	L	L1	
		A	B	A	B											
12	5~30	30.5	17	35.5	22	35~100	45.5	32	4.5	5.5	25	45	55	13.5	24	
16	5~30	30.5	17	35.5	22	35~100	45.5	32	4.5	5.5	30	45	55	13.5	25.5	
20	5~50	34	19.5	44	29.5	75~200	55.5	41	6.6	8	39	48	60	14.5	28.5	
25	5~50	37.5	22.5	47.5	32.5	75~300	59	44	6.6	8	42	52	64	15	32.5	



## COMPACT CYLINDER

### FBC

Male thread




Female thread




Code	Standard stroke										Long stroke				FD	FT	FV	FX	FZ
	Stroke range	Without magnet				Magnet				Stroke range	A	B	L	L1					
		A	B	L	L1	A	B	L	L1										
12	5~30	26	17	3.5	14	31	22	3.5	14	35~100	51	32	13.5	24	4.5	5.5	25	45	55
16	5~30	26	17	3.5	15.5	31	22	3.5	15.5	35~100	51	32	13.5	25.5	4.5	5.5	30	45	55
20	5~50	32	19.5	4.5	18.5	42	29.5	4.5	18.5	75~200	63.5	41	14.5	28.5	6.6	8	39	48	60
25	5~50	35.5	22.5	5	22.5	45.5	32.5	5	22.5	75~300	67	44	15	32.5	6.6	8	42	52	64

### CB

Male thread




Female thread




Code	Standard stroke										Long stroke						CD	CT	CU	CW	CX	CZ	RR	
	Stroke range	Without magnet				Magnet				Stroke range	A	B	CL	L	L1									
		A	B	CL	L	L1	A	B	CL							L								L1
12	5~30	40.5	17	34.5	3.5	14	45.5	22	39.5	3.5	14	35~100	65.5	32	59.5	13.5	24	5	4	7	14	5	10	6
16	5~30	41.5	17	35.5	3.5	15.5	46.5	22	40.5	3.5	15.5	35~100	66.5	32	60.5	13.5	25.5	5	4	10	15	6.5	12	6
20	5~50	51	19.5	42	4.5	18.5	61	29.5	52	4.5	18.5	75~200	82.5	41	73.5	14.5	28.5	8	5	12	18	8	16	9
25	5~50	57.5	22.5	47.5	5	22.5	67.5	32.5	57.5	5	22.5	75~300	89	44	79	15	32.5	10	5	14	20	10	20	10

**LB**


Standard stroke



Female thread




Male thread




Long stroke

Female thread



Male thread






Code	Standard stroke							Long stroke				L	L1	LD	LG	LH	LT	LX	LY	LZ	X	Y
	Stroke range	Without magnet			Magnet			Stroke range	A	B	LS											
A		B	LS	A	B	LS																
32	5~50	47.2	23	7	57.2	33	17	125~300	69.7	45.5	29.5	17	38.5	6.6	4	30	3.2	57	57	71	11.2	5.8
	75,100	57.2	33	17																		
40	5~50	53.7	29.5	13.5	63.7	39.5	23.5	125~300	79.2	55	39	17	38.5	6.6	4	33	3.2	64	64	78	11.2	7
	75,100	63.7	39.5	23.5																		
50	5~50	56.7	30.5	7.5	66.7	40.5	17.5	125~300	81.7	55.5	32.5	18	43.5	9	5	39	3.2	79	78	95	14.7	8
	75,100	66.7	40.5	17.5																		
63	5~50	62.2	36	10	72.2	46	20	125~300	83.2	57	31	18	43.5	11	5	46	3.2	95	91.5	113	16.2	9
	75,100	72.2	46	20																		
80	5~50	75	43.5	13.5	85	53.5	23.5	125~300	97.5	66	36	20	53.5	13	7	59	4.5	118	114	140	19.5	11
	75,100	85	53.5	23.5																		
100	5~50	88	53	19	98	63	29	125~300	—	—	—	22	53.5	13	7	71	6	137	136	162	23	12.5
	75,100	98	63	29																		

**FAC**

Female thread

Male thread






Code	Standard stroke					Long stroke		FD	FT	FV	FX	FZ	L	L1	M	
	Stroke range	Without magnet		Magnet		Stroke range	A									B
		A	B	A	B											
32	5~50	40	23	50	33	125~300	62.5	45.5	5.5	8	48	56	65	17	38.5	34
	75,100	50	33													
40	5~50	46.5	29.5	56.5	39.5	125~300	72	55	5.5	8	54	62	72	17	38.5	40
	75,100	56.5	39.5													
50	5~50	48.5	30.5	58.5	40.5	125~300	73.5	55.5	6.6	9	67	76	89	18	43.5	50
	75,100	58.5	40.5													
63	5~50	54	36	64	46	125~300	75	57	9	9	80	92	108	18	43.5	60
	75,100	64	46													
80	5~50	63.5	43.5	73.5	53.5	125~300	86	66	11	11	99	116	134	20	53.5	77
	75,100	73.5	53.5													
100	5~50	75	53	85	63	125~300	-	-	11	11	117	136	154	22	53.5	94
	75,100	85	63													

**FBC**

Standard stroke

Male thread



Female thread



Long stroke

Male thread

Female thread




Code	Standard stroke							Long stroke					FD	FT	FV	FX	FZ	M
	Stroke range	Without magnet		Magnet		L	L1	Stroke range	A	B	L	L1						
		A	B	A	B													
32	5~50	38	23	48	33	7	28.5	125~300	70.5	45.5	17	38.5	5.5	8	48	56	65	34
	75,100	48	33															
40	5~50	44.5	29.5	54.5	39.5	7	28.5	125~300	80	55	17	38.5	5.5	8	54	62	72	40
	75,100	54.5	39.5															
50	5~50	47.5	30.5	57.5	40.5	8	33.5	125~300	82.5	55.5	18	43.5	6.6	9	67	76	89	50
	75,100	57.5	40.5															
63	5~50	53	36	63	46	8	33.5	125~300	84	57	18	43.5	9	9	80	92	108	60
	75,100	63	46															
80	5~50	64.5	43.5	74.5	53.5	10	43.5	125~300	97	66	20	53.5	11	11	99	116	134	77
	75,100	74.5	53.5															
100	5~50	76	53	86	63	12	43.5	125~300	-	-	-	-	11	11	117	136	154	94
	75,100	86	63															

CB

Standard stroke

Male thread


Female thread



Long stroke


Male thread

Female thread




Code	Standard stroke									Long stroke													
	Stroke range	Without magnet			Magnet			L	L1	Stroke range	A	B	CL	L	L1	CD	CT	CU	CW	CX	CZ	N	RR
		A	B	CL	A	B	CL																
32	5~50	60	23	50	70	33	60	7	28.5	125~300	92.5	45.5	82.5	17	38.5	10	5	14	20	18	36	M6×1.0	10
	75,100	70	33	60																			
40	5~50	68.5	29.5	58.5	78.5	39.5	68.5	7	28.5	125~300	104	55	94	17	38.5	10	6	14	22	18	36	M6×1.0	10
	75,100	78.5	39.5	68.5																			
50	5~50	80.5	30.5	66.5	90.5	40.5	76.5	8	33.5	125~300	115.5	55.5	101.5	18	43.5	14	7	20	28	22	44	M8×1.25	14
	75,100	90.5	40.5	76.5																			
63	5~50	88	36	74	98	46	84	8	33.5	125~300	119	57	105	18	43.5	14	8	20	30	22	44	M10×1.5	14
	75,100	98	46	84																			
80	5~50	109.5	43.5	91.5	119.5	53.5	101.5	10	43.5	125~300	142	66	124	20	53.5	18	10	27	38	28	56	M12×1.75	18
	75,100	119.5	53.5	101.5																			
100	5~50	132	53	110	142	63	120	12	43.5	125~300	-	-	-	-	22	13	31	45	32	64	M12×1.75	22	
	75,100	142	63	120																			

**F** Rear flange




Code Tube I.D.	P2 <sup>h9</sup>	S2
12	6	1.5
16	10	1.5
20	13	2
25	15	2
32	21	2
40	28	2
50	35	2
63	35	2
80	43	2
100	59	2

**RF**




Code Tube I.D.	P1 <sup>h9</sup>	S1
12	15	1.5
16	20	1.5
20	13	2
25	15	2
32	21	2
40	28	2
50	35	2
63	35	2
80	43	2
100	59	2

**Rod front nut**



Code Tube I.D.	A	B	C	D
12	4	8	9.2	M5×0.8
16	5	10	11.5	M6×1.0
20	5	13	15	M8×1.25
25	6	17	19.6	M10×1.25
32,40	8	22	25.4	M14×1.5
50,63	11	27	31.4	M18×1.5
80	13	32	37	M22×1.5
100	16	41	47.3	M26×1.5

**Pin** for CB









Code Tube I.D.	A	B	C	$\varnothing D^{g9}$	$\varnothing d$	E	Snap ring
12	14.6	10.2	2.2	5 <sup>-0.03</sup> <sub>-0.06</sub>	4.8 <sup>0</sup> <sub>-0.04</sub>	0.7 <sup>+0.10</sup> <sub>0</sub>	STW-5
16	16.6	12.2	2.2	5 <sup>-0.03</sup> <sub>-0.06</sub>	4.8 <sup>0</sup> <sub>-0.04</sub>	0.7 <sup>+0.10</sup> <sub>0</sub>	STW-5
20	21	16.2	2.4	8 <sup>-0.04</sup> <sub>-0.08</sub>	7.6 <sup>0</sup> <sub>-0.06</sub>	0.9 <sup>+0.10</sup> <sub>0</sub>	STW-8
25	25.6	20.2	2.7	10 <sup>-0.04</sup> <sub>-0.08</sub>	9.6 <sup>0</sup> <sub>-0.06</sub>	1.15 <sup>+0.14</sup> <sub>0</sub>	STW-10
32,40	41.6	36.2	2.7	10 <sup>-0.04</sup> <sub>-0.08</sub>	9.6 <sup>0</sup> <sub>-0.09</sub>	1.15 <sup>+0.14</sup> <sub>0</sub>	STW-10
50,63	50.6	44.2	3.2	14 <sup>-0.05</sup> <sub>-0.10</sub>	13.4 <sup>0</sup> <sub>-0.11</sub>	1.15 <sup>+0.14</sup> <sub>0</sub>	STW-14
80	64	56.2	3.9	18 <sup>-0.05</sup> <sub>-0.10</sub>	17.0 <sup>0</sup> <sub>-0.11</sub>	1.35 <sup>+0.14</sup> <sub>0</sub>	STW-18
100	72	64.2	3.9	22 <sup>-0.07</sup> <sub>-0.12</sub>	21.0 <sup>0</sup> <sub>-0.21</sub>	1.35 <sup>+0.14</sup> <sub>0</sub>	STW-22

### Cylinder weight







#### Standard stroke

Unit: g

Model		Basic weight MCJQ-11	Basic weight (magnet) MCJQ-11	Stroke 5 mm MCJQ-11	Basic weight MCJQ-12	Basic weight (magnet) MCJQ-12	Stroke 5 mm MCJQ-12
Tube I.D.	Stroke range (mm)						
$\phi 12$	5~30	22	31	7	19	28	7
$\phi 16$	5~30	33	42	8	28	37	8
$\phi 20$	5~50	55	82	13	48	75	13
$\phi 25$	5~50	92	140	16	75	123	16
$\phi 32$	5~50	129	215	22	109	166	22
	51~100	206	215	22	157	166	22
$\phi 40$	5~50	226	315	24	184	266	24
	51~100	298	315	24	249	266	24
$\phi 50$	5~50	367	500	35	317	409	35
	51~100	476	500	35	386	409	35
$\phi 63$	5~50	530	714	41	446	622	41
	51~100	685	714	41	594	622	41
$\phi 80$	5~50	1032	1278	65	904	1109	65
	51~100	1240	1278	65	1072	1109	65
$\phi 100$	5~50	1864	2278	90	1679	2030	90
	51~100	2230	2278	90	1982	2030	90








#### Long stroke

Unit: g

Model		Basic weight MCJQ-11	Basic weight (magnet) MCJQ-11	Stroke 5 mm MCJQ-11	Basic weight MCJQ-12	Basic weight (magnet) MCJQ-12	Stroke 5 mm MCJQ-12
Tube I.D.	Stroke range (mm)						
$\phi 12$	31~100	46	47	7	43	44	7
$\phi 16$	31~100	68	70	8	63	65	8
$\phi 20$	51~200	116	120	13	106	110	13
$\phi 25$	51~300	172	180	16	153	161	16
$\phi 32$	101~300	287	295	22	238	247	22
$\phi 40$	101~300	409	426	24	360	377	24
$\phi 50$	101~300	658	682	35	566	589	35
$\phi 63$	101~300	852	881	41	760	789	41
$\phi 80$	101~300	1531	1568	65	1398	1436	65

#### Accessories weight

Unit: g

Model	LB	CB	FAC/FBC	F	RF	Pin	Nut
Tube I.D.							
$\phi 12$	51	31	56	1	1	2	1
$\phi 16$	60	37	67	2	1	3	2
$\phi 20$	145	61	135	3	1	8	4
$\phi 25$	166	94	153	4	2	16	6
$\phi 32$	107	136	165	9	3	25	18
$\phi 40$	125	171	203	17	9	25	18
$\phi 50$	209	331	357	28	16	61	32
$\phi 63$	296	538	547	52	30	61	32
$\phi 80$	586	1034	1046	107	52	127	56
$\phi 100$	960	1765	1328	175	82	214	56

# MCJQ Multiple position series

## COMPACT CYLINDER



Special spec




Rod end shape



Technical data



Caution for safety  
(Read before installing)



### Features

Two-stage stroke: Two compact cylinders with same I.D. but different strokes length are connected to achieve two-stage stroke.

### Specification


Model	MCJQ-3*									
Acting type	Double acting									
Tube I.D. (mm)	12	16	20	25	32	40	50	63	80	100
Port size	M5×0.8			Rc1/8		Rc1/4		Rc3/8		
Medium	Air									
Operating pressure range (MPa)	0.07~1		0.05~1							
Proof pressure	1.5 MPa									
Ambient temperature	-5°C~+60°C (No freezing)									
Available speed range	50~500 mm/sec									
Sensor switch (*2)	RCE, RCE1 (*1)	(*)	●	●	●	●	●	●	●	●
	RDEP	●	●	-	●	-	●	●	●	●

\*1.  $\phi 12$ ,  $\phi 16$ : only applicable to RDE and RDE1E.

\*2. RCE , RCE1 , RDEP  specification.

### Order example

**MCJQ – 32 – 20 – 10×25 M – F – G**




\* The total stroke must be greater than the first stroke.

### Double acting – Table for standard stroke


Tube I.D.	Stroke 1		Stroke2	
	Standard stroke	Standard stroke	Long stroke (mm)	
$\phi 12, 16$	5, 10, 15, 20, 25, 30	5, 10, 15, 20, 25, 30	35, 40, 45, 50, 75, 100	
$\phi 20$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50	5, 10, 15, 20, 25, 30, 35, 40, 45, 50	75, 100, 125, 150, 175, 200	
			75, 100, 125, 150, 175, 200, 250, 300	
$\phi 32 \sim 80$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100	5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 75, 100	125, 150, 175, 200, 250, 300	
			-	

\* Please contact us if the stroke is out of specification.


### Flat washer kits



### Double acting



### Double acting (with magnet)



### Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	100	Q'y	Component parts (inclusion)	Repair kits (inclusion)
1	Body #1, #2	Aluminum alloy										1		
2	Rod cover	Aluminum alloy										1	●	
3	End cover	Aluminum alloy										1	●	
4	Center cover	Aluminum alloy										1	●	
5	Piston	Aluminum alloy										2	●	
6		Aluminum alloy										2	●	
7	Piston rod #1, #2	Carbor steel										1		
8	Magnet ring	Magnet										2	●	
9	Wear ring	—				Resin						2	●	
10	Piston packing	NBR										2	●	●
11	Rod packing	NBR										2	●	●
12	Cover ring	NBR										3	●	●
13	Piston gasket	NBR										2	●	●
14	Cushion packing	NBR										2	●	●
15	Cushion packing	NBR										2	●	●
16	Bush #1	—				Bearing alloy						1	●	
17	Bush #2	—				Bearing alloy						1	●	
18	Snap ring	Stainless steel					Spring steel					1	●	
19	Piston bolt	Stainless steel					SCM					2	●	
20	Bolt	SUS		SCM								2		
21	Silencer	Brass										1	●	

### Order example Component parts


Tube I.D.	Component parts
ø12	CP-MCJQ-3-12(M)
ø16	CP-MCJQ-3-16(M)
ø20	CP-MCJQ-3-20(M)
ø25	CP-MCJQ-3-25(M)
ø32	CP-MCJQ-3-32(M)
ø40	CP-MCJQ-3-40(M)
ø50	CP-MCJQ-3-50(M)
ø63	CP-MCJQ-3-63(M)
ø80	CP-MCJQ-3-80(M)
ø100	CP-MCJQ-3-100(M)

M: With magnet


### Repair kits

Tube I.D.	Repair kits
ø12	PS-MCJQ-3-12
ø16	PS-MCJQ-3-16
ø20	PS-MCJQ-3-20
ø25	PS-MCJQ-3-25
ø32	PS-MCJQ-3-32
ø40	PS-MCJQ-3-40
ø50	PS-MCJQ-3-50
ø63	PS-MCJQ-3-63
ø80	PS-MCJQ-3-80
ø100	PS-MCJQ-3-100

### Double acting



### Double acting (with magnet)



### Material

No.	Tube I.D. Part name	12	16	20	25	32	40	50	63	80	Q'y	Component parts (inclusion)	Repair kits (inclusion)
1	Body #1, #2	Aluminum alloy									1		
2	Rod cover	Aluminum alloy									1	●	
3	End cover	Aluminum alloy									1	●	
4	Center cover	Aluminum alloy									1	●	
5	Piston #1, #2	Aluminum alloy									1	●	
6	Piston #1 With magnet	Aluminum alloy									1	●	
7	Piston #2 With magnet	Aluminum alloy									1	●	
8	Piston rod #1, #2	Carbor steel									1		
9	Magnet ring	Magnet									2	●	
10	Wear ring #1	Resin									1	●	
11	Wear ring #2	Resin									1	●	
12	Piston packing	NBR									2	●	●
13	Rod packing #1, #2	NBR									1	●	●
14	Cover ring	NBR									3	●	●
15	Piston gasket	NBR									2	●	●
16	Cushion packing	NBR									2	●	●
17	Cushion packing	NBR									2	●	●
18	Bush #1	Bearing alloy									1	●	
19	Bush #2	Bearing alloy									1	●	
20	Snap ring	Stainless steel				Spring steel					1	●	
21	Piston bolt	Stainless steel				SCM					2	●	
22	Bolt	SUS		SCM							2		
23	Silencer	Brass									1	●	

### Order example

#### Component parts

Tube I.D.	Component parts
ø12	CPL-MCJQ-3-12(M)
ø16	CPL-MCJQ-3-16(M)
ø20	CPL-MCJQ-3-20(M)
ø25	CPL-MCJQ-3-25(M)
ø32	CPL-MCJQ-3-32(M)
ø40	CPL-MCJQ-3-40(M)
ø50	CPL-MCJQ-3-50(M)
ø63	CPL-MCJQ-3-63(M)
ø80	CPL-MCJQ-3-80(M)

M: With magnet

#### Repair kits

Tube I.D.	Repair kits
ø12	PSL-MCJQ-3-12
ø16	PSL-MCJQ-3-16
ø20	PSL-MCJQ-3-20
ø25	PSL-MCJQ-3-25
ø32	PSL-MCJQ-3-32
ø40	PSL-MCJQ-3-40
ø50	PSL-MCJQ-3-50
ø63	PSL-MCJQ-3-63
ø80	PSL-MCJQ-3-80


# MCJQ Dimensions – Double acting $\phi 12 \sim \phi 25$

## COMPACT CYLINDER



$\phi 20, \phi 25$

Total stroke 5~100




\* Stroke 1: First stroke, Stroke 2: Total stroke

for total stroke over 101

$\phi 12$

$\phi 16$



**MCJQ-31 male thread size**

Code Tube I.D.	C1	H1	L1*1,2	L2*1	X
12	9	M5×0.8	14 (24)	24	10.5
16	10	M6×1.0	15.5 (25.5)	25.5	12
20	12	M8×1.25	18.5 (28.5)	28.5	14
25	15	M10×1.25	22.5 (32.5)	32.5	17.5

\*1. L1: Total stroke (Standard stroke)  
L2: Total stroke (Long stroke)  
\*2. ( ) Dimensions for piston rod extended "L" type.

Code Tube I.D.	First stroke				Total stroke									
	Standard stroke		Standard stroke						Long stroke					
	Stroke range	Without Magnet B1	Magnet B1	Stroke range	Without magnet A B2		Magnet A B2		L*	Stroke range	Without Magnet A	Magnet A	B2	L
12	5~30	17	22	5~30	42.5	22	52.5	27	3.5 (13.5)	31~100	62.5	67.5	32	13.5
16	5~30	17	22	5~30	42.5	22	52.5	27	3.5 (13.5)	31~100	62.5	67.5	32	13.5
20	5~50	19.5	29.5	5~50	50	26	70	36	4.5 (14.5)	51~200	75	85	41	14.5
25	5~50	22.5	32.5	5~50	56.5	29	76.5	39	5 (15)	51~300	81.5	91.5	44	15

Code Tube I.D.	C	D	E	F	H	I	K	M	N	OA	OB	P	Q	RA	RB	Z1	Z2	Z3
12	6	6	25	5	M3×0.5	32	5	15.5	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	4.2	6.3	0.5
16	8	8	29	5	M4×0.7	38	6	20	3.5	M4×0.7	6.5	M5×0.8	7.5	7	4	4.2	6.3	0.5
20	7	10	36	5.5	M5×0.8	47	8	25.5	5.4	M6×1.0	9	M5×0.8	9	10	7	6.2	8.8	1
25	12	12	40	5.5	M6×1.0	52	10	28	5.4	M6×1.0	9	M5×0.8	11	10	7	6.2	8.8	1

\* ( ) Dimensions for piston rod extended "L" type.


# MCJQ Dimensions – Double acting $\phi 32 \sim \phi 100$

## COMPACT CYLINDER




$\phi 50 \sim \phi 100$


2- $\phi N$  thru  
2-Counterbore  $\phi OB \times RB$  dp  
2-OA $\times$ RA dp




Total stroke 5~100




\* Stroke 1: First stroke, Stroke 2: Total stroke




$\phi 32$



$\phi 40$





for total stroke over 101



$\phi 32 \sim \phi 100$  (Total stroke 5~100)

$\phi 32 \sim \phi 80$  (Total stroke over 101)



### MCJQ-31 male thread size

Code	First stroke		Total stroke												
	Standard stroke		Standard stroke							Long stroke					
	Stroke range	Without Magnet	Stroke range	Without magnet	Magnet	L*5	Q	Stroke range	Without Magnet	Magnet	B2	L	Q		
32	5-50	23	5-50	60.5	30.5	7 (17)	12.5	101-300	85.5	95.5	45.5	17	12.5		
		33		80.5	40.5										
	51-100	33	51-100	80.5	40.5										
40	5-50	29.5	5-50	76.5	40	7 (17)	14	101-300	101.5	111.5	55	17	14		
				39.5	86.5									50	
	51-100	39.5	51-100	96.5	50										
50	5-50	30.5	5-50	79	40.5	8 (18)	14	101-300	104	114	55.5	18	14		
				40.5	89									50.5	
	51-100	40.5	51-100	99	50.5										
63	5-50	36	5-50	86	42	8 (18)	15.5	101-300	111	121	57	18	16.5		
				46	96									52	
	51-100	46	51-100	106	52										
80	5-50	43.5	5-50	104.5	51	10 (20)	18	101-300	129.5	139.5	66	20	19		
				53.5	114.5									61	
	51-100	53.5	51-100	124.5	61										
100	5-50	53	5-50	125.5	60.5	12 (22)	22	101-300	139.5	139.5	66	20	19		
				63	135.5									70.5	
	51-100	63	51-100	145.5	70.5										

Code Tube I.D.	C1	H1	L1*1,2	L2*1	X
32	20.5	M14 $\times$ 1.5	28.5 (38.5)	38.5	23.5
40	20.5	M14 $\times$ 1.5	28.5 (38.5)	38.5	23.5
50	26	M18 $\times$ 1.5	33.5 (43.5)	43.5	28.5
63	26	M18 $\times$ 1.5	33.5 (43.5)	43.5	28.5
80	32.5	M22 $\times$ 1.5	43.5 (53.5)	53.5	35.5
100	32.5	M26 $\times$ 1.5	43.5 (53.5)	—	35.5

\*1. L1: Total stroke (Standard stroke)  
L2: Total stroke (Long stroke)  
\*2. ( ) Dimensions for piston rod extended "L" type.

Code Tube I.D.	C	D	E	F	G <sup>h9</sup>	H	I	J	JJ	K	M	N	OA	OB	P1	P2	RA	RB	T	Z1	Z2	Z3
32	13	16	45	7.5*1	22 <sup>+0</sup> <sub>-0.052</sub>	M8 $\times$ 1.25	60	4.5	49.5	14	34	5.5	M6 $\times$ 1.0	9	Rc1/8*1	Rc1/8*1	10	7	14	6.2	8.8	1
40	13	16	52	8	28 <sup>+0</sup> <sub>-0.052</sub>	M8 $\times$ 1.25	70	5	57	14	40	5.5	M6 $\times$ 1.0	9	Rc1/8	Rc1/8	10	7	14	6.2	8.8	1
50	15	20	64	10.5*2	35 <sup>+0</sup> <sub>-0.062</sub>	M10 $\times$ 1.5	86	7	71	17	50	6.6	M8 $\times$ 1.25	11	Rc1/4*2	Rc1/4	14	8	19	8.2	10.8	1
63	15	20	77	10.5	35 <sup>+0</sup> <sub>-0.062</sub>	M10 $\times$ 1.5	103	7	84	17	60	9	M10 $\times$ 1.5	14	Rc1/4*3	Rc1/4*3	18	10.5	19	10.2	13.8	1
80	21	25	98	12.5	43 <sup>+0</sup> <sub>-0.062</sub>	M16 $\times$ 2.0	132	6	104	22	77	11	M12 $\times$ 1.75	17.5	Rc3/8*4	Rc3/8*4	22	13.5	26	12.2	17.3	2
100	27	30	117	13	—	M20 $\times$ 2.5	156	6.5	123.5	27	94	11	M12 $\times$ 1.75	17.5	Rc3/8*4	Rc3/8*4	22	13.5	26	12.2	17.3	2

\*1. First stroke without magnet=5mm, P1=M5 $\times$ 0.8, F=5.5, Total stroke without magnet=5mm, P1=P2=M5 $\times$ 0.8, F=5.5

\*2. First stroke or total stroke without magnet=5mm, P1=Rc1/8, F=8

\*3. First stroke without magnet=5mm, P1=Rc1/8, Total stroke without magnet=5mm, P1=P2=Rc1/8

\*4. First stroke without magnet=5mm, P1=Rc1/4, Total stroke without magnet=5mm, P1=P2=Rc1/4

\*5. ( ) Dimensions for piston rod extended "L" type.




Special spec



Technical data



Caution for safety  
(Read before installing)



### Table for stroke

Tube I.D.	Standard stroke	Long stroke
ø12, 16	5,10,15,20,25,30	—
ø20, 25 (*1)	5,10,15,20,25,30,35,40,45,50	75,100
ø32, 40	↑ 75, 100	—

\*1. Using long stroke type body when the cylinder stroke is longer than 51 mm.

\*2. Please contact us if the stroke is out of specification.

### Tightening torque


Tube I.D.	Rod thread	Tightening torque (kgf·cm)
ø12	M5×0.8	22.8
ø16	M6×1.0	41
ø20	M8×1.25	100
ø25	M10×1.25	190
ø32,40	M14×1.5	540

\* Make sure the tightening torque of rod thread does not exceed the value above.

\* The tolerance of tightening torque is ±5%.

### Order example

**MCKJQ — 12 — 20 — 25 M — F — G**



STYLE

Code	Symbol	Description
1 1		Double acting / Male thread
1 2		Double acting / Female thread

TYPE

Code	Description
Blank	Standard
F	Rear flange  (for standard stroke)
L	Piston rod extended to 10 mm (for tube I.D. ø40 standard stroke). For adding LB and FAC accessories
N2*	Front mounting holes enlarged

### Features

- The profile designs are based on MCJQ.
- Hexagonal rods for non-rotating feature.
- Anodised aluminum tubes provide better corrosion and abrasion resistance.
- Stainless Steel rods for better corrosion resistance.

### Specification

Model	MCKJQ					
Acting type	Double acting					
Tube I.D. (mm)	12	16	20	25	32	40
Port size	M5×0.8			Rc1/8		
Medium	Air					
Operating perssure range	0.1~1 MPa		0.8~1 MPa		0.6~1 MPa	
Proof pressure	1.5 MPa					
Ambient temperature	-5°C~+60°C (No freezing)					
Available speed range	50~500 mm/sec					
Rod non-rotating accuracy	±1°	±0.7°		±0.5°		
Allowable rotational torque (kgf·cm)	0.4	2	2.5		4.5	
Sensor switch (*2)	RCE, RCE1	(*1)		●	●	●
	RDEP	●	●	—	●	—

\*1. ø12, ø16: only applicable to RDE and RDE1E.


\*2. RCE , RCE1 , RDEP specification.

\*3. The cylinder is allowed little leakage. Before delivery, it has passed the standard of leakage test.





\* Please confirm the mounting method before purchase and contact us if it is **A** mounting method. (Refer to "Plate mounting methods" ).

### Caution

Please don't attempt to rotate the piston rod.



### Accessories

Accessories				
Code	LB *1 (Purchase 2 pcs)	CB	FAC *1	FBC
Mounting Tube I.D.				
ø40	<b>LB-J1-40</b>	<b>CB-J1-40</b>	<b>FAC-J1-40</b>	

\*1. Within the standard stroke, LB and FAC must be used with the L type (as the piston rod needs to be extended by 10 mm).  
See previous page for stroke range.

\*2. The mounting accessories only for tube I.D. ø40.

\*3. Refer to MCJQ dimension.


### Order example of self-assembled

The tube I.D. ø40 of LB accessories with stroke 25mm.


No.	Order number	Qty
1	<b>LB-J1-40</b>	2
2	<b>MCKJQ-12-40-25-L</b>	1

\* To order accessories/cylinder, please place orders separately according to the order codes in the above table.  
Please refer to the previous page for the cylinder ordering method.

### Pin







Applicable	CB accessories
Code	<b>PIN-CB-P</b> (With snap ring)
Fig Tube I.D.	
ø40	<b>PIN-J1-32-1-P</b>

### Rod nut

Code	NUT
Fig Tube I.D.	
ø12	<b>NUT-M5x0.8x4Hx8B</b>
ø16	<b>NUT-M6x1.0x5Hx10B</b>
ø20	<b>NUT-M8x1.25x5Hx13B</b>
ø25	<b>NUT-M10x1.25x6Hx17B</b>
ø32	<b>NUT-M14x1.5x8Hx22B</b>
ø40	







### Cylinder weight

#### Standard stroke

Model		Basic weight MCKJQ-11	Basic weight (magnet) MCKJQ-11	Stroke 5mm MCKJQ-11	Basic weight MCKJQ-12	Basic weight (magnet) MCKJQ-12	Stroke 5mm MCKJQ-12
Tube I.D.	Stroke range (mm)						
ø12	5~30	38	46	7	36	44	7
ø16		55	66	9	50	61	9
ø20	5~50	100	130	14	93	123	14
ø25		150	189	18	137	176	18
ø32	5~100	231	283	22	200	252	22
ø40		250	315	23	219	284	23

Unit: g


#### Long stroke

Model		Basic weight MCKJQ-11	Basic weight (magnet) MCKJQ-11	Stroke 5mm MCKJQ-11	Basic weight MCKJQ-12	Basic weight (magnet) MCKJQ-12	Stroke 5mm MCKJQ-12
Tube I.D.	Stroke range (mm)						
ø20	51 or more	308	312	14	301	305	14
ø25		398	407	16	390	399	16



Unit: g

\* The weight is based on 51 mm stroke.


**Standard stroke**  $\phi 12\sim\phi 32$




**Standard stroke**  $\phi 12\sim\phi 32$   
(with magnet)



**Standard stroke**  $\phi 40$



**Standard stroke**  $\phi 40$   
(with magnet)



### Standard stroke – Material


No.	Tube I.D. Part name	12	16	20	25	32	40	Q'y	Repair kits (inclusion)
1	Body	Aluminum alloy						1	
2	Rod cover	Aluminum alloy						1	
3	End cover	Aluminum alloy						1	
4	Piston rod	Stainless steel						1	
5	Piston	Aluminum alloy						1	
6	Rod packing	NBR						1	●
7	Snap ring	Spring steel						1	
8	Cover ring	NBR						1	●
9	Piston bolt	Stainless steel				SCM		1	
10	Piston packing	NBR						1	●
11	Piston gasket	NBR						1	●
12	Cushion packing	NBR						2	●
13	Magnet ring	Magnet						1	
14	Wear ring	-				Resin		1	
15	Bush	Bearing alloy						1	
16	Bolt	Carbon steel					-	2	
17	Washer	Carbon steel						1	
18	Set screw	-					*1	1	

\*1. Alloy steel



### Order example Repair kits

Tube I.D.	Repair kits
$\phi 12$	<b>PS-MCKJQ-12</b>
$\phi 16$	<b>PS-MCKJQ-16</b>
$\phi 20$	<b>PS-MCKJQ-20</b>
$\phi 25$	<b>PS-MCKJQ-25</b>
$\phi 32$	<b>PS-MCKJQ-32</b>
$\phi 40$	<b>PS-MCKJQ-40</b>

### Long stroke $\phi 20, \phi 25$



### Long stroke $\phi 20, \phi 25$ (with magnet)



### Long stroke – Material

No.	Tube I.D. Part name	Material	Q'y	Component parts (inclusion)	Repair kits (inclusion)
1	Body	Aluminum alloy	1		
2	Rod cover	Aluminum alloy	1	●	
3	End cover	Aluminum alloy	1	●	
4	Piston rod	Stainless steel	1		
5	Piston	Aluminum alloy	1	●	
6	Rod packing	NBR	1	●	●
7	Snap ring	Stainless steel	1	●	
8	Cover ring	NBR	2	●	●
9	Piston bolt	Stainless steel	1	●	
10	Piston packing	NBR	1	●	●
11	Piston gasket	NBR	1	●	●
12	Cushion packing	NBR	2	●	●
13	Magnet ring	Magnet	1	●	
14	Wear ring	Resin	1	●	
15	Bush	Bearing alloy	1	●	
16	Washer	Carbon steel	1	●	
17	Snap ring	Spring steel	1	●	
18	Bolt	Carbon steel	2		

### Order example Component parts


Tube I.D.	Component parts
$\phi 20$	<b>CPL-MCKJQ-20(M)</b>
$\phi 25$	<b>CPL-MCKJQ-25(M)</b>

M: With magnet

### Repair kits


Tube I.D.	Repair kits
$\phi 20$	<b>PSL-MCKJQ-20</b>
$\phi 25$	<b>PSL-MCKJQ-25</b>

### F Rear flange



Code Tube I.D.	P2 <sup>h9</sup>	S2
12	6	1.5
16	10	1.5
20	13	2
25	15	2
32	21	2
40	28	2

### N2 Front mounting holes enlarged (Applicable mounting method **A**)



Code Tube I.D.	N2
12	4.5
16	4.5
20	6.5
25	6.5
32	6.5

## Plate mounting methods

### ⚠ Caution


Different mounting methods match different bolts and plate. Please confirm the mounting method before purchase.

\* The plates and bolts are prepared by the customers.


### Bolt specification

Tube I.D. Mounting	$\phi 12$	$\phi 16$	$\phi 20$	$\phi 25$	$\phi 32$	$\phi 40$
<b>A, C</b>	M4×0.7	M4×0.7	M6×1.0	M6×1.0	M6×1.0	M6×1.0
<b>B, D</b>	M3×0.5	M3×0.5	M5×0.8	M5×0.8	M5×0.8	M5×0.8


**A** The plate is in front and the bolt is mounted from the front. For  $\phi 12 \sim \phi 32$ , when selecting mounting option A, the order code must be N2 type.  
Order example: **MCKJQ-12-20-25M-N2**





**B** The plate is in back and the bolt is mounted from the front.



**C** The plate is in back and the bolt is mounted from the back.




**D** The plate is in front and the bolt is mounted from the back.




### 12


#### $\phi 12, \phi 16$




#### $\phi 20, \phi 25$



#### $\phi 32$



#### $\phi 40$




#### $\phi 12, \phi 16$

#### $\phi 20, \phi 25$

#### $\phi 32$

#### $\phi 40$



### 11 Male thread

Code	B1	C1	H1	L1*	MM	X
12	8	9	4	14	M5×0.8	10.5
16	10	10	5	15.5	M6×1.0	12
20	13	12	5	18.5	M8×1.25	14
25	17	15	6	22.5	M10×1.25	17.5
32	22	20.5	8	28.5	M14×1.5	23.5
40	22	20.5	8	28.5 (38.5)	M14×1.5	23.5

\* ( ) Dimensions for piston rod extended "L" type.

Code	Stroke range	Standard stroke						Long stroke																			
		Without magnet			Magnet			Stroke range	A	B	F	C	D	E	F	G	H	I	J	K	L*2	M	N1	O	Q	T	Z
		A	B	F	A	B	F																				
12	5~30	25.5	22	-	30.5	27	-	-	-	-	6	15 <sup>0</sup> <sub>-0.043</sub>	25	5	1.5	M3×0.5	32	6.74	6	3.5	15.5	3.5	-	12.5	5	-	
16	5~30	27	23.5	-	32	28.5	-	-	-	-	8	19 <sup>0</sup> <sub>-0.052</sub>	29	5	1.5	M4×0.7	38	8.96	8	3.5	20	3.5	-	14	6.5	-	
20	5~50	32	27.5	5.5	42	37.5	5.5	51~100	53.5	49	9	7	21 <sup>0</sup> <sub>-0.052</sub>	36	-	2	M5×0.8	47	11.24	10	4.5	25.5	5.5	-	17	8	-
25	5~50	35.5	30.5	5.5	45.5	40.5	5.5	51~100	57	52	11	12	22 <sup>0</sup> <sub>-0.052</sub>	40	-	2	M6×1.0	52	13.52	12	5	28	5.5	-	19	8	-
32	5~50	39	32	-	49	42	-	-	-	-	13	28 <sup>0</sup> <sub>-0.052</sub>	45	7.5*	2	M8×1.25	60	15.76	14	7	34	5.5	4.5	19.5*	9	14	
	51~100	49	42	-	49	42	-	-	-	-	13	28 <sup>0</sup> <sub>-0.052</sub>	45	7.5*	2	M8×1.25	60	15.76	14	7	34	5.5	4.5	19.5*	9	14	
40	5~50	36.5	29.5	-	46.5	39.5	-	-	-	-	13	28 <sup>0</sup> <sub>-0.052</sub>	52	8	2	M8×1.25	70	15.76	14	7(17)	40	5.5	5	11	-	14	
	51~100	46.5	39.5	-	46.5	39.5	-	-	-	-	13	28 <sup>0</sup> <sub>-0.052</sub>	52	8	2	M8×1.25	70	15.76	14	7(17)	40	5.5	5	11	-	14	

\*1. Without magnet with stroke=5mm, Port size = M5×0.8, Q=20.5, F=5.5

\*2. ( ) Dimensions for piston rod extended "L" type.




Special spec



Technical data



Caution for safety  
(Read before installing)



### Table for standard stroke

Tube I.D.	Stroke (mm)	Max. stroke
ø20,25	5, 10, 15, 20, 25, 30, 40, 50, 60, 80, 100, 200	300
ø32,40	5, 10, 15, 20, 25, 30, 40, 50, 60, 80, 100, 200, 300	300
ø50,63	10, 15, 20, 25, 30, 40, 50, 60, 80, 100, 200, 300, 400	400
ø80,100	15, 20, 25, 30, 40, 50, 60, 80, 100, 200, 300, 400, 500	500

\* Please contact us if the stroke is out of specification.

### Order example

MCJI – 12 – 20 – 25

MODEL      1: Single rod      TUBE I.D.      STROKE  
                  2: Double rod

STYLE

Code	Symbol	Description	Code	Symbol	Description
1 1		Double acting / Male thread	2 1		Double rod / Male thread
1 2		Double acting / Female thread	2 2		Double rod / Female thread

### Features


- ISO 21287 standard.
- Wide range of bore sizes and strokes.
- Ultra compact, light weight and space saving.
- Sensor slots on RCI sides for flush mounting of proximity sensors.
- Magnetic as standard.

### Specification

Model	MCJI	
Acting type	Double acting	
Tube I.D. (mm)	20,25	32,40,50,63,80,100
Port size	M5×0.8	G1/8
Medium	Air	
Operating perssure range	0.05~1 MPa	
Proof pressure	1.5 MPa	
Cushion	Rubber bumper	
Lubricator	Without lubrication	
Stroke length tolerance (*)	+0~+1.0 mm	
Ambient temperature	-5°C~+60°C (No freezing)	
Available speed range	50~500 mm/sec	
Sensor switch	RDT, RQT  RCI	

\* Stroke length tolerance does not include the amount of bumper change.

### Installation of sensor switch



### Order example of mounting accessories

Code	LB (Purchase 2 pcs)	CA	CB	FAC	FBC	MP	ROD NUT
Mounting Tube I.D.							
ø20	LB-J2-20	CA-J2-20	-	FAC-J2-20		MP-J2-20	NUT-M8x1.25x4Hx13B
ø25	LB-J2-25	CA-J2-25	-	FAC-J2-25		MP-J2-25	
ø32	LB-J2-32	CA-J2-32	CB-J2-32	FAC-J2-32		MP-J2-32	NUT-M10x1.25x5Hx17B
ø40	LB-J2-40	CA-J2-40	CB-J2-40	FAC-J2-40		MP-J2-40	
ø50	LB-J2-50	CA-J2-50	CB-J2-50	FAC-J2-50		MP-J2-50	NUT-M12x1.25x6Hx19B
ø63	LB-J2-63	CA-J2-63	CB-J2-63	FAC-J2-63		MP-J2-63	
ø80	LB-J2-80	CA-J2-80	CB-J2-80	FAC-J2-80		MP-J2-80	NUT-M16x1.5x8Hx24B
ø100	LB-J2-100	CA-J2-100	CB-J2-100	FAC-J2-100		MP-J2-100	

### Pin

Applicable CA & CB accessories

Code	PIN-CB-P (With snap ring)
Fig Tube I.D.	
ø20	-
ø25	-
ø32	PIN-J2-32-1-P
ø40	PIN-J2-40-1-P
ø50	PIN-J2-50-1-P
ø63	PIN-J2-63-1-P
ø80	PIN-J2-80-1-P
ø100	PIN-J2-100-1-P

### Theoretic force





Unit: N

Tube I.D.	Acting direction	Operating perssure (MPa)		
		0.3	0.5	0.7
20	IN	69	116	162
	OUT	92	154	216
25	IN	121	202	283
	OUT	144	241	337
32	IN	203	339	475
	OUT	237	394	552
40	IN	337	561	785
	OUT	370	616	863
50	IN	519	864	1210
	OUT	578	963	1348
63	IN	858	1430	2003
	OUT	917	1529	2141
80	IN	1387	2311	3236
	OUT	1479	2466	3452
100	IN	2219	3698	5178
	OUT	2311	3852	5393


### Allowable Lateral Load


Please make sure to use the cylinder within allowable lateral load. Otherwise, the cylinder may be damaged or the life may be shortened.




### Allowable kinetic energy

Please make sure to use the cylinder within allowable kinetic energy. If it is used outside the range, it may cause excessive impact and damage the device.






### Single rod



### Double rod



### Order example Component parts / Repair kits

### Material

No.	Part name	Material	Q'y		Component parts (inclusion)	Repair kits (inclusion)
			Single	Double		
1	Rod cover	Aluminum alloy	1	2	●	
2	End cover	Aluminum alloy	1	—	●	
3	Tube	Aluminum alloy	1	1		
4	Piston-R	Aluminum alloy	1	1	●	
5	Piston-H	Aluminum alloy	1	1	●	
6	Piston rod	*1	1	2		
7	Rod packing	NBR	1	1	●	●
8	Bush	Bearing alloy	1	1	●	
9	Magnet ring	Magnet material	1	1	●	
10	Piston packing	NBR	1	1	●	●
11	O-ring	NBR	1	1	●	●
12	Screw	Carbon steel	1	—	●	
13	Cushion	NBR	2	2	●	●
14	O-ring	NBR	2	2	●	●
15	Screw	Stainless steel	8	8	●	
16	Wear ring	Resin	1	1	●	

\*1. Material  $\phi 20, \phi 25$ : Stainless steel;  $\phi 32 \sim \phi 100$ : Medium carbon steel.

### Single rod












Tube I.D.	Component parts	Repair kits
$\phi 20$	CP-MCJI-20	PS-MCJI-20
$\phi 25$	CP-MCJI-25	PS-MCJI-25
$\phi 32$	CP-MCJI-32	PS-MCJI-32
$\phi 40$	CP-MCJI-40	PS-MCJI-40
$\phi 50$	CP-MCJI-50	PS-MCJI-50
$\phi 63$	CP-MCJI-63	PS-MCJI-63
$\phi 80$	CP-MCJI-80	PS-MCJI-80
$\phi 100$	CP-MCJI-100	PS-MCJI-100


### Double rod

Tube I.D.	Component parts	Repair kits
$\phi 20$	CP-MCJI-2-20	PS-MCJI-2-20
$\phi 25$	CP-MCJI-2-25	PS-MCJI-2-25
$\phi 32$	CP-MCJI-2-32	PS-MCJI-2-32
$\phi 40$	CP-MCJI-2-40	PS-MCJI-2-40
$\phi 50$	CP-MCJI-2-50	PS-MCJI-2-50
$\phi 63$	CP-MCJI-2-63	PS-MCJI-2-63
$\phi 80$	CP-MCJI-2-80	PS-MCJI-2-80
$\phi 100$	CP-MCJI-2-100	PS-MCJI-2-100

### Cylinder weight

Unit: g

Model	Basic weight MCJI-11	Stroke 10mm MCJI-11	Basic weight MCJI-12	Stroke 10mm MCJI-12	LB	FAC/FBC	MP	CA	CB	PIN (CA & CB)	Nut
Tube I.D.											
$\phi 20$	121	14	108	14	76	126	28	66	N/A	N/A	3
$\phi 25$	147	18	135	18	88	159	37	82	N/A	N/A	3
$\phi 32$	238	24	214	24	106	206	60	174	160	31	7
$\phi 40$	322	32	291	32	140	268	89	260	248	51	7
$\phi 50$	493	46	455	46	242	492	129	403	390	58	9
$\phi 63$	703	48	667	48	288	635	182	634	576	119	9
$\phi 80$	1260	76	1190	76	567	1457	339	1149	1085	150	18
$\phi 100$	2140	92	2060	92	766	2033	568	1550	1623	285	18






No.	Accessories	Material	Page link
1	Mounting accessories LB	Carbon steel	<a href="#">↗</a>
2	Mounting accessories FAC/FBC	Carbon steel	<a href="#">↗</a>
3	Mounting accessories MP	Aluminum	<a href="#">↗</a>
4	Mounting accessories CA	Cast iron	<a href="#">↗</a>
5	Mounting accessories CB+PIN	Cast iron / *	<a href="#">↗</a>
6	Floating joint MFC	Carbon steel	<a href="#">↗</a>
7	Floating joint MFCS	Carbon steel	<a href="#">↗</a>
8	Female rod ends PHS	Carbon steel	<a href="#">↗</a>
9	Fitting PC (PISCO)	–	<a href="#">↗</a>
10	Speed controller JSC (PISCO)	–	<a href="#">↗</a>
11	Sensor switch R*T	–	<a href="#">↗</a>
12	Sensor switch RCI	–	<a href="#">↗</a>

\* Material of PIN is carbon steel.



**12** Single rod

**22** Double rod

$\phi 20 \sim \phi 25$



$\phi 32 \sim \phi 100$




**11** | **21** Male thread

Code Tube I.D.	A	A1	B	B1	KK
20	16	14	13	4	M8×1.25
25	16	14	13	4	M8×1.25
32	19	17	17	5	M10×1.25
40	19	17	17	5	M10×1.25
50	22	20	19	6	M12×1.25
63	22	20	19	6	M12×1.25
80	28	26	24	8	M16×1.5
100	28	26	24	8	M16×1.5


Code Tube I.D.	AF	C	D	E	EE	G	WH	I	J	KF	PL	TG	RT	ZA	ZB	ZC
20	14	11	10	35.5	M5×0.8	8	6	9	2.1	M6×1.0	7	22	M5×0.8	37	43	49
25	14	11	10	39.5	M5×0.8	8	6	9	2.1	M6×1.0	7	26	M5×0.8	39	45	51
32	15	14	12	47.0	G1/8	10	7	9	2.1	M8×1.25	7.5	32.5	M6×1.0	44	51	58
40	15	14	12	54.5	G1/8	10	7	9	2.1	M8×1.25	7.5	38	M6×1.0	45	52	59
50	18	14	16	65.5	G1/8	14	8	12	2.6	M10×1.5	7.5	46.5	M8×1.25	45	53	61
63	18	14.5	16	75.5	G1/8	14	8	12	2.6	M10×1.5	7.5	56.5	M8×1.25	49	57	65
80	20	15.5	20	95.5	G1/8	17	10	12	2.6	M12×1.75	8	72	M10×1.5	54	64	74
100	20	18.5	20	113.5	G1/8	17	10	12	2.6	M12×1.75	9.5	89	M10×1.5	67	77	87

**MP**




Code Tube I.D.	B	E	WH	ZA	Max. overall stroke
20	13	35.5	6	37	600 mm
25	13	39.5	6	39	600 mm
32	15	47.0	7	44	800 mm
40	15	54.5	7	45	800 mm
50	15	65.5	8	45	800 mm
63	15	75.5	8	49	800 mm
80	17	95.5	10	54	1000 mm
100	19.5	113.5	10	67	1000 mm



\* The max. overall stroke length may not be exceeded when combining cylinders and multi-position kits.



No.	Part name	Q'y
1	Connection block	1
2	Flange	2
3	Bolt	2
4	Bolt	2





**LB**




Code Tube I.D.	AB	AH	AO	AU	E	EA	L	R	SA	T	TR	WH	XA
20	7	27	7	16	35.5	44.8	21	—	69	4	22	6	59
25	7	29	7	16	39.5	48.8	22	—	71	4	26	6	61
32	7	33.5	7	16	47.0	57.0	24.5	15	76	4	32	7	67
40	10	38	9	18	54.5	65.3	26	17.5	81	4	36	7	70
50	10	45	9	21	65.5	77.8	31	20	87	5	45	8	74
63	10	50	9	21	75.5	87.8	31	22.5	91	5	50	8	78
80	12	63	11	26	95.5	110.8	40	—	106	6	63	10	90
100	14.5	74	13	27	113.5	130.8	46	—	121	6	75	10	104

**FAC**

$\phi 20 \sim \phi 25$





$\phi 32 \sim \phi 100$




Code Tube I.D.	D	E	FB	MF	R	TF	UF	W	ZB
20	16	35.5	6.6	8	—	55	70	2	43
25	16	39.5	6.6	8	—	60	76	2	45
32	30	47.0	7	10	32	64	80	3	51
40	35	54.5	9	10	36	72	90	3	52
50	40	65.5	9	12	45	90	110	4	53
63	45	75.5	9	12	50	100	120	4	57
80	45	95.5	12	16	63	126	150	6	64
100	55	113.5	14	16	75	150	175	6	77

**FBC**

$\phi 20 \sim \phi 25$




$\phi 32 \sim \phi 100$




Code Tube I.D.	D	E	FB	MF	R	TF	UF	ZF
20	16	35.5	6.6	8	—	55	70	51
25	16	39.5	6.6	8	—	60	76	53
32	30	47.0	7	10	32	64	80	61
40	35	54.5	9	10	36	72	90	62
50	40	65.5	9	12	45	90	110	65
63	45	75.5	9	12	50	100	120	69
80	45	95.5	12	16	63	126	150	80
100	55	113.5	14	16	75	150	175	93

**CA**



Code Tube I.D.	CD	EW	FL	L	MR	ZE
20	8	16 h12	20	14	8	63
25	8	16 h12	20	14	8	65
32	10	25.8 <sup>+0</sup> <sub>-0.4</sub>	22	13	10	73
40	12	27.8 <sup>+0</sup> <sub>-0.4</sub>	25	16	12	77
50	12	31.8 <sup>+0</sup> <sub>-0.4</sub>	27	16	12	80
63	16	39.8 <sup>+0</sup> <sub>-0.4</sub>	32	21	16	89
80	16	49.8 <sup>+0</sup> <sub>-0.4</sub>	36	22	16	100
100	20	59.8 <sup>+0</sup> <sub>-0.4</sub>	41	30	21	118


**CB**



Code Tube I.D.	CB	CD	FL	L	MR	UB	ZE
32	26	10	22	13	10	45	73
40	28	12	25	16	12	52	77
50	32	12	27	16	12	60	80
63	40	16	32	21	16	70	89
80	50	16	36	22	16	90	100
100	60	20	41	29	20	110	118

\*  $\varnothing 20$ ,  $\varnothing 25$  without CB accessory.

**PIN**



Code Tube I.D.	A(e8)	B	C	E	F	Snap ring
32	10	9.6	1.15	45.2	50.5	STW-10
40	12	11.5	1.15	52.2	57.5	STW-12
50	12	11.5	1.15	60.2	65.5	STW-12
63	16	15.2	1.15	70.2	75.5	STW-16
80	16	15.2	1.15	90.2	95.5	STW-16
100	20	19	1.35	110.3	116	STW-20

# MCJI Multiple position series

## ISO 21287 COMPACT CYLINDER




Special spec



Technical data



Caution for safety  
(Read before installing)




### Specification

Model	MCJI-3*	
Acting type	Double acting	
Tube I.D. (mm)	20,25	32,40,50,63,80,100
Port size	M5×0.8	G1/8
Medium	Air	
Operating pressure range	0.05~1 MPa	
Proof pressure	1.5 MPa	
Cushion	Rubber bumper	
Lubricator	Without lubrication	
Stroke length tolerance (*)	+0~+1.0 mm	
Ambient temperature	-5°C~+60°C (No freezing)	
Available speed range	50~500 mm/sec	
Sensor switch	RDT, RQT , RCI	

\* Stroke length tolerance does not include the amount of bumper change.

### Order example

**MCJI — 32 — 40 — 20×25**



#### STYLE


Code	Symbol	Description
3 1		Double acting / Male thread
3 2		Double acting / Female thread

### Table for standard stroke

Tube I.D.	First stroke (mm)	Max. stroke
ø20,25	5,10,15,20,25,30,40,50,60,80,100	110
ø32,40	5,10,15,20,25,30,40,50,60,80,100	120
ø50,63	10,15,20,25,30,40,50,60,80,100,110,120	150
ø80,100	15,20,25,30,40,50,60,80,100,110,120	140

Tube I.D.	Total stroke (mm)	Max. stroke
ø20,25	5,10,15,20,25,30,40,50,60,80,100,200	300
ø32,40	5,10,15,20,25,30,40,50,60,80,100,200,300	300
ø50,63	10,15,20,25,30,40,50,60,80,100,200,300,400	400
ø80,100	15,20,25,30,40,50,60,80,100,200,300,400,500	500

\* Please contact us if the stroke is out of specification.



### Material

No.	Part name	Material	Q'ty	Component parts (inclusion)	Repair kits (inclusion)
1	Rod cover	Aluminum alloy	2	●	
2	Tube	Aluminum alloy	2		
3	Piston-R	Aluminum alloy	2	●	
4	Piston-H	Aluminum alloy	2	●	
5	Piston rod	*1	1		
6	Rod packing	NBR	2	●	●
7	Bush	Bearing alloy	3	●	
8	Magnet ring	Magnet material	2	●	
9	Piston packing	NBR	2	●	●
10	O-ring	NBR	2	●	●
11	Screw	Carbon steel	2	●	
12	Cushion	NBR	2	●	●
13	Cushion	NBR	1	●	●
14	O-ring	NBR	3	●	●
15	Screw	Stainless steel	8	●	
16	Wear ring	Resin	2	●	
17	End cover	Aluminum alloy	1	●	
18	Center cover	Aluminum alloy	1	●	
19	Piston rod	*1	1		
20	Screw	Carbon steel	2		
21	Silencer	Brass	1	●	

\*1. Material  $\varnothing 20, \varnothing 25$ : Stainless steel;  $\varnothing 32 \sim \varnothing 100$ : Medium carbon steel.


### Order example

#### Component parts / Repair kits

Tube I.D.	Component parts	Repair kits
$\varnothing 20$	CP-MCJI-3-20	PS-MCJI-3-20
$\varnothing 25$	CP-MCJI-3-25	PS-MCJI-3-25
$\varnothing 32$	CP-MCJI-3-32	PS-MCJI-3-32
$\varnothing 40$	CP-MCJI-3-40	PS-MCJI-3-40
$\varnothing 50$	CP-MCJI-3-50	PS-MCJI-3-50
$\varnothing 63$	CP-MCJI-3-63	PS-MCJI-3-63
$\varnothing 80$	CP-MCJI-3-80	PS-MCJI-3-80
$\varnothing 100$	CP-MCJI-3-100	PS-MCJI-3-100


### 32

$\varnothing 20, \varnothing 25$



\* Stroke1: First stroke, Stroke2: Total stroke.

$\varnothing 32 \sim \varnothing 100$



### 31 Male thread

Code Tube I.D.	A	A1	B	B1	KK
20	16	14	13	4	M8×1.25
25	16	14	13	4	M8×1.25
32	19	17	17	5	M10×1.25
40	19	17	17	5	M10×1.25
50	22	20	19	6	M12×1.25
63	22	20	19	6	M12×1.25
80	28	26	24	8	M16×1.5
100	28	26	24	8	M16×1.5

Code Tube I.D.	AF	C	D	E	EE	G	WH	I	J	KF	PL	TG	RT	ZA	ZE
20	14	11	10	35.5	M5×0.8	8	6	9	2.1	M6×1.0	7	22	M5×0.8	37	80
25	14	11	10	39.5	M5×0.8	8	6	9	2.1	M6×1.0	7	26	M5×0.8	39	84
32	15	14	12	47.0	G1/8	10	7	9	2.1	M8×1.25	7.5	32.5	M6×1.0	44	95
40	15	14	12	54.5	G1/8	10	7	9	2.1	M8×1.25	7.5	38	M6×1.0	45	97
50	18	14	16	65.5	G1/8	14	8	12	2.6	M10×1.5	7.5	46.5	M8×1.25	45	98
63	18	14.5	16	75.5	G1/8	14	8	12	2.6	M10×1.5	7.5	56.5	M8×1.25	49	106
80	20	15.5	20	95.5	G1/8	17	10	12	2.6	M12×1.75	8	72	M10×1.5	54	118
100	20	18.5	20	113.5	G1/8	17	10	12	2.6	M12×1.75	9.5	89	M10×1.5	67	144

\* Stroke1: First stroke, Stroke2: Total stroke.




Special spec



Technical data






Caution for safety  
(Read before installing)



### Features

- Plate type design for ultra compact, Oval piston design for space saving.
- Sensor slots on sides for flush mounting of proximity sensors.
- Magnetic as standard.

### Specification

Model	MCJU				
Acting type	Double acting				
Tube I.D. (mm)	25	32	40	50	63
Port size	M5×0.8	Rc1/8		Rc1/4	
Medium	Air				
Operating pressure range	0.05~0.7 MPa				
Proof pressure	1.0 MPa				
Available speed range	50~500 mm/sec				
Cushion	Rubber bumper				
Lubricator	Without lubrication				
Stroke length tolerance (*)	+0~+1.5 mm				
Ambient temperature	-5°C~+60°C (No freezing)				
Sensor switch	RDC(V), RQC(V)  , RDVE(V)  , RDGV 				


### Table for standard stroke

Tube I.D.	Stroke (mm)	Max. stroke
ø25,32,40 50,63	5,10,15,20,25,30,40,50,75, 100,200,250	300





\* Please contact us if the stroke is out of specification.

\* Stroke length tolerance does not include the amount of bumper change.




### Order example




#### STYLE

Code	Symbol	Description
1 1		Double acting / Male thread
1 2		Double acting / Female thread
2 1		Double rod / Male thread
2 2		Double rod / Female thread


### Order example of mounting accessories

Code	LB (Purchase 2 pcs)	FAC	FBC
Mounting Tube I.D.			
ø25	LB-J3-25	FAC-J3-25	
ø32	LB-J3-32	FAC-J3-32	
ø40	LB-J3-40	FAC-J3-40	
ø50	LB-J3-50	FAC-J3-50	
ø63	LB-J3-63	FAC-J3-63	


### Installation of sensor switch



### Single rod



### Double rod



### Material

No.	Part name	Material	Q'y / Style				Repair kits (inclusion)
			11	12	21	22	
1	Rod cover	Aluminum alloy	1	2			
2	End cover	Aluminum alloy	1	-			
3	Tube	Aluminum alloy		1			
4	Piston	Aluminum alloy		1			
5	Piston rod-R *1	Carbon steel		1			
6	Piston rod-H *1	Carbon steel	-	1			
7	Piston packing	HNBR		1		●	
8	Rod packing	HNBR	1	2		●	
9	Magnet	Magnet material		4			
10	Wear ring	Resin		1			
11	Cushion pad	TPU		2			
12	Bush	Bearing alloy	1	2			
13	O-ring	NBR		1			
14	Piston bolt	Stainless steel	1	-			
15	Bolt	Stainless steel		4			
16	Nut	Carbon steel	1	-	2	-	




\*1. When customized material is bearing steel, only two-side across flat (wrench flat) is available.

### Order example

#### Repair kits









Tube I.D.	Repair kits
ø25	<b>PS-MCJU-25</b>
ø32	<b>PS-MCJU-32</b>
ø40	<b>PS-MCJU-40</b>
ø50	<b>PS-MCJU-50</b>
ø63	<b>PS-MCJU-63</b>


#### Accessories weight

Model	LB	FAC/FBC	Nut
Tube I.D.			
ø25	67	97	8
ø32	141	141	11
ø40	204	226	16
ø50	324	447	32
ø63	616	809	32

### Cylinder weight




Unit: g

Model	Basic weight MCJU-11	Stroke 10mm MCJU-11	Basic weight MCJU-12	Stroke 10mm MCJU-12	Basic weight MCJU-21	Stroke 10mm MCJU-21	Basic weight MCJU-22	Stroke 10mm MCJU-22
Tube I.D.								
ø25	192	20	167	20	246	28	198	28
ø32	320	27	282	27	381	40	305	40
ø40	454	37	403	37	561	54	444	54
ø50	846	57	768	57	1060	83	842	83
ø63	1234	76	1157	76	1466	102	1248	102





No.	Accessories	Material	Page link
1	Mounting accessories LB	Carbon steel	<a href="#">[Link]</a>
2	Mounting accessories FAC/FBC	Carbon steel	<a href="#">[Link]</a>
3	Floating joint MFC	Carbon steel	<a href="#">[Link]</a>
4	Floating joint MFCS	Carbon steel	<a href="#">[Link]</a>
5	Female rod ends PHS	Carbon steel	<a href="#">[Link]</a>
6	Fitting PC (PISCO)	-	<a href="#">[Link]</a>
7	Speed controller JSC (PISCO)	-	<a href="#">[Link]</a>
8	Sensor switch R*C(V)	-	<a href="#">[Link]</a>
9	Sensor switch RDFE	-	<a href="#">[Link]</a>
10	Sensor switch RDGV	-	<a href="#">[Link]</a>

12




11 Male thread




Code Tube I.D.	A	A1	B	B1	CA	CB	D	E	ET	FT	FX	FY	GX	GY	H	KA	KB	KK
25	22	19.5	17	6	54	24.2	12	26	M5×0.8×11 dp	M5×0.8×7.5 dp	9	7	10.5	5	36	10	5.5	M10×1.25
32	26	23.5	19	7	68	28	14	42	M6×1.0×11 dp	M6×1.0×12 dp	6.5	8	9	5.5	40	12	5.5	M12×1.75
40	30	27	22	8	86	32	16	54	M8×1.25×11 dp	M8×1.25×13 dp	8	9	10	7	45	14	6	M14×1.5
50	35	32	26	11	104	39	20	64	M10×1.5×15 dp	M10×1.5×14.5 dp	10	9	11.5	8	53	18	7	M18×1.5
63	35	32	26	11	124	50	20	72	M12×1.75×15 dp	M12×1.75×18 dp	11	12	11.5	10	56	18	7	M18×1.5

Code Tube I.D.	KT	N	NA	NB	NC	ND	NE	S	P	WH	ZA
25	M6×1.0×12 dp	16.5	6	26	sinkø7.5×4.5 dp	M5×0.8	4.2	55	M5×0.8	14	69
32	M8×1.25×13 dp	18	6.5	28	sinkø9×5.5 dp	M6×1.0	5.1	58	Rc1/8	14	72
40	M8×1.25×13 dp	18.5	8	36	sinkø10.5×6.5 dp	M8×1.25	6.7	60	Rc1/8	15	75
50	M10×1.5×15 dp	24	10	42	sinkø13.5×8.5 dp	M10×1.5	8.5	74	Rc1/4	18	92
63	M10×1.5×15 dp	24	11	46	sinkø17×10.5 dp	M12×1.75	10.2	75	Rc1/4	21	96

22




21 Male thread



Code Tube I.D.	A	A1	B	B1	CA	CB	D	E	ET	FT	FX	FY	GX	GY	H	KA	KB	KK
25	22	19.5	17	6	54	24.2	12	26	M5×0.8×11 dp	M5×0.8×7.5 dp	9	7	10.5	5	36	10	5.5	M10×1.25
32	26	23.5	19	7	68	28	14	42	M6×1.0×11 dp	M6×1.0×12 dp	6.5	8	9	5.5	40	12	5.5	M12×1.75
40	30	27	22	8	86	32	16	54	M8×1.25×11 dp	M8×1.25×13 dp	8	9	10	7	45	14	6	M14×1.5
50	35	32	26	11	104	39	20	64	M10×1.5×15 dp	M10×1.5×14.5 dp	10	9	11.5	8	53	18	7	M18×1.5
63	35	32	26	11	124	50	20	72	M12×1.75×15 dp	M12×1.75×18 dp	11	12	11.5	10	56	18	7	M18×1.5


Code Tube I.D.	KT	N	NA	NB	NC	ND	NE	S	P	WH	ZB
25	M6×1.0×12 dp	16.5	6	26	sinkø7.5×4.5 dp	M5×0.8	4.2	55	M5×0.8	14	83
32	M8×1.25×13 dp	18	6.5	28	sinkø9×5.5 dp	M6×1.0	5.1	58	Rc1/8	14	86
40	M8×1.25×13 dp	18.5	8	36	sinkø10.5×6.5 dp	M8×1.25	6.7	60	Rc1/8	15	90
50	M10×1.5×15 dp	24	10	42	sinkø13.5×8.5 dp	M10×1.5	8.5	74	Rc1/4	18	110
63	M10×1.5×15 dp	24	11	46	sinkø17×10.5 dp	M12×1.75	10.2	75	Rc1/4	21	117

**LB**




Code Tube I.D.	A	BA	BB	CA	CB	D	DE	E	F	ZA
25	79	6	12	29	56	11	23	3.2	5.5	91
32	90	8	16	37	71	12	27	4.5	6.6	106
40	96	10	18	46	89	15	31	4.5	9	116
50	116	11	21	57	109	18	37	5	11	138
63	123	14	24	67	129	22	48	6	13.5	151

**FAC**



Code Tube I.D.	A	B	CA	CB	D	E	H	ZB
25	76	24	66	14	8	5.5	36	99
32	94	28	82	16	8	7	40	106
40	118	32	102	18	9	9	45	114
50	144	39	126	22	12	11	53	139
63	168	50	148	30	14	13	56	145

**FBC**






Technical data



Caution for safety  
(Read before installing)



### Features

- Compact and space saving.

### Specification

Model	MCFA					
Acting type	Double acting					
Tube I.D. (mm)	6	10	16	20	25	32
Port size	M5×0.8					Rc1/8
Medium	Air					
Max. operating pressure	0.7 MPa					
Min. operating pressure (MPa)	0.12	0.06	0.05			
Proof pressure	1 MPa					
Cushion	With rubber cushion pad					
Lubrication	Not required					
Ambient temperature	-5~+60°C (No freezing)					
Available speed range	50~500 mm/sec					
Sensor switch	RCE , RCE1 , RDEP					

### Order example

MCFA — 11 — 6 — 10M — K — □

MODEL

- 1: Single rod  
2: Double rod

STROKE

- Blank: Standard  
K: Non-rotating rod

TUBE I.D.

M: Magnet

- PORT THREAD  
Blank: M5×0.8  
(for ø6~ø25)  
Blank: Rc thread  
G: G thread  
NPT: NPT thread  
(for ø32)

STYLE

Code	Symbol	Description
1 1		Double action / Male thread
2 1		Double rod / Male thread

### Table for standard stroke

Tube I.D.	Stroke (mm)
ø6, 10, 16	5,10,15,20,25,30
ø20, 25, 32	5,10,15,20,25,30,40,50

### Tightening torque

When mounting MCFA series, refer to the below table.


Tube I.D.	Hexagon socket head cap screw dia.(mm)	Proper tightening torque N.m[kgf.cm]
ø6, 10	M3	1.1 [11.2] ± 10%
ø16	M4	2.5 [25.5] ± 10%
ø20, 25	M5	5.0 [51.0] ± 10%
ø32	M6	8.0 [81.6] ± 10%

### Cylinder weight

Unit: g


Model	Basic weight MCFA-11	Basic weight (magnet) MCFA-11	Stroke 5 mm MCFA-11
Tube I.D.			
ø6	20	18	3
ø10	32	31	3
ø16	42	58	6
ø20	90	118	10
ø25	161	202	17
ø32	268	330	26

### Installation of sensor switch




### Double acting

$\phi 6$



$\phi 10 \sim \phi 32$



### Material

No.	Tube I.D. Part name	6	Note
1	Body	Aluminum alloy	
2	Head cover	Aluminum alloy	
3	Piston	Aluminum alloy	
4	Rod	Stainless steel	
5	Cover ring	NBR	
6	Rod packing	NBR	
7	Piston packing	NBR	
8	Magnet ring	Magnet material	for with magnet
9	Cushion packing	PU	
10	Snap ring	Spring steel	
11	Fixed ring	Aluminum alloy	
12	Rod front nut	Carbon steel	


No.	Tube I.D. Part name	10	16	20	25	32	Note
1	Body	Aluminum alloy					
2	Head cover	Aluminum alloy					
3	Piston	Aluminum alloy					
4	Cushion packing	NBR					
5	Rod *1	Stainless steel			*2		
6	Wear ring	Resin					
7	Cover ring	NBR					
8	Rod packing	NBR					
9	Piston packing	NBR					
10	Magnet ring	Magnet material					for with magnet
11	Piston gasket	-	NBR				
12	Piston bolt	-	SCM				for without magnet
		-	Stainless steel				for with magnet
13	Snap ring	Spring steel					
14	Rod front nut	Carbon steel					

\*1. When customized material is bearing steel, only two-side across flat (wrench flat) is available.


\*2. Medium carbon steel

### 11

$\phi 6, \phi 10$



$\phi 16\sim\phi 32$




Code Tube I.D.	A	A'	B	B1	C	C1	D	E	GA	GB	H	H1	J	K	L	MM	NN	P	Q	QA	R
6	7	—	13	5.5	22	6.4	3	7	15	10	13	1.8	10	17	—	M3×0.5	M3×0.5×5depth	3.2	—	—	7
10	10	—	15	7	24	8.1	4	7	16.5	10	16	2.4	11	18	—	M4×0.7	M3×0.5×5depth	3.2	—	—	9
16	11	12.5	20	8	32	9.2	6	7	16.5*	11.5	16	4	14	25	5	M5×0.8	M4×0.7×6depth	4.5	4	2	12
20	12	14	26	10	40	11.5	8	9	19	12.5	19	5	16	30	6	M6×1.0	M5×0.8×8depth	5.5	9	4.5	16
25	15.5	18	32	13	50	15.0	10	10	21.5	13	23	5	20	38	8	M8×1.25	M5×0.8×8depth	5.5	9	4.5	20
32	19.5	22	40	17	62	19.6	12	11	23	12.5	27	6	24	48	10	M10×1.25	M6×1.0×9depth	6.6	13.5	4.5	24

\* Without magnet with stroke=5mm, GA=14.5mm.


Code Tube I.D.	T	Without magnet		Magnet	
		S	Z	S	Z
6	6×4.8depth	33	46	33	46
10	6×5depth	36	52	36	52
16	7.6×6.5depth	30	46	40	56
20	9.3×8depth	36	55	46	65
25	9.3×9depth	40	63	50	73
32	11×11.5depth	42	69	52	79

### 11

$\phi 6, \phi 10$



$\phi 16 \sim \phi 32$




Code Tube I.D.	A	A'	B	B1	C	C1	D	E	F	FL	FK	FY	GA	GB	H	H1	J	K	KI	L	MM	NA	NB
6	7	—	13	5.5	22	6.4	3	7	8	9	11	20.5	15	10	18	1.8	10	17	M3×0.5	—	M3×0.5	6	14
10	10	—	15	7	24	8.1	4	7	8	12	12	22	16.5	10	21	2.4	11	18	M3×0.5	—	M4×0.7	7	15
16	11	12.5	20	8	32	9.2	6	7	8	17	13	28	16.5*	11.5	26	4	14	25	M4×0.7	5	M5×0.8	6	18
20	12	14	26	10	40	11.5	8	9	8	20	16	33	19	12.5	29	5	16	30	M4×0.7	6	M6×1.0	8	20
25	15.5	18	32	13	50	15.0	10	10	10	22	20	43.5	21.5	13	33	5	20	38	M5×0.8	8	M8×1.25	10	28
32	19.5	22	40	17	62	19.6	12	11	12	29	24	51.5	23	12.5	42	6	24	48	M5×0.8	10	M10×1.25	12	32

\* Without magnet with stroke=5mm, GA=14.5mm.


Code Tube I.D.	NN	P	Q	QA	R	T	U	Y	Without magnet		Magnet	
									S	Z	S	Z
6	M3×0.5×5depth	3.2	—	—	7	6×4.8depth	10	10.5	33	51	33	51
10	M3×0.5×5depth	3.2	—	—	9	6×5depth	10.5	11.5	36	57	36	57
16	M4×0.7×6depth	4.5	4	2	12	7.6×6.5depth	12.5	15.5	30	56	40	66
20	M5×0.8×8depth	5.5	9	4.5	16	9.3×8depth	13.5	19.5	36	65	46	75
25	M5×0.8×8depth	5.5	9	4.5	20	9.3×9depth	19	24.5	40	73	50	83
32	M6×1.0×9depth	6.6	13.5	4.5	24	11×11.5depth	21	30.5	42	84	52	94

21

$\phi 6, \phi 10$



$\phi 16\sim\phi 32$




Code Tube I.D.	A	A'	B	B1	C	C1	D	E	GA	GB	H	H1	J	K	L	MM	NN	P	Q	QA	R	SA
6	7	—	13	5.5	22	6.4	3	7	15	16	13	1.8	10	17	—	M3×0.5	M3×0.5×5depth	3.2	—	—	7	6
10	10	—	15	7	24	8.1	4	7	16.5	16	16	2.4	11	18	—	M4×0.7	M3×0.5×5depth	3.2	—	—	9	6
16	11	12.5	20	8	32	9.2	6	7	16.5*	19	16	4	14	25	5	M5×0.8	M4×0.7×6depth	4.5	4	2	12	7.5
20	12	14	26	10	40	11.5	8	9	19	21.5	19	5	16	30	6	M6×1.0	M5×0.8×8depth	5.5	9	4.5	16	9
25	15.5	18	32	13	50	15.0	10	10	21.5	22	23	5	20	38	8	M8×1.25	M5×0.8×8depth	5.5	9	4.5	20	9
32	19.5	22	40	17	62	19.6	12	11	23	22.5	27	6	24	48	10	M10×1.25	M6×1.0×9depth	6.6	13.5	4.5	24	10

\* Without magnet with stroke=5mm, GA=14.5mm.


Code Tube I.D.	T	W	Without magnet		Magnet	
			S	Z	S	Z
6	6×4.8depth	13	38	70	38	70
10	6×5depth	16	36	74	36	74
16	7.6×6.5depth	16	30	69.5	40	79.5
20	9.3×8depth	19	36	83	46	93
25	9.3×9depth	23	40	95	50	105
32	11×11.5depth	27	42	106	52	116

### 21

$\phi 6, \phi 10$



$\phi 16 \sim \phi 32$



Code Tube I.D.	A	A'	B	B1	C	C1	D	E	F	FL	FK	FY	GA	GB	H	H1	J	KI	L	MM	NA	NB	P	Q
6	7	—	13	5.5	22	6.4	3	7	8	9	11	20.5	15	16	18	1.8	10	M3×0.5	—	M3×0.5	6	14	3.2	—
10	10	—	15	7	24	8.1	4	7	8	12	12	22	16.5	16	21	2.4	11	M3×0.5	—	M4×0.7	7	15	3.2	—
16	11	12.5	20	8	32	9.2	6	7	8	17	13	28	16.5*	19	26	4	14	M4×0.7	5	M5×0.8	6	18	4.5	4
20	12	14	26	10	40	11.5	8	9	8	20	16	33	19	21.5	29	5	16	M4×0.7	6	M6×1.0	8	20	5.5	9
25	15.5	18	32	13	50	15.0	10	10	10	22	20	43.5	21.5	22	33	5	20	M5×0.8	8	M8×1.25	10	28	5.5	9
32	19.5	22	40	17	62	19.6	12	11	12	29	24	51.5	23	22.5	42	6	24	M5×0.8	10	M10×1.25	12	32	6.6	13.5

\* Without magnet with stroke=5mm, GA=14.5mm.


Code Tube I.D.	QA	R	SA	T	U	W	Y	Without magnet		Magnet	
								S	Z	S	Z
6	—	7	6	6×4.8depth	10	13	10.5	38	75	38	75
10	—	9	6	6×5depth	10.5	16	11.5	36	79	36	79
16	2	12	7.5	7.6×6.5depth	12.5	16	15.5	30	79.5	40	89.5
20	4.5	16	9	9.3×8depth	13.5	19	19.5	36	93	46	103
25	4.5	20	9	9.3×9depth	19	23	24.5	40	105	50	115
32	4.5	24	10	11×11.5depth	21	27	30.5	42	121	52	131



Technical data




Caution for safety  
(Read before installing)







### Order example

**MCFCB – S – 11 – 16 – 10M**



#### \* STYLE

Code	Symbol	Description
1 1		Double acting / Male thread
1 2		Double acting / Female thread
1 5		Single acting / Normally returned male thread
1 6		Single acting / Normally returned female thread




\* Single acting only for  $\phi 6, \phi 8, \phi 10$ .

\* Single acting without magnet type.

### Features

- Compact and space saving.
- Flush fitting sensor.

### Specification

Model	MCFCB					
Acting type	Single / Double			Double acting		
Tube I.D. (mm)	6	8	10	12	16	20
Port size	M3×0.5					M5×0.8
Medium	Air					
Max. operating pressure	0.7 MPa					
Min. operating pressure (MPa)	Single	0.3	0.2	—		
	Double	0.15	0.1	0.07	0.05	
Proof pressure	1 MPa					
Lubrication	Not required					
Ambient temperature	-5~+60°C (No freezing)					
Available speed range	50~500 mm/sec					
Sensor switch (*)	RDC(V), RQC(V)  , RDFE(V)  , RDGV 					

\* Short stroke length (4, 6, 8mm) only use RDGV.


### Double acting – Table for standard stroke

Tube I.D.	Stroke (mm)
$\phi 6, 8$	4, 6, 8, 10, 15, 20, 25
$\phi 10$	4, 6, 8, 10, 15, 20, 30
$\phi 12, 16$	5, 10, 15, 20, 25, 30
$\phi 20$	5, 10, 15, 20, 25, 30, 35, 40, 45, 50

### Single acting – Table for standard stroke

Tube I.D.	Stroke (mm)
$\phi 6$	4, 6, 8
$\phi 8, 10$	4, 6, 8, 10

### Installation of sensor switch






ø6, ø8, ø10

ø12, ø16, ø20

Double acting

Single acting



### Material

No.	Part name	Material	Note	Q'y	Component parts (inclusion)	Repair kits (inclusion)
1	Body	Aluminum alloy		1		
2	Rod cover	Copper	ø12~20 use aluminum alloy	1	●	
3	Piston	Aluminum alloy		1	●	
4	Piston rod	Stainless steel		1		
5	Piston packing	NBR		1	●	●
6	Rod packing	NBR		1	●	●
7	Magnet ring	Magnet material	for with magnet	1	●	
8	Piston	Aluminum alloy	for with magnet	1	●	
9	Cover ring	NBR		1	●	●
10	Wear ring	Resin		1	●	
11	Snap ring	Spring steel		1	●	
12	Piston gasket	NBR	Only for ø20	1	●	●
13	Piston bolt	Stainless steel	Only for ø20	1	●	
14	Cushion packing	PU		2	●	●
15	Spring	Stainless steel		1	●	
16	Silencer	Brass		1	●	

### Order example Component parts

Tube I.D.	Component parts
ø6	CP-MCFB-6(M)
ø8	CP-MCFB-8(M)
ø10	CP-MCFB-10(M)
ø12	CP-MCFB-12(M)
ø16	CP-MCFB-16(M)
ø20	CP-MCFB-20(M)

\* M: With magnet.

### Repair kits

Tube I.D.	Repair kits
ø6	PS-MCFB-6
ø8	PS-MCFB-8
ø10	PS-MCFB-10
ø12	PS-MCFB-12
ø16	PS-MCFB-16
ø20	PS-MCFB-20



### Seal kit



Acting type	Rod packing		Piston packing		Cover ring		Piston gasket	
	Double acting	Normally retruned	Double acting	Single acting	Double acting	Normally retruned	Double acting	Normally retruned
Tube I.D. / Q'y	1	0	1	1	1	0	1	0
ø6	KSYR-4	—	PP-6	KSYP-6	d7×w1	—	—	—
ø8	KSYR-5	—	PP-8	KSYP-8	d9×w1	—	—	—
ø10	KSYR-6	—	OPA-10	KSYP-10	d10×w1	—	—	—
ø12	KSYR-6	—	OPA-12	—	d10×w1	—	—	—
ø16	KSYR-8	—	OPA-16	—	d14×w1	—	—	—
ø20	KSYR-10	—	OPA-20	—	d18×w1	—	d6×w1	—



### Cylinder weight

Unit: g

Model	MCFB-11								MCFB-11 (With magnet)							
																
Tube I.D.	Stroke (mm)								Stroke (mm)							
	4	6	8	10	15	20	25	30	4	6	8	10	15	20	25	30
$\varnothing 6$	15	16	18	19	22	25	28	—	16	17	18	19	22	25	28	—
$\varnothing 8$	19	20	22	23	26	29	33	—	20	21	23	24	27	31	34	—
$\varnothing 10$	21	22	24	25	29	32	36	39	23	24	26	27	31	34	38	41
Tube I.D.	Stroke (mm)								Stroke (mm)							
	5	10	15	20	25	30	40	50	5	10	15	20	25	30	40	50
$\varnothing 12$	24	29	34	39	44	49	—	—	27	32	37	42	47	52	—	—
$\varnothing 16$	38	45	52	59	66	73	—	—	42	49	56	63	70	77	—	—
$\varnothing 20$	63	73	83	93	103	113	133	153	68	78	88	98	108	118	138	158

Model	MCFB-12								MCFB-12 (With magnet)							
																
Tube I.D.	Stroke (mm)								Stroke (mm)							
	4	6	8	10	15	20	25	30	4	6	8	10	15	20	25	30
$\varnothing 6$	14	15	16	18	21	24	27	—	15	16	17	18	21	24	27	—
$\varnothing 8$	17	18	19	21	24	27	30	—	18	19	20	22	25	28	31	—
$\varnothing 10$	18	19	21	22	26	29	33	36	20	21	23	24	28	31	35	38
Tube I.D.	Stroke (mm)								Stroke (mm)							
	5	10	15	20	25	30	40	50	5	10	15	20	25	30	40	50
$\varnothing 12$	21	26	31	36	41	46	—	—	24	29	34	39	44	49	—	—
$\varnothing 16$	31	38	45	52	59	66	—	—	35	42	49	56	63	70	—	—
$\varnothing 20$	52	62	72	82	92	102	122	142	57	67	77	87	97	107	127	147

